



AQL 03A/1/CIS/LED

Self-contained 3 watt, maintained surface mount led luminaire, including control module, series Aqualux

Product Information

| | |
|-----------------|-----------------------|
| Type | AQL 03A/1/CIS/LED |
| Catalog number | 7141055 |
| Category_ | Escape route lighting |
| GTIN | 08713812761336 |
| GID | 7TCA091180R0158 |
| Serie | Aqualux |
| Warranty (Year) | 5 |



Characteristics

| | |
|---|-------------------------------------|
| Power supply system | Self-contained individual battery |
| Continuous operation | Yes |
| Mounting Method | Ceiling;Wall |
| Mounting form | Surface |
| Material housing | Aluminium / plastic |
| Colour housing | White / aluminium |
| Material cover | Plastic, transparent |
| Material | Aluminium / polycarbonate |
| Colour | White / aluminium |
| Length (mm) | 381 |
| Width (mm) | 170 |
| Height/depth (mm) | 75 |
| Nominal voltage (V) | 230 |
| Voltage type | AC |
| Duration (hours) | 1 |
| Battery | NiCd |
| Monitoring equipment | Safety module for monitoring |
| With lamp | Yes |
| Lamp Type | Led |
| Lamp holder | Other |
| Lamp power (W) | 3 |
| Number of lamps | 1 |
| Light output in emergency operation (lm) | 119 |
| Average lifespan light source (hours) | 50.000 |
| Colour of light | White |
| Colour temperature (K) | 6500 |
| Protection class | II |
| Degree of protection (IP) | 65 |
| With remote switch connection | No |
| Wiring system | Maintained / non-maintained circuit |
| Type of indicator | Not applicable |
| Circuit | Other |
| Impact strength (IK) | 10 |
| Power consumption maintained mode (W) | 5,1 |
| Apparent power consumption maintained mode (VA) | 9,9 |
| Nominal current (mA) | 42,5 |
| Inrush Current (A - 0.1ms) | 18 |
| Powerfactor | 0,52 |
| Temperature range (°C) | 0 ~ +35 |

Article Details

| | |
|-----------------|---------------------|
| Product class | Emergency luminaire |
| E-code | EC001957 |
| Discount group | 30502 |
| Harmonized code | 9405408440 |
| GLN | 8713812000008 |

Ordering information

| | |
|------------------------|--------|
| Orderable | Yes |
| Order-Unit | Pieces |
| Minimum order quantity | 1 |
| Order Increment | 1 |

Supply Information

| | |
|-----------------------------------|-----------------|
| Weight (kg) | 1,643 |
| Packaging | Cardboard box |
| Packaging dimensions (LxWxH) (mm) | 426 x 188 x 111 |