


Temp.
0 25 40 50 60C



Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



Molded Case Circuit Breaker E 100 Line

GES6114

Current Ratings

60, 70 and 80 Amperes

Voltage Ratings

1-pole – 277 Vac, 125 Vdc

2- and 3-pole – 480 Vac, 250 Vdc

Frequency Rating

60 Hertz

Type TED, 60-80 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous

Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.