

TECHNICAL DATA SHEET - INTERACTIVE PDF

Conduit Hub, stainless steel

For use with conduit and enclosure

T&B® Fittings



Stainless steel conduit hub provides a Type 4X connection means between conduit and enclosure.

Certifications / Standards:



[3-Part Specification:](#)
[Tools and Calculators](#)

Features:

- Compact body design and gasket helps make the conduit hub suitable for installation in tight spaces
- Conduit seal is extended to cover threads on conduit
- Conduit hub offers a UL Type 4X rating, IP66 and IP67 and is suitable for wash down areas

Applications:

- For use with stainless steel electrical enclosures and conduit
- Food and beverage facilities

Product selection and dimensions - (inches)

Part no.	Trade size	A NPT	B NPT	C	D	E	F	G
H050FGSST	½"	½"	½"	1.181	0.945	0.709	1.571	0.583
H075FGSST	¾"	¾"	¾"	1.417	1.378	0.984	1.701	0.598
H100FGSST	1"	1"	1"	1.811	1.811	1.181	1.984	0.697
H125FGSST	1¼"	1¼"	1¼"	2.126	2.165	1.535	2.165	0.724
H150FGSST	1½"	1½"	1½"	2.480	2.362	1.772	2.256	0.724
H200FGSST	2"	2"	2"	3.032	2.913	2.205	2.496	0.724

Note: Product must be installed in accordance with applicable national and local electrical codes.

Conforms to:

- UL Listed, Type 4X, IP66 and IP67 rated

Material / Finishes:

- Stainless Steel, Type 316 (corrosion resistance)
- TPE Seal Material (FDA compliant)

