

PRODUCT SPECIFICATION

LTCXXW1LS11

Daylite 230v AC Clear IP65 EMEX Test Surface

Catalogue Number **LTCXXW1LS11**

GID **7TCA09114OR0545**

Warranty **3 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Mains / Slave Operation**

Mounting Method/Form **Ceiling, Wall Surface**

Housing Material **Plastic**

Colour **White**

Dimensions (LxWxD) **342 x 98 x 72 mm**

Temperature Range **0 to 40°C**

Weight **0.67 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**

Battery **Mains / Central Battery**

Monitoring Equipment **EMEX test**

Lamp **1 x 2W LED**

Emergency Light Output (Lumens) **251**

Average Lifespan light source (Hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 4000 / 80**

Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**

Exit Sign Viewing/Recognition Distance (m) **23**

Nominal Voltage **220-240v AC 50/60Hz**

Power Consumption **4.6 VA / 4.4 Watts**

Current **Nominal: 13.59mA (mA) Inrush: 1.1A**

Accessories

RSEN2X Down ISO7010 Legend

RSEN3X Left ISO7010 Legend

RSEN6X Right ISO7010 Legend

RSEN5X Up ISO7010 Legend

RSB1X Arabic English Legend

XTR Semi-recessing bezel White



Exit Sign
LTCXXW1LS11 + RSEN5X



Bulkhead
LTCXXW1LS11

