

产品认证证书

II型自愿认证

证书编号: CQC2010010307387700

发证日期: 2022年02月23日

有效期至: 2032年02月22日

委托人名称 ABB Stotz-Kontakt GmbH
及注册地址 Eppelheimer Strasse 82 69123 Heidelberg Germany

制造商名称 ABB Stotz-Kontakt GmbH
及注册地址 Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称 ABB Stotz-Kontakt GmbH
及生产地址 Eppelheimer Strasse 82 69123 Heidelberg Germany

产品名称和系列、规格、型号 电动机保护用断路器
MS132, MO132, MS132-T, MS132-B, MO132-B, MS132-K, MS132-L; 具体参数和型号解释详见附件

产品标准和技术要求 GB/T 14048.2-2020;GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年09月02日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

陈昕

签发

谢肇煦

中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0132247

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2010010307387700

Valid from: Feb.23,2022

Valid until: Feb.22,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND LOCATION OF THE FACTORY ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

PRODUCT NAME, MODEL AND SPECIFICATION Motor protection circuit breaker
MS132, MO132, MS132-T, MS132-B, MO132-B, MS132-K, MS132-L; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 14048.2-2020;GB/T 14048.4-2020

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Sep.02,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

陈昕

SIGNATURE

谢肇煦

CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0132247

产品认证证书

II型自愿认证

证书编号: CQC2010010307387700

第1页 共3页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 132247

MS132, MO132, MS132-T, MS132-B, MO132-B, MS132-K, MS132-L

Uimp: 6kV;

Ui: 690V;

Ue: AC230V, AC400V, AC440V, AC500V, AC690V;

In: 0.1-0.16A, 0.16-0.25A, 0.25-0.4A, 0.4-0.63A, 0.63-1.0A, 1.0-1.6A, 1.6-2.5A, 2.5-4.0A, 4.0-6.3A, 6.3-10A, 8.0-12A, 10-16A, 16-20A, 20-25A, 25-32A;

过电流脱扣器类型: 热磁式;

AC230V, AC400V: Ics=30kA(25-32A), Icu=50kA(25-32A); Ics=Icu=50kA(20-25A);

Ics=Icu=100kA(0.1-0.16A, 0.16-0.25A, 0.25-0.4A, 0.4-0.63A, 0.63-1.0A, 1.0-1.6A, 1.6-2.5A, 2.5-4.0A, 4.0-6.3A, 6.3-10A, 8.0-12A, 10-16A, 16-20A);

AC440V: Ics=Icu=30kA(2.5-4.0A, 4.0-6.3A, 6.3-10A, 8.0-12A, 10-16A, 16-20A, 20-25A, 25-32A);

Ics=Icu=100kA(0.1-0.16A, 0.16-0.25A, 0.25-0.4A, 0.4-0.63A, 0.63-1.0A, 1.0-1.6A, 1.6-2.5A);

AC500V: Ics=Icu=10kA(20-25A, 25-32A); Ics=Icu=20kA(2.5-4.0A, 4.0-6.3A, 6.3-10A, 8.0-12A, 10-16A, 16-20A); Ics=Icu=100kA(0.1-0.16A, 0.16-0.25A, 0.25-0.4A, 0.4-0.63A, 0.63-1.0A, 1.0-1.6A, 1.6-2.5A);

AC690V: Ics=Icu=3kA(2.5-4.0A, 4.0-6.3A, 6.3-10A, 8.0-12A, 10-16A, 16-20A, 20-25A, 25-32A);

Ics=Icu=100kA(0.1-0.16A, 0.16-0.25A, 0.25-0.4A, 0.4-0.63A, 0.63-1.0A, 1.0-1.6A, 1.6-2.5A);

选择性类别: A;

使用类别: AC-3, AC-3e;

适用频率: 50/60Hz;

脱扣级别: 10;

极数: 3P;

适用于隔离;

配用的辅助触头:



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2010010307387700

第 2 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 132247

HKF1-xx, HKF1-xxK (CQC 证书编号: CQC2017010304032779)

lth: 5A;

AC-15: Ue:/le: 24V/3A, 120V/3A, 240V/1.5A;

DC-13: Ue:/le: 24V/1A, 125V/0.27A, 250V/0.11A;

1NO,1NC

HK1-xx, HK1-xxK, SK1-xx, SK1-xxK,CK1-xx (CQC 证书编号:

CQC2017010304032778)

lth: 6A;

AC-15: Ue:/le: 24V/6A, 110-120V/6A, 220-240V/4A, 400V/3A, 690V/1A;

DC-13: Ue:/le: 24V/2A, 110-125V/0.55A, 250V/0.27A, 400V/0.15A, 600V/0.15A;

2NO, 2NC



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2010010307387700

第 3 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 132247

型号解释:

MS	132	-	16	K	T	HKF1-11
1	2		3	4	5	6

1: Product series 产品系列 (MS/MO)

MS: with thermal tripping and magnetic tripping 带过载和短路

MO: only have magnetic tripping that thermal tripping function is deactivated
只有短路保护

2: Basic type 基本型号 (132)

3: Current range 电流等级 (0.16/0.25/0.4/0.63/1.0/1.6/2.5/4.0/6.3/10/12/16/20/25/32)

4: blank: standard version (screw terminal) 空白: 标准版 (螺纹端子)

K: Push In terminal 插接型端子

5: blank: standard product 空白: 标准版

T: Transformer protection 变压器保护

B: Railway Application 铁路用

L: Green House Application Green House 项目用

6: blank: without accessory 空白: 不带附件

HKF1: mounted accessory for HKF1-xx, HKF1-xxK, HK1-xx, HK1-xxK, SK1-xx,

SK1-xxK, CK1-xx

HKF1: 带附件 HKF1-xx, HKF1-xxK, HK1-xx, HK1-xxK, SK1-xx, SK1-xxK, CK1-xx



中国质量认证中心

