


MULTIPLE OF TRIP RATING PLUG



MULTIPLE OF TRIP RATING PLUG



Frames 800-4000A PowerBreak

All Voltages: 600 Vac and below

Low-Voltage Circuit Breakers

EntelliGuard TU trip unit for PowerBreak II Circuit Breakers
UL 489 Stored Energy Mechanism Circuit Breakers

Adjustable Selective Instantaneous Trip

Curves apply at 60 Hertz and from -20°C to 55°C circuit breaker ambient temperature.

DES100

Adjustable Instantaneous Minimum Pickup 2X Rating Plug

Adjustable Instantaneous RELT Minimum Pickup 1.5X Rating Plug