

DRAWING NUMBER	D 2501 8003-015
----------------	-----------------

0T600U03

600VAC 600A 3-Pole
Non-Fused Open Type Switch
Rotary operated

cuLus Listed, 97C2

Open Type Switch
UL File #101914

CSA Certified, File #58077

Short Circuit Rating at 600VAC	
IkA	Fuse/A Fuse class
100	800 J, T or L
100	600 RK5
35	Circuit Breaker

3-phase HP Ratings				
VAC	208	240	480	600
HP	150	200	450	500

Accessories:

Operating Handle

OHB175J12 - Type 1, 3R, 12

UHBI/3L1Z = type 1, 3K, 4, 4X, 1Z
Ref drawing D 2301 8001=001 for

pistol grip handle dimensions and installation details.

Terminal Lug Kits

OZXA-800 - 6 lugs

Wire Range:

(2) #2 AWG - 600kcmil
AL7CU, UL Listed

Operating Shaft - Max. encl. depth

OXFORD 12X220 - 12.00 in.

0XP12X280 - 14.50 in.
0XP12X325 - 16.30 in.

OXFORD 19.10 in.



OX-P12X465 - 21.80 in.

OX-P12X625 - 28.10 in.

Auxiliary Contacts

OA1G10 – 1n.o.

OA3G01 – 1n.c.



REV.	REV. OR LET.	DATE	REV. OR APD BY	THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS CONFIDENTIAL INFORMATION WHICH MUST NOT BE DUPLICATED, USED OR DISCLOSED OTHER THAN EXPRESSLY AUTHORIZED BY ABB Inc.		DATE 14/3/11 DRAWN F. GARCIA CHK'D PROJECT NO.	REV. A SIZE A	TITLE OT600U03 3-Pole Non-Fused Open Type Switch DRAWING NUMBER D 2501 8003-015
	REVISIONS				ABB Inc.	SHEET 1 OF 1	A	D 2501 8003-015