

## Product Specification

### Indulux



Luminaire

#### IND1LSLTC

#### Indulux LED S/S 230V LTC

Catalogue Number  
 Category  
 GTIN  
 GID  
 Warranty (Year)  
 Other

IND1LSLTC  
 Combined Escape route or Sign Luminaire  
 05415022466959  
 7TCA091720R0180  
 3  
 Refer to ABB warranty terms & conditions



Configurable pictograms included

Power Supply System  
 Mounting Method  
 Mounting Form  
 Material Housing  
 Colour Housing  
 Material Cover  
 Material  
 Colour  
 Length (mm)  
 Width (mm)  
 Height/depth (mm)  
 Nominal Voltage (V)  
 Voltage Type  
 Duration (hours)  
 Battery  
 Monitoring Equipment  
 Lamp Type  
 Lamp Power  
 Number of Lamps  
 Light output in Emergency Operation (lm)  
 Average Lifespan light source (hours)  
 Colour of Light  
 Colour Temperature (K)  
 CRI  
 Degree of Protection (IP)  
 Impact Strength (IK)  
 Wiring System  
 Type of Legend

Mains / Slave Operation  
 Ceiling, Wall  
 Surface  
 316L stainless steel/plastic  
 White/Grey  
 No cover supplied  
 316L stainless steel/plastic  
 Silver/Clear  
 398  
 100  
 100  
 220-240  
 AC 50/60Hz  
 Mains / Central Battery  
 Mains / Central Battery  
 EMEX test  
 LED  
 5  
 1  
 400  
 60000  
 White  
 6000  
 80  
 68  
 10  
 Mains / CBU  
 Varies

Legend style	Internal Foil supplied
Recognition distance (m)	17
Power Consumption Maintained mode (W)	13
Power Consumption Maintained mode (VA)	14
Nominal current (mA)	60
Inrush Current (A to 0.1ms)	2
Power Factor	0.92
Temperature range (°C)	-25 to +40°C
Weight (Kg)	1.4
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	430 x 130 x 140

### **Accessories**

**102601K** Cable Entry Cover kit

**102702K** Battery replacement