


Aqualux

Durable & high performance



Edge-lit LED exit sign

- Attractive aluminium modular enclosure
- Clear polycarbonate broad delivery diffuser
- Intelligent self-test as standard
- Complies to IEC 60598.2.22



LED base unit

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTOW3L261	CT 2LED M3	220-240 AC 50Hz	2 x LED 1W	59	9.9 / 5.1	3	0-25	1.7
OW1L261HF	2XLED SIGN 230VHF	220-240 AC/DC 0-60Hz	2 x LED 1W	89	8 / 3.5	230V	0-40	1.5
OW1L261LTC	2XLED 230V LTC	220-240 AC 50/60Hz	2 x LED 1W	89	8 / 3.5	230V	0-40	1.5
OW3L261	2LED M3	220-240 AC 50Hz	2 x LED 1W	59	9.9 / 5.1	3	0-25	1.7
OW3L261LS*	2LEDM3 LSENS	220-240 AC 50Hz	2 x LED 1W	59	9.9 / 5.1	3	0-25	1.7
OW3L261V2	2LED M3 220V60HZ	220-240 AC 50/60Hz	2 x LED 1W	59	9.9 / 5.1	3	0-25	1.7
DLOW3LS60	3W LED DALI M3	220-240 AC 50Hz	1 x LED 3W	79	9.9 / 5.1	3	0-25	1.7

* Includes daylight sensor

Legends

Single sided		Double sided	
Part No.	Pictogram	Part No.	Pictogram
RSEN2W		RSEN2W + RSEN6W	
RSEN3W		RSEN2W + RSEN2W	
RSEN6W			
RSEN5W			
Arabic legend format			
On request			

ISO 7010 pictogram legends are shown
Euro format & Special legends are available
to order see pages 139-141

Accessories

Order code	Description
OW/BWM	Wall mount end cantilever bracket
OW/DSC	Blank double sided diffuser
OW/BCR	Recessing kit

