

QUICK REFERENCE

Ty-Rap®

High-performance cable ties for quality, performance and innovation

Features

- Working temperature: -40 °F to +185 °F
- UL Listed
- Plenum rated AH-2 for indoor use



Ty-Rap cable ties

Standard part number			Bulk part number				
Natural nylon (indoor)	UV weather resistant nylon black (outdoor)	Std. pkg. qty.	Natural nylon (indoor)	UV weather resistant nylon black (outdoor)	Bulk pkg. qty.	Nominal length (in.)	Tensile strength (lb.)
TY523M	TY523MX	100	TY23M	TY23MX	1000	4	18
TY52315M	TY52315MX	100	TYB2315M	TYB2315MX	1000	7	18
TY5232M	TY5232MX	100	TY232M	TY232MX	1000	8	18
TY5234M	TY5234MX	100	TY234M	TY234MX	1000	14	18
TY526M	TY526MX	100	TY26M	TY26MX	1000	11	30
TY5244M	TY5244MX	100	TY244M	TY244MX	1000	14	30
TY524M	TY524MX	100	TY24M	TY24MX	1000	5	40
TY5242M	TY5242MX	100	TY242M	TY242MX	1000	8	40
TY525M	TY525MX	100	TY25M	TY25MX	1000	7	50
TY5253M	TY5253MX	100	TY253M	TY253MX	1000	11	50
TY528M	TY528MX	100	TY28M	TY28MX	1000	14	50
TY5272M†	TY5272MX*	50	TY272M†	TY272MX*	500	9	120
TY527M†	TY527MX*	50	TY27M†	TY27MX*	500	13	120
TY5275M	TY5275MX	50	TY275M	TY275MX	500	18	120
TY5277M	TY5277MX	50	TY277M	TY277MX	500	24	120
TY529M	TY529MX	50	TY29M	TY29MX	500	30	120
TY53510M†	TY53510MX*	50	-	-	-	10	175
TY54513M†	TY54513MX*	50	-	-	-	13	175
Mounting bases							
TC150X150A-L*	TC150X150AX-L*	50	TC150150A*	TC150150AX*	500		4-Way 1.5"
TC5345A†	TC5345AX†	100	TC345A†	TC345AX†	1000		4-Way 1"
TC5344A†	TC5344AX†	100	TC344A†	TC344AX†	1000		4-Way 0.75"
TC5342A*	N/A	100	TC342A*	TC342A-X†	1000		2-Way 1"

*Not UL Listed or Recognized
 † UL Recognized only

Tooling



ERG50 Tool for 18–50 lb.



ERG120 Tool for 50–120 lb.

QUICK REFERENCE

Catamount®

General purpose contractor cable ties

Features

- Working temperature: -40 °F to +185 °F
- UL Listed
- Plenum rated AH-2 for indoor use



Catamount cable ties

Standard part number			Bulk part number				
Natural nylon (indoor)	UV weather resistant nylon black (outdoor)	Std. pkg. qty.	Natural nylon (indoor)	UV weather resistant nylon black (outdoor)	Bulk pkg. qty.	Nominal length (in.)	Tensile strength (lb.)
L-4-18-9-C*†	L-4-18-0-C*†	100	L-4-18-9-M*†	L-4-18-0-M*†	1000	4	18
TY125-18-100	TY125-18X-100*†	100	TY125-18	TY125-18X*†	1000	5	18
L-6-18-9-C*†	L-4-18-0-C*†	100	L-6-18-9-M*†	L-4-18-0-M*†	1000	6	18
L-8-18-9-C*†	L-4-18-0-C*†	100	L-8-18-9-M*†	L-8-18-0-M*†	1000	8	18
L-4-18ID-9-C**	-	100	L-4-18ID-9-M**	-	1000	4	18
TT-7-30-9-L**	TT-7-30-0-L**	50	-	-	-	7	30
TT-11-30-9-L**	TT-11-30-0-L**	50	-	-	-	11	30
TT-14-30-9-L**	TT-14-30-0-L**	50	-	-	-	14	30
L-5-30MH-9-C	L-5-30MH-0-C**	100	L-5-30MH-9-M	L-5-30MH-0-M**	1000	5	30
L-5-40-9-C*†	L-5-40-0-C*†	100	L-5-40-9-M*†	L-5-40-0-M*†	1000	5	40
L-8-40-9-C*†	L-8-40-0-C*†	100	L-8-40-9-M*†	L-8-40-0-M*†	1000	8	40
L-11-40-9-C*†	L-11-40-0-C*†	100	L-11-40-9-D*†	L-11-40-0-D*†	500	11	40
L-14-40-9-C*†	L-14-40-0-C*†	100	L-14-40-9-D*†	L-14-40-0-D*†	500	14	40
L-7-50-9-C*†	L-7-50-0-C*†	100	L-7-50-9-M*†	L-7-50-0-M*†	1000	7	50
TY225-50-100*†	TY225-50X-100*†	100	TY225-50*†	TY225-50X*†	1000	9	50
L-11-50-9-C*†	L-11-50-0-C*†	100	L-11-50-9-D*†	L-11-50-0-D*†	500	11	50
L-14-50-9-C*†	L-14-50-0-C*†	100	L-14-50-9-D*†	L-14-50-0-D*†	500	14	50
L-7-50MH-9-C*	L-7-50MH-0-C*	100	L-7-50MH-9-M*	L-7-50MH-0-M*	1000	7	50
L-11-50MH-9-C**	L-11-50MH-0-C**	100	L-11-50MH-9-D**	L-11-50MH-0-D**	500	11	50
L-14-50MH-9-C**	L-14-50MH-0-C**	100	L-14-50MH-9-D**	L-14-50MH-0-D**	500	14	50
L-5-50R-9-C**	L-5-50R-0-C**	100	L-5-50R-9-D**	L-5-50R-0-D**	500	5	50
L-5-50PM-9-C**	L-5-50PM-0-C**	100	L-5-50PM-9-D**	L-5-50PM-0-D**	500	5	50
L-7-50ID-9-C**	L-7-50ID-0-C	100	L-7-50ID-9-M**	L-7-50ID-0-M	1000	7	50
L-8-120-9-C*†	L-8-120-0-C*†	100	L-8-120-9-L*†	L-8-120-0-L*†	50	8	120
L-11-120-9-C*†	L-11-120-0-C*†	100	L-11-120-9-L*†	L-11-120-0-L*†	50	11	120
L-14-120-9-C*†	L-14-120-0-C*†	100	L-14-120-9-L*†	L-14-120-0-L*†	50	14	120
TY450-120-50*†	TY450-120X-50*†	50	-	-	-	18	120
-	-	-	TY600-120*†	TY600-120X*†	50	25	120
-	TY800-120X-50*†	50	TY800-120*†	TY800-120X*†	50	31	120
L-14-120MH-9-C**	L-14-120MH-0-C**	100	-	-	-	14	120
Mounting bases							
MPNY-750-9-C**	MPNY-750-0-C**	100	MPNY-750-9-D**	MPNY-750-0-D**	500	4-Way 0.75"	
MPNY-1000-9-C**	MPNY-1000-0-C**	100	MPNY-1000-9-D**	-	500	4-Way 1"	

*UL Listed
**UL Recognized

† Plenum rated AH-2 & flame rated V-2
TT = Twist Tail

MH = Screw mount
R = Releasable

ID = Identification

ABB Installation Products Inc.
Electrification business
860 Ridge Lake Blvd.
Memphis, TN 38120

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Installation Products Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved