

PRODUCT SPECIFICATION

CTWWA3LS11

Weatherforce Self-Contained PRIS IP65 Naveo Surface

Catalogue Number **CTWWA3LS11**
 GID **7TCA091180R0353**
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Metal/plastic**
 Colour **White**
 Dimensions (LxWxD) **400 x 140 x 100 mm**
 Temperature Range **0 to 30°C**
 Weight **1.82 Kg**

Emergency Duration (Hours) **3 Hours**
 Battery **NiCd**
 Monitoring Equipment **Naveo®Pro**
 Lamp **1 x 2W LED**
 Emergency Light Output (Lumens) **207**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 4000 / 80**
 Degree of Protection **IP65 IK10**

Type of Legend **Single or Double Sided**
 Exit Sign Viewing/Recognition Distance (m) **24**
 Nominal Voltage **220-240v AC 50/60Hz**
 Power Consumption **6.1 VA / 3.9 Watts**
 Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

Accessories

- RSEN2120** Down ISO7010 Legend
- RSEN3120** Left ISO7010 Legend
- RSEN6120** Right ISO7010 Legend
- RSEN5120** Up ISO7010 Legend
- RSEN120** ISO7010 Legend Separate Arrow for Up, Down, Left or Right installation
- RSB1B** Arabic English Legend
- BBZ** Semi recessing bezel White



Exit Sign
CTWWA3LS11 + RSEN5120



Bulkhead
CTWWA3LS11

