



## Declaration of Conformity

This declaration of conformity is issued under the sole responsibility of the manufacturer

**ABB Low-voltage Products Division**  
**8155 T&B Blvd**  
**Memphis, Tennessee 38125**  
**USA**

Object of declaration

### Terminals

**Type: Ring Terminals, Fork Terminals, Flat Blade Terminal, Quick Connector, Lip Blade Terminal, Bullet Disconnect, Butt Splice, Nylon-Insulated Piggyback**

The object of the declaration described above is in conformity with the relevant Australian / New Zealand harmonization legislation, and are in conformity with the following harmonized standards or other normative documents:

**IEC 61210:2 2010**  
**AS NZS 61210-2002**

**AS NZS 4437-1996**  
**IEC 60352-2:2006**

### Signed for and on behalf of

ABB Low-voltage Products Division

**ABB**

Memphis, Tennessee, USA on **02 December 2017**

**Michael Pratt**  
GPG R&D Director

**Bill Haigis**  
Sr. Global  
Operations  
Manager



Refer to below tables for catalog numbers, item descriptions and performance classifications.

## ANNEX I Catalog Number Description

All Parts below meet requirements of IEC60352-2

Cat. No.	Description	Wire size & bolt size	Tooling
R1.5-3VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	0.5-1.5SQMM M3	ERG9004
R1.5-4VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	0.5-1.5SQMM M4	
R1.5-5VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	0.5-1.5SQMM M5	
R1.5-6VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	0.5-1.5SQMM M6	
R1.5-8VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	0.5-1.5SQMM M8	
R1.5-10VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	0.5-1.5SQMM M10	
R1.5-12VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	0.5-1.5SQMM M12	
R2.5-3VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	1.5-2.5SQMM M3	
R2.5-4VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	1.5-2.5SQMM M4	
R2.5-5VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	1.5-2.5SQMM M5	
R2.5-6VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	1.5-2.5SQMM M6	
R2.5-8VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	1.5-2.5SQMM M8	
R2.5-10VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	1.5-2.5SQMM M10	
R2.5-12VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	1.5-2.5SQMM M12	
R6-4VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	4-6SQMM M4	
R6-5VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	4-6SQMM M5	
R6-6VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	4-6SQMM M6	
R6-8VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	4-6SQMM M8	
R6-10VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	4-6SQMM M10	
R6-12VDC-H	Vinyl-Insulated Ring Terminal, Double Crimp	4-6SQMM M12	
F1.5-3VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	0.5-1.5SQMM M3	
F1.5-4VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	0.5-1.5SQMM M4	
F1.5-5VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	0.5-1.5SQMM M5	
F1.5-6VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	0.5-1.5SQMM M6	
F2.5-3VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	1.5-2.5SQMM M3	
F2.5-4VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	1.5-2.5SQMM M4	
F2.5-5VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	1.5-2.5SQMM M5	
F2.5-6VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	1.5-2.5SQMM M6	
F6-4VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	4-6SQMM M4	
F6-5VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	4-6SQMM M5	
F6-6VDC-H	Vinyl-Insulated Fork Terminal, Double Crimp	4-6SQMM M6	
P1.5VDC-H	Vinyl-Insulated Pin Connector, Double Crimp	0.5-1.5SQMM Pin	
P2.5VDC-H	Vinyl-Insulated Pin Connector, Double Crimp	1.5-2.5SQMM Pin	
P6VDC-H	Vinyl-Insulated Pin Connector, Double Crimp	4-6SQMM Pin	
B1.5VDC-H	Vinyl-Insulated Flat Blade Terminal, Double Crimp	0.5-1.5SQMM Flat Blade	
B2.5VDC-H	Vinyl-Insulated Flat Blade Terminal, Double Crimp	1.5-2.5SQMM Flat Blade	
B6-VDC-H	Vinyl-Insulated Flat Blade Terminal, Double Crimp	4-6SQMM Flat Blade	

MBD1.5-4NDC-H	Nylon-Insulated Male Bullet Disconnect, Double Crimp	0.5-1.5SQMM Male Bullet	ERG9003
MBD2.5-4NDC-H	Nylon-Insulated Male Bullet Disconnect, Double Crimp	1.5-2.5SQMM Male Bullet	
FIRD1.5-39NDC-H	Nylon-Insulated Female Bullet Disconnect, Double Crimp	0.5-1.5SQMM Female Bullet	
FIRD2.5-39NDC-H	Nylon-Insulated Female Bullet Disconnect, Double Crimp	1.5-2.5SQMM Female Bullet	
MD1.5-638NDC-H	Nylon-Insulated Male Disconnect, Double Crimp	0.5-1.5SQMM Male Tab	
MD2.5-638NDC-H	Nylon-Insulated Male Disconnect, Double Crimp	1.5-2.5SQMM Male Tab	
MD6-638NDC-H	Nylon-Insulated Male Disconnect, Double Crimp	4-6SQMM Male Tab	
FIMD1.5-638NDC-H	Fully Nylon-Insulated Male Disconnect, Double Crimp	0.5-1.5SQMM Male Tab	
FIMD2.5-638NDC-H	Fully Nylon-Insulated Male Disconnect, Double Crimp	1.5-2.5SQMM Male Tab	
FIMD6-638NDC-H	Fully Nylon-Insulated Male Disconnect, Double Crimp	4-6SQMM Male Tab	
BS1.5VSC-H	Vinyl-Insulated Butt Splice	0.5-1.5SQMM Splice	
BS2.5VSC-H	Vinyl-Insulated Butt Splice	1.5-2.5SQMM Splice	
BS6VSC-H	Vinyl-Insulated Butt Splice	4-6SQMM Splice	
R1.5-3VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	0.5-1.5SQMM M3	ERG9002
R1.5-4VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	0.5-1.5SQMM M4	
R1.5-5VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	0.5-1.5SQMM M5	
R1.5-6VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	0.5-1.5SQMM M6	
R1.5-8VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	0.5-1.5SQMM M8	
R1.5-10VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	0.5-1.5SQMM M10	
R2.5-3VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	1.5-2.5SQMM M3	
R2.5-4VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	1.5-2.5SQMM M4	
R2.5-5VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	1.5-2.5SQMM M5	
R2.5-6VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	1.5-2.5SQMM M6	
R2.5-8VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	1.5-2.5SQMM M8	
R2.5-10VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	1.5-2.5SQMM M10	
R2.5-12VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	1.5-2.5SQMM M12	
R6-4VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	4-6SQMM M4	
R6-5VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	4-6SQMM M5	
R6-6VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	4-6SQMM M6	
R6-8VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	4-6SQMM M8	
R6-10VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	4-6SQMM M10	
R6-12VSC-H	Vinyl-Insulated Ring Terminal, Single Crimp	4-6SQMM M12	
F1.5-3VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	0.5-1.5SQMM M3	
F1.5-4VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	0.5-1.5SQMM M4	
F1.5-5VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	0.5-1.5SQMM M5	
F1.5-6VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	0.5-1.5SQMM M6	
F2.5-3VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	1.5-2.5SQMM M3	
F2.5-4VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	1.5-2.5SQMM M4	
F2.5-5VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	1.5-2.5SQMM M5	
F2.5-6VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	1.5-2.5SQMM M6	
F6-4VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	4-6SQMM M4	
F6-5VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	4-6SQMM M5	

F6-6VSC-H	Vinyl-Insulated Fork Terminal, Single Crimp	4-6SQMM M6	
P1.5-23VSC-H	Vinyl-Insulated Pin Connector, Single Crimp	0.5-1.5SQMM Pin	
P2.5-23VSC-H	Vinyl-Insulated Pin Connector, Single Crimp	1.5-2.5SQMM Pin	
P6-27VSC-H	Vinyl-Insulated Pin Connector, Single Crimp	4-6SQMM Pin	
LB1.5-3VSC-H	Vinyl-Insulated Lipped Blade Terminal, Single Crimp	0.5-1.5SQMM Lipped Blade	
LB1.5-5VSC-H	Vinyl-Insulated Lipped Blade Terminal, Single Crimp	0.5-1.5SQMM Lipped Blade	
LB2.5-3VSC-H	Vinyl-Insulated Lipped Blade Terminal, Single Crimp	1.5-2.5SQMM Lipped Blade	
LB2.5-5VSC-H	Vinyl-Insulated Lipped Blade Terminal, Single Crimp	1.5-2.5SQMM Lipped Blade	
LB6-5VSC-H	Vinyl-Insulated Lipped Blade Terminal, Single Crimp	4-6SQMM Lipped Blade	
B1.5-3VSC-H	Vinyl-Insulated Flat Blade Terminal, Single Crimp	0.5-1.5SQMM Flat Blade	
B2.5-24VSC-H	Vinyl-Insulated Flat Blade Terminal, Single Crimp	1.5-2.5SQMM Flat Blade	
B6-4VSC-H	Vinyl-Insulated Flat Blade Terminal, Single Crimp	4-6SQMM Flat Blade	

All Parts below meet requirements of IEC60352-2 & IEC61210

<b>Cat. No.</b>	<b>Description</b>	<b>Wire size &amp; tab size</b>	<b>Tooling</b>
FD1.5-638NDC-H	Nylon-Insulated Female Disconnect, Double Crimp	0.5-1.5SQMM 0.8x6.35mm	ERG9003
FD2.5-638NDC-H	Nylon-Insulated Female Disconnect, Double Crimp	1.5-2.5SQMM 0.8x6.35mm	
FD6-638NDC-H	Nylon-Insulated Female Disconnect, Double Crimp	4-6SQMM 0.8x6.35mm	
PBD1.5-648NDC-H	Nylon-Insulated Piggyback, Double Crimp	0.5-1.5SQMM 0.8x6.35mm	
PBD2.5-648NDC-H	Nylon-Insulated Piggyback, Double Crimp	1.5-2.5SQMM 0.8x6.35mm	
FIFD1.5-638NDC-H	Fully Nylon-Insulated Disconnect, Double Crimp	0.5-1.5SQMM 0.8x6.35mm	
FIFD2.5-638NDC-H	Fully Nylon-Insulated Disconnect, Double Crimp	1.5-2.5SQMM 0.8x6.35mm	
FIFD6-638NDC-H	Fully Nylon-Insulated Disconnect, Double Crimp	4-6SQMM 0.8x6.35mm	