

THIS POLE ONLY INSTALLED ON 3 POLE SWITCHES

FRONT COVER ASSEMBLY, LINE SHIELD, NAME PLATE AND INSULATING BARRIER REMOVED FOR CLARITY



ACCEPTS 3 OF 3 OR 1.5 INCH LONG SHACKLE PADLOCKS IN THE OFF POSITION
Ø .375 MAX.



VIEWING WINDOW LOCATION (WHERE APPLICABLE)





DETAIL A
SCALE 1:1

THIS POLE ONLY INSTALLED ON 3 POLE SWITCHES



FRONT COVER ASSEMBLY, LINE SHIELD, NAME PLATE AND INSULATING BARRIER REMOVED FOR CLARITY
NON-FUSED VERSION SHOWN

SKU	AMP	VIEWING WINDOW	HD/GD	POLES	VOLTS	A	B	C	D	H	J	K
THF3225A1,THF3225A1Z	400A	NO	HD	2	240V	14.9 379	14.1 358	49.0 1245	22.4 569	10.6 269	3.1 79	32.5 826
THF3225A1CN,THF3225A1CNZ										-	-	-
THF3325A1,THF3325A1Z				3					21.2 539	10.6 269	3.1 79	32.5 826
THF4325A1,THF4325A1Z										-	-	-
THF4325A1CN,THF4325A1CNZ					600V		15.8 401	53.7 1364	26.3 668	15.3 389	3.1 79	32.5 826
THF3365A1,THF3365A1Z										-	-	-
THF4365A1CN,THF4365A1CNZ										15.3 389	3.1 79	32.5 826
THN3365A1,THN3365A1Z							21.7 551	49.0 1245	21.6 549	-	-	-
THF3226A1,THF3226A1Z	600A			2	240V	14.1 358	17.1 434	53.7 1364	26.3 668	15.0 381	3.1 79	32.3 821
THF3226A1CN,THF3226A1CNZ										-	-	-
THF3326A1,THF3326A1Z				3						15.0 381	3.1 79	32.3 821
THF4326A1,THF4326A1Z										-	-	-
THF4326A1CN,THF4326A1CNZ					600V		14.1 358			15.0 381	3.1 79	32.3 821
THF3366A1,THF3366A1Z										-	-	-
THF4366A1CN,THF4366A1CNZ										15.0 381	3.1 79	32.3 821
THN3366A1,THN3366A1Z							20.8 528	49.0 1245	21.6 549	-	-	-
THF3225A1VW	400A	YES		2	240V	14.9 379	14.1 358	49.0 1245	22.4 569	10.6 269	3.1 79	32.5 826
THF3225A1CNVW										-	-	-
THF3325A1VW				3					21.2 539	10.6 269	3.1 79	32.5 826
THF4325A1VW										-	-	-
THF4325A1CNVW					600V		15.8 401	53.7 1364	26.3 668	15.3 389	3.1 79	32.5 826
THF3365A1VW										-	-	-
THF4365A1CNVW										15.3 389	3.1 79	32.5 826
THN3365A1VW							21.7 551	49.0 1245	21.6 549	-	-	-
THF3226A1VW	600A			2	240V	14.1 358	17.1 434	53.7 1364	26.3 668	15.0 381	3.1 79	32.3 821
THF3226A1CNVW										-	-	-
THF3326A1VW				3						15.0 381	3.1 79	32.3 821
THF4326A1VW										-	-	-
THF4326A1CNVW					600V		14.1 358			15.0 381	3.1 79	32.3 821
THF3366A1VW										-	-	-
THF4366A1CNVW										15.0 381	3.1 79	32.3 821
THN3366A1VW							20.8 528	49.0 1245	21.6 549	-	-	-



MOUNTING BRACKET DIMENSION

ABB

OUTLINE DRAWING-HEAVY DUTY SAFETY SWITCH
400 & 600A, NEMA 1 WITH & W/O VW

THIRD ANGLE	SHEET#	DWG NO.	DATE	REV
	1 of 1	1SQC920065D0201	Apr-2026	F