

PRODUCT SPECIFICATION

OZD1LS61HF

Horizon 230v AC 25M IP20 Recess

Catalogue Number **OZD1LS61HF**
GID **7TCA091070R0097**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Mains / Slave Operation**
Mounting Method/Form **Ceiling Surface**
Housing Material **Aluminium/Plastic**
Colour **White/Silver**
Dimensions (LxWxD) **364 x 167 x 82 mm**
Temperature Range **0 to 40°C**
Weight **1.1 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
Battery **Mains / Central Battery**
Monitoring Equipment **None**
Lamp **2 x 2W LED**
Emergency Light Output (Lumens) **Not Applicable**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 6350 / 73**
Degree of Protection **IP40**

Type of Legend **Single or Double Sided (Order separate)**
Exit Sign Viewing/Recognition Distance (m) **25**
Nominal Voltage **220-240v AC/DC 0-60Hz**
Power Consumption **6.8 VA / 3.1 Watts**
Current **Nominal: 29.6mA (mA) Inrush: 27A**

Accessories

XEN20HS Single Sided Down ISO7010 Legend
XEN30HS Single Sided Left ISO7010 Legend
XEN60HS Single Sided Right ISO7010 Legend
XEN50HS Single Sided Up ISO7010 Legend
XB01HS Single Sided Arabic English Legend
XLF802HS Fire Extinguisher Legend
XLF803HS Hose Reel Legend

XEN22HD Double Sided Down+Down ISO7010 Legend
XEN36HD Double Sided Left+Right ISO7010 Legend
XEN55HD Double Sided Up+Up ISO7010 Legend



Exit sign
OZD1LS61HF + XEN20HS

