


Dimension drawings

Automatic transfer switches

UL: 260U

IEC: 315E, 400E



OX_260_400			
No. of poles	2	3	4
A	65/2.56	65/2.56	65/2.56
A1	277/10.91	277/10.91	277/10.91
A2	160/6.30	225/8.86	290/11.42
B	325/12.80	390/15.35	455/17.91

Note: B dimension, recommended to leave 2cm/1" free space on the left side (for removing the mechanism)