

Item	Qty	Description of products and services	Price per unit	Amount
------	-----	--------------------------------------	----------------	--------

		<p><b>Indoor Siren 24 V, red, EN 54, Part 3</b></p> <p>The CS200 indoor siren is approved for fire alarm control panels in accordance with EN54 and VdS. It has a high sound level and low current consumption. It is possible to choose between 32 modes using DIP switches. A diode is integrated into the siren for the cable monitoring function in ABB fire alarm control panels.</p> <p>Voltage range 9 - 28 V DC Current consumption 6 - 44 mA / 19 mA for DIN mode Volume 107 dB(A) / 102 dB(A) for DIN mode Connection terminals 0.28 mm<sup>2</sup> - 2.5 mm<sup>2</sup> solid Modes 32 Degree of protection IP21C Temperature range -10 °C to +55 °C Housing color Red Material ABS (V0) Height 63 mm Diameter 63 mm Weight 0.2 kg VdS number G209123 CPD number 0832-CPD-1654 Approval in acc. with EN54-3</p> <p>Manufacturer: EATON Distributor: ABB STOTZ-KONTAKT</p> <p><b>Type: CS200</b></p> <p>Material:..... Labor:.....</p>	Carry:	
--	--	--	--------	--

		CS200_AT_EN_V2-0 9AKK107680A9373 Rev. A	Carry:	
--	--	--	--------	--

**CS200**

**CS200**