

Stanilite®

Platinum exit LED edgelit surface mount Nexus®



Catalogue no.	Description
Nexus products	
SGPLSNRFLEDP	Platinum exit LED edgelit surface mount Nexus RF pictograph
Accessories	
PLSLEDCLKIT	Cantilever mounting kit
PLSLEDWMKIT	Wall mounting kit
Spare parts	
03-01308P	Battery LiFePO4 3.2V 1.5Ah

Range

Platinum range

Product group

Exit LED edgelit



Features

- High emergency classification
- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, wireless
- RF frequency range 920 - 925 MHz
- Architecturally pleasing slim line design
- One-box solution, overall light weight and snap n' clip mechanism allows for quick and easy installation
- Surface mounted - suitable for ceilings where a recessed fitting is not feasible
- Includes all pictograph diffuser options
- Wall and cantilever mounting kit options available



Dimensions			
	Length	Width	Height (incl. bracket)
	375.5mm	79mm	220mm

Weight	
Model	Weight
Nexus RF	2.1kg

Construction	
Part	Construction
Visible housing	White powder coated zinc steel
Diffuser	Moulded acrylic
Non-visible housing	Plastic

Light source		
Model	Light source	
Nexus RF	Multiple LED 0.7W	

Power consumption		
Model	Power consumption	
Nexus RF	2.4W	

Note: Preliminary results

Photometrics			
Model	Class		Classification
Nexus RF	C0		D3.2
	C90		E2

Note: Preliminary results

Note:
 - Complies to IEC60598.2.22 and AS2293