

PRODUCT-DETAILS

11100353

DECO LED20/DALI



General Information

Extended Product Type	11100353
Product ID	7TCA305025R0028
EAN	8713812777542
Catalog Description	DECO LED20/DALI
Long Description	Self-contained 22 watt, maintained surface mount led luminaire, DALI, including control module, series Decolux

Technical

Function	Escape route lighting
Rated Voltage (U _r)	220 ... 230 V
Input Voltage Type	AC
Power Supply Type	Peripheral (Individual Battery)
Number of Poles	3
Number of Lamps	2
Number of Lighting Heads	1
Functional Testing	4000 K Safety Module for Monitoring (Central Fedded System)

Capability

Wiring Configuration	Continuous circuit/emergency circuit Suitable for through wiring
Illuminance	Standby Mode 207 lm
Ballast Type	Current Controlled
Connection Type	Screw
Lamp Type	LED not exchangeable
Light Distribution Type	Diffuser Lens Optic Panel
Mounting Type	Wall surface mounted / ceiling surface mounting
Cover Material	Plastic, Opal
Housing Material	Plastic
Housing Color	White
Battery Chemical Composition	Nickel-Metal Hydride
Battery Type	Industrial
Battery Weight	200 g
Number of Batteries	1

Environmental

Ambient Temperature	IEC62722-2-1 0 ... 30 °C
Degree of Protection	IP65
Protection Class	Grounded (Class I)

Dimensions

Product Net Width	340 mm
Product Net Height	101 mm
Product Net Depth / Length	340 mm
Product Net Weight	2.250 kg

Ordering

Package Level 1 Units	box 1 piece
Package Level 1 Gross Weight	2.500 kg

Installation

Instructions and Manuals	9AKK107992A6821
Instructions and Manuals (Part 2)	9AKK107046A3206

Popular Downloads

Classifications

ETIM 8	EC001957 - Emergency luminaire
ETIM 9	EC001957 - Emergency luminaire
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	940540844

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting

