

General Electric roll-in replacement breaker availability

Medium voltage

Original Breaker Type	KV	MVA	New kA	AMPS	AMVAC	ADVAC
AM-13.8-250/500, 1200A	15	500	25	1200	*	*
AM-13.8-250/500, 2000A	15	500	25	2000	*	*
AM-13.8-250/500/750, 1200A	15	750	40	1200	*	*
AM-13.8-250/500/750, 2000A	15	750	40	2000	*	*
AM-13.8-750-5H, 1200A	15	750	40	1200	*	*
AM-13.8-750-5H, 2000A	15	750	40	2000	*	*
AM-13.8-750T, 1200A	15	750	40	1200	*	*
AM-13.8-750T, 2000A	15	750	40	2000	*	*
AM-15-250/500, 1200A	15	500	25	1200	*	
AM-15-250/500, 2000A	15	500	25	2000	*	
AM-4.16-150, 1200A	5	150	31.5	1200	*	
AM-4.16-150, 2000A	5	150	31.5	2000	*	
AM-4.16-250H, 1200A	5	250	40	1200	*	
AM-4.16-250H, 2000A	5	250	40	2000	*	
AM-4.16-350, 3000A	5	350	50	3000	*	
AM-5-150, 1200A	5	150	31.5	1200	*	
AM-7.2-500, 1200A	7	500	40	1200	*	*
AM-7.2-500, 2000A	7	500	40	2000	*	*
AM-7.5-250, 1200A	7	250	31.5	1200	*	
AM-7.5-250, 2000A	7	250	31.5	2000	*	

* Available, ** Contact factory, (Blank) Not available

Low voltage

Original Type	Frame	Direct replacement		Cradle in cradle	
		MO	EO	MO	EO
AK-#-25	600			*	*
AK-#-50	1600			*	*
AK-#A-25	600			*	*
AK-#A-50	1600			*	*
AK-#A-75	3200			*	*
AKR-#A-30	800	*	*	*	*
AKR-#A-50	1600			*	*
AKR-#A-75	3200			*	*
AKT-#A-50	2000			*	*
AK-#-15	225	*	*		

* Available, ** Contact factory, (Blank) Not available