

Item	Qty	Description of products and services	Price per unit	Amount
------	-----	--------------------------------------	----------------	--------

2

2

		<p><b>IP Switch Master, 5 Port, MDRC</b></p> <p>Layer 2 Ethernet switch with 5 RJ 45 ports (1 Gigabit-Port) for DIN rail mounting. Can be extended to 10 ports through lateral coupling with the IP Switch Slave (ISS/S).</p> <p>Features:</p> <ul style="list-style-type: none"> <li>- arbitrarily cascadable by using front ports</li> <li>- 4096 MAC addresses storable</li> <li>- autosensing</li> <li>- autopartitioning</li> <li>- auto-negotiation</li> <li>- semi and full duplex operation</li> <li>- MDI/MDIx (autocrossing)</li> <li>- store and forward principle</li> </ul> <p>Power supply                      90 – 240 V AC, 50 – 60 Hz (integrated power supply)</p> <p>Inputs/Outputs                      5 x RJ 45 ports (4 x 10/100 Mbit/s, 1 x 10/100/1000 Mbit/s)</p> <p>Bitrate                                      10/100/1000 Mbit/s</p> <p>Safety class                              II, DIN EN 61 140</p> <p>Protection class                      IP 20, DIN EN 60 529</p> <p>Colour                                      similar RAL 7035</p> <p>Mounting                                      DIN rail 35 mm, DIN EN 60 715</p> <p>Width                                        6 modules à 18 mm</p> <p>Manufacturer                              ABB STOTZ-KONTAKT</p> <p><b>Type</b>                                        <b>ISM/S 5.1</b></p> <p>Material.....                              Labour.....</p>	Carry:	
--	--	---	--------	--

		<p>ISMS_51_AT_EN_V2-0 2CDC 502 059 D0201</p>	Carry:	
--	--	--	--------	--

ISM/S 5.1

ISM/S 5.1