

PRODUCT SPECIFICATION

SR2-SE230-BC1

Serenga 2 230v AC Escape Route 4-12 m IP54 Surface

Catalogue Number **SR2-SE230-BC1**
GID **7TCA091130R0417**
Warranty **4 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Mains / Slave Operation**
Mounting Method/Form **Ceiling Surface**
Housing Material **Aluminium/Plastic**
Colour **White**
Dimensions (LxWxD) **150 x 150 x 35 mm**
Temperature Range **0 to 40°C**
Weight **0.745 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
Battery **Mains / Central Battery**
Monitoring Equipment **None**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **203**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 5600 / 70**
Degree of Protection **IP54**

Type of Legend **Not Applicable**
Exit Sign Viewing/Recognition Distance (m) **Not Applicable**
Nominal Voltage **220-240v AC 50/60Hz**
Power Consumption **5.5 VA / 5 Watts**
Current **Nominal: 24mA (mA)**

Accessories

- SR2-LENS1** Lens A Escape route 2-4M Ceiling mount
- SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount
- SR2-LENS3** Lens C Escape route 8-12M Ceiling mount
- SR2-LENS4** Lens D Open Area 2-4M Ceiling mount
- SR2-LENS5** Lens E Open Area 4-8M Ceiling mount
- SR2-LENS6** Lens E Open Area 8-12M Ceiling mount
- SR2-LENS7** Lens G Escape route 2-4M Wall mount

