

PRODUCT SPECIFICATION

CTEGR3LS1-S32

Guideway Self-Contained 32M IP40 Naveo Recess

Catalogue Number **CTEGR3LS1-S32**
 GID **7TCA091180R0255**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Recessed**
 Housing Material **Aluminium/Plastic**
 Colour **Silver**
 Dimensions (LxWxD) **335 x 84 x 184 mm**
 Temperature Range **5 to 35°C**
 Weight **1.5 Kg**

Emergency Duration (Hours) **3**
 Battery **NiMH**
 Monitoring Equipment **Naveo®Pro**
 Lamp **1 x 4W LED**
 Emergency Light Output (Lumens) **Not Applicable**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 5000 / 80**
 Degree of Protection **IP40**

Type of Legend **Single or Double Sided**
 Exit Sign Viewing/Recognition Distance (m) **32**
 Nominal Voltage **220-240v AC 50Hz**
 Power Consumption **7.1 VA / 6.5 Watts**
 Current **Nominal: 31mA (mA)**

Accessories

- XEN2EG32** Down ISO7010 Legend Single Sided
- XEN3EG32** Left ISO7010 Legend Single Sided
- XEN6EG32** Right ISO7010 Legend Single Sided
- XEN5EG32** Up ISO7010 Legend Single Sided
- XBN1EG32** Arabic English Legend Single Sided
- XEN0G22** Blank Legend Single Sided

EG-T4EG Cover Discs (2x semi-circular, 2x rectangular) for Slave

- EG-TKIT50** Suspension Kit Pendant 50mm
- EG-TKIT100** Suspension Kit Pendant 100mm
- EG-WKIT150** Wire Suspension Kit 150mm

- XEN602EG32** Down ISO7010 Legend Flag Mount
- XEN603EG32** Left ISO7010 Legend Flag Mount
- XEN606EG32** Right ISO7010 Legend Flag Mount
- XEN605EG32** Up ISO7010 Legend Flag Mount



Exit Sign Suspended
CTEGR3LS1-S32 + EG-WKIT150



Exit Sign Recessed
CTEGR3LS1-S32

