

Joslyn Model Number	ABB Model Number	ABB Detailed Description
1260-21	OVRHT3B501201P	OVRHT3B, 1-phase, 2-wire + ground, 50 kA, 120V
1261-21	OVRHT3B502401P	OVRHT3B, 1-phase, 2-wire + ground, 50 kA, 240V
	OVRHT3B502771P	OVRHT3B, 1-phase, 2-wire + ground, 50 kA, 277V
1263-21	OVRHT3B504801P	OVRHT3B, 1-phase, 2-wire + ground, 50 kA, 480V
1265-21	OVRHT3B501202S	OVRHT3B, 2-phase, 3-wire + ground, 50 kA, 120/240V
	OVRHT3B502402S	OVRHT3B, 2-phase, 3-wire + ground, 50 kA, 240/480
1452-21	OVRHT3B502403H	OVRHT3B, 3-phase High-Leg , 4-wire + ground, 50 kA, 120/240V
1455-21	OVRHT3B501203Y	OVRHT3B, 3-phase Wye , 4-wire + ground, 50 kA, 120/208V
	OVRHT3B502203Y	OVRHT3B, 3-phase Wye , 4-wire + ground, 50 kA, 220/380V
1457-21	OVRHT3B502303Y	OVRHT3B, 3-phase Wye , 4-wire + ground, 50 kA, 230/400V
	OVRHT3B502403Y	OVRHT3B, 3-phase Wye , 4-wire + ground, 50 kA, 240/415V
1456-21	OVRHT3B502773Y	OVRHT3B, 3-phase Wye , 4-wire + ground, 50 kA, 277/480V
	OVRHT3B503473Y	OVRHT3B, 3-phase Wye , 4-wire + ground, 50 kA, 347/600V
1455-21-D	OVRHT3B502403D	OVRHT3B, 3-phase Delta , 3-wire + ground, 50 kA, 240V
	OVRHT3B503803D	OVRHT3B, 3-phase Delta , 3-wire + ground, 50 kA, 380V
1459-21	OVRHT3B504003D	OVRHT3B, 3-phase Delta , 3-wire + ground, 50 kA, 400V
1456-21-D	OVRHT3B504803D	OVRHT3B, 3-phase Delta , 3-wire + ground, 50 kA, 480V
	OVRHT3B506003D	OVRHT3B, 3-phase Delta , 3-wire + ground, 50 kA, 600V
1261-21-TNC	OVRHT3B502301PI	OVRHT3B, 1-phase, 2-wire + ground (for TNC earthing systems), 50 kA, 230V
1261-21-TNS	OVRHT3B502301PJ	OVRHT3B, 1-phase, 2-wire + ground (for TNS earthing systems), 50 kA, 230V
1261-21-IT	OVRHT3B502301PK	OVRHT3B, 1-phase, 2-wire + ground (for IT earthing systems), 50 kA, 230V
1261-21-TT	OVRHT3B502301PL	OVRHT3B, 1-phase, 2-wire + ground (for TT earthing systems), 50 kA, 230V
	OVRHT3C501201P	OVRHT3C, 1-phase, 2-wire + ground, 50 kA, 120V
	OVRHT3C502401P	OVRHT3C, 1-phase, 2-wire + ground, 50 kA, 240V
	OVRHT3C502771P	OVRHT3C, 1-phase, 2-wire + ground, 50 kA, 277V
	OVRHT3C504801P	OVRHT3C, 1-phase, 2-wire + ground, 50 kA, 480V
	OVRHT3C501202S	OVRHT3C, 2-phase, 3-wire + ground, 50 kA, 120/240V
	OVRHT3C502402S	OVRHT3C, 2-phase, 3-wire + ground, 50 kA, 240/480
	OVRHT3C502403H	OVRHT3C, 3-phase High-Leg , 4-wire + ground, 50 kA, 120/240V

OVRHT3C501203Y OVRHT3C, 3-phase Wye , 4-wire + ground, 50 kA, 120/208V
 OVRHT3C502203Y OVRHT3C, 3-phase Wye , 4-wire + ground, 50 kA, 220/380V
 OVRHT3C502303Y OVRHT3C, 3-phase Wye , 4-wire + ground, 50 kA, 230/400V
 OVRHT3C502403Y OVRHT3C, 3-phase Wye , 4-wire + ground, 50 kA, 240/415V
 OVRHT3C502773Y OVRHT3C, 3-phase Wye , 4-wire + ground, 50 kA, 277/480V
 OVRHT3C503473Y OVRHT3C, 3-phase Wye , 4-wire + ground, 50 kA, 347/600V

OVRHT3C502403D OVRHT3C, 3-phase Delta , 3-wire + ground, 50 kA, 240V
 OVRHT3C503803D OVRHT3C, 3-phase Delta , 3-wire + ground, 50 kA, 380V
 OVRHT3C504003D OVRHT3C, 3-phase Delta , 3-wire + ground, 50 kA, 400V
 OVRHT3C504803D OVRHT3C, 3-phase Delta , 3-wire + ground, 50 kA, 480V
 OVRHT3C506003D OVRHT3C, 3-phase Delta , 3-wire + ground, 50 kA, 600V

OVRHT3C502301PI OVRHT3C, 1-phase, 2-wire + ground (for TNC earthing systems), 50 kA, 230V
 OVRHT3C502301PJ OVRHT3C, 1-phase, 2-wire + ground (for TNS earthing systems), 50 kA, 230V
 OVRHT3C502301PK OVRHT3C, 1-phase, 2-wire + ground (for IT earthing systems), 50 kA, 230V
 OVRHT3C502301PL OVRHT3C, 1-phase, 2-wire + ground (for TT earthing systems), 50 kA, 230V

LDP20-120-1	OVRHLD20-120-1	OVR HW, LD, 20kA, 120V, L-N, L-G (1 LED)
LDP20-120-1B	OVRHLD20-120-16	OVR HW, LD, 20kA, 120V, L-N, L-G (1 LED), Mounting bracket
LDP20-120-2	OVRHLD20-120-2	OVR HW, LD, 20kA, 120V, L1-N, L2-N (2 LEDs)
LDP20-120-2B	OVRHLD20-120-26	OVR HW, LD, 20kA, 120V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP20-120-3	OVRHLD20-120-3	OVR HW, LD, 20kA, 120V, L1-G, L2-G (2 LEDs)
LDP20-120-3B	OVRHLD20-120-36	OVR HW, LD, 20kA, 120V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP20-120-4	OVRHLD20-120-4	OVR HW, LD, 20kA, 120V, L1-G, N-G (1 LED)
LDP20-120-4B	OVRHLD20-120-46	OVR HW, LD, 20kA, 120V, L1-G, N-G (1 LED), Mounting bracket
LDP20-120-5	OVRHLD20-120-5	OVR HW, LD, 20kA, 120V, L-N, L-G (2 LEDs)
LDP20-120-5B	OVRHLD20-120-56	OVR HW, LD, 20kA, 120V, L-N, L-G (2 LEDs), Mounting bracket
LDP20-120-6	OVRHLD20-120-6	OVR HW, LD, 20kA, 120V, L-N (1 LED)
LDP20-120-6B	OVRHLD20-120-66	OVR HW, LD, 20kA, 120V, L-N (1 LED), Mounting bracket
LDP20-120-7	OVRHLD20-120-7	OVR HW, LD, 20kA, 120V, L-G (1 LED)
LDP20-120-7B	OVRHLD20-120-76	OVR HW, LD, 20kA, 120V, L-G (1 LED), Mounting bracket
LDP20-120-8	OVRHLD20-120-8	OVR HW, LD, 20kA, 120V, N-G (0 LED)
LDP20-120-8B	OVRHLD20-120-86	OVR HW, LD, 20kA, 120V, N-G (0 LED), Mounting bracket
LDP20-120-9	OVRHLD20-120-9	OVR HW, LD, 20kA, 120V, L1-L2 (1 LED)
LDP20-120-9B	OVRHLD20-120-96	OVR HW, LD, 20kA, 120V, L1-L2 (1 LED), Mounting bracket

LDP20-127-1	OVRHLD20-127-1	OVR HW, LD, 20kA, 127V, L-N, L-G (1 LED)
LDP20-127-1B	OVRHLD20-127-16	OVR HW, LD, 20kA, 127V, L-N, L-G (1 LED), Mounting bracket
LDP20-127-2	OVRHLD20-127-2	OVR HW, LD, 20kA, 127V, L1-N, L2-N (2 LEDs)
LDP20-127-2B	OVRHLD20-127-26	OVR HW, LD, 20kA, 127V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP20-127-3	OVRHLD20-127-3	OVR HW, LD, 20kA, 127V, L1-G, L2-G (2 LEDs)
LDP20-127-3B	OVRHLD20-127-36	OVR HW, LD, 20kA, 127V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP20-127-4	OVRHLD20-127-4	OVR HW, LD, 20kA, 127V, L1-G, N-G (1 LED)
LDP20-127-4B	OVRHLD20-127-46	OVR HW, LD, 20kA, 127V, L1-G, N-G (1 LED), Mounting bracket
LDP20-127-5	OVRHLD20-127-5	OVR HW, LD, 20kA, 127V, L-N, L-G (2 LEDs)
LDP20-127-5B	OVRHLD20-127-56	OVR HW, LD, 20kA, 127V, L-N, L-G (2 LEDs), Mounting bracket
LDP20-127-6	OVRHLD20-127-6	OVR HW, LD, 20kA, 127V, L-N (1 LED)
LDP20-127-6B	OVRHLD20-127-66	OVR HW, LD, 20kA, 127V, L-N (1 LED), Mounting bracket
LDP20-127-7	OVRHLD20-127-7	OVR HW, LD, 20kA, 127V, L-G (1 LED)
LDP20-127-7B	OVRHLD20-127-76	OVR HW, LD, 20kA, 127V, L-G (1 LED), Mounting bracket
LDP20-127-8	OVRHLD20-127-8	OVR HW, LD, 20kA, 127V, N-G (0 LED)
LDP20-127-8B	OVRHLD20-127-86	OVR HW, LD, 20kA, 127V, N-G (0 LED), Mounting bracket
LDP20-127-9	OVRHLD20-127-9	OVR HW, LD, 20kA, 127V, L1-L2 (1 LED)
LDP20-127-9B	OVRHLD20-127-96	OVR HW, LD, 20kA, 127V, L1-L2 (1 LED), Mounting bracket

LDP20-230-1	OVRHLD20-230-1	OVR HW, LD, 20kA, 230V, L-N, L-G (1 LED)
LDP20-230-1B	OVRHLD20-230-16	OVR HW, LD, 20kA, 230V, L-N, L-G (1 LED), Mounting bracket
LDP20-230-2	OVRHLD20-230-2	OVR HW, LD, 20kA, 230V, L1-N, L2-N (2 LEDs)
LDP20-230-2B	OVRHLD20-230-26	OVR HW, LD, 20kA, 230V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP20-230-3	OVRHLD20-230-3	OVR HW, LD, 20kA, 230V, L1-G, L2-G (2 LEDs)
LDP20-230-3B	OVRHLD20-230-36	OVR HW, LD, 20kA, 230V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP20-230-4	OVRHLD20-230-4	OVR HW, LD, 20kA, 230V, L1-G, N-G (1 LED)
LDP20-230-4B	OVRHLD20-230-46	OVR HW, LD, 20kA, 230V, L1-G, N-G (1 LED), Mounting bracket
LDP20-230-5	OVRHLD20-230-5	OVR HW, LD, 20kA, 230V, L-N, L-G (2 LEDs)
LDP20-230-5B	OVRHLD20-230-56	OVR HW, LD, 20kA, 230V, L-N, L-G (2 LEDs), Mounting bracket
LDP20-230-6	OVRHLD20-230-6	OVR HW, LD, 20kA, 230V, L-N (1 LED)
LDP20-230-6B	OVRHLD20-230-66	OVR HW, LD, 20kA, 230V, L-N (1 LED), Mounting bracket
LDP20-230-7	OVRHLD20-230-7	OVR HW, LD, 20kA, 230V, L-G (1 LED)
LDP20-230-7B	OVRHLD20-230-76	OVR HW, LD, 20kA, 230V, L-G (1 LED), Mounting bracket
LDP20-230-8	OVRHLD20-230-8	OVR HW, LD, 20kA, 230V, N-G (0 LED)
LDP20-230-8B	OVRHLD20-230-86	OVR HW, LD, 20kA, 230V, N-G (0 LED), Mounting bracket
LDP20-230-9	OVRHLD20-230-9	OVR HW, LD, 20kA, 230V, L1-L2 (1 LED)
LDP20-230-9B	OVRHLD20-230-96	OVR HW, LD, 20kA, 230V, L1-L2 (1 LED), Mounting bracket

LDP20-277-1	OVRHLD20-277-1	OVR HW, LD, 20kA, 277V, L-N, L-G (1 LED)
LDP20-277-1B	OVRHLD20-277-16	OVR HW, LD, 20kA, 277V, L-N, L-G (1 LED), Mounting bracket
LDP20-277-2	OVRHLD20-277-2	OVR HW, LD, 20kA, 277V, L1-N, L2-N (2 LEDs)
LDP20-277-2B	OVRHLD20-277-26	OVR HW, LD, 20kA, 277V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP20-277-3	OVRHLD20-277-3	OVR HW, LD, 20kA, 277V, L1-G, L2-G (2 LEDs)
LDP20-277-3B	OVRHLD20-277-36	OVR HW, LD, 20kA, 277V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP20-277-4	OVRHLD20-277-4	OVR HW, LD, 20kA, 277V, L1-G, N-G (1 LED)
LDP20-277-4B	OVRHLD20-277-46	OVR HW, LD, 20kA, 277V, L1-G, N-G (1 LED), Mounting bracket
LDP20-277-5	OVRHLD20-277-5	OVR HW, LD, 20kA, 277V, L-N, L-G (2 LEDs)
LDP20-277-5B	OVRHLD20-277-56	OVR HW, LD, 20kA, 277V, L-N, L-G (2 LEDs), Mounting bracket
LDP20-277-6	OVRHLD20-277-6	OVR HW, LD, 20kA, 277V, L-N (1 LED)
LDP20-277-6B	OVRHLD20-277-66	OVR HW, LD, 20kA, 277V, L-N (1 LED), Mounting bracket
LDP20-277-7	OVRHLD20-277-7	OVR HW, LD, 20kA, 277V, L-G (1 LED)
LDP20-277-7B	OVRHLD20-277-76	OVR HW, LD, 20kA, 277V, L-G (1 LED), Mounting bracket
LDP20-277-8	OVRHLD20-277-8	OVR HW, LD, 20kA, 277V, N-G (0 LED)
LDP20-277-8B	OVRHLD20-277-86	OVR HW, LD, 20kA, 277V, N-G (0 LED), Mounting bracket
LDP20-277-9	OVRHLD20-277-9	OVR HW, LD, 20kA, 277V, L1-L2 (1 LED)
LDP20-277-9B	OVRHLD20-277-96	OVR HW, LD, 20kA, 277V, L1-L2 (1 LED), Mounting bracket

LDP25-120-1	OVRHLD25-120-1	OVR HW, LD, 25kA, 120V, L-N, L-G (1 LED)
LDP25-120-1B	OVRHLD25-120-16	OVR HW, LD, 25kA, 120V, L-N, L-G (1 LED), Mounting bracket
LDP25-120-2	OVRHLD25-120-2	OVR HW, LD, 25kA, 120V, L1-N, L2-N (2 LEDs)
LDP25-120-2B	OVRHLD25-120-26	OVR HW, LD, 25kA, 120V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP25-120-3	OVRHLD25-120-3	OVR HW, LD, 25kA, 120V, L1-G, L2-G (2 LEDs)
LDP25-120-3B	OVRHLD25-120-36	OVR HW, LD, 25kA, 120V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP25-120-4	OVRHLD25-120-4	OVR HW, LD, 25kA, 120V, L1-G, N-G (1 LED)
LDP25-120-4B	OVRHLD25-120-46	OVR HW, LD, 25kA, 120V, L1-G, N-G (1 LED), Mounting bracket
LDP25-120-5	OVRHLD25-120-5	OVR HW, LD, 25kA, 120V, L-N, L-G (2 LEDs)
LDP25-120-5B	OVRHLD25-120-56	OVR HW, LD, 25kA, 120V, L-N, L-G (2 LEDs), Mounting bracket
LDP25-120-6	OVRHLD25-120-6	OVR HW, LD, 25kA, 120V, L-N (1 LED)
LDP25-120-6B	OVRHLD25-120-66	OVR HW, LD, 25kA, 120V, L-N (1 LED), Mounting bracket
LDP25-120-7	OVRHLD25-120-7	OVR HW, LD, 25kA, 120V, L-G (1 LED)
LDP25-120-7B	OVRHLD25-120-76	OVR HW, LD, 25kA, 120V, L-G (1 LED), Mounting bracket
LDP25-120-8	OVRHLD25-120-8	OVR HW, LD, 25kA, 120V, N-G (0 LED)
LDP25-120-8B	OVRHLD25-120-86	OVR HW, LD, 25kA, 120V, N-G (0 LED), Mounting bracket
LDP25-120-9	OVRHLD25-120-9	OVR HW, LD, 25kA, 120V, L1-L2 (1 LED)
LDP25-120-9B	OVRHLD25-120-96	OVR HW, LD, 25kA, 120V, L1-L2 (1 LED), Mounting bracket

LDP25-127-1	OVRHLD25-127-1	OVR HW, LD, 25kA, 127V, L-N, L-G (1 LED)
LDP25-127-1B	OVRHLD25-127-16	OVR HW, LD, 25kA, 127V, L-N, L-G (1 LED), Mounting bracket
LDP25-127-2	OVRHLD25-127-2	OVR HW, LD, 25kA, 127V, L1-N, L2-N (2 LEDs)
LDP25-127-2B	OVRHLD25-127-26	OVR HW, LD, 25kA, 127V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP25-127-3	OVRHLD25-127-3	OVR HW, LD, 25kA, 127V, L1-G, L2-G (2 LEDs)
LDP25-127-3B	OVRHLD25-127-36	OVR HW, LD, 25kA, 127V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP25-127-4	OVRHLD25-127-4	OVR HW, LD, 25kA, 127V, L1-G, N-G (1 LED)
LDP25-127-4B	OVRHLD25-127-46	OVR HW, LD, 25kA, 127V, L1-G, N-G (1 LED), Mounting bracket
LDP25-127-5	OVRHLD25-127-5	OVR HW, LD, 25kA, 127V, L-N, L-G (2 LEDs)
LDP25-127-5B	OVRHLD25-127-56	OVR HW, LD, 25kA, 127V, L-N, L-G (2 LEDs), Mounting bracket
LDP25-127-6	OVRHLD25-127-6	OVR HW, LD, 25kA, 127V, L-N (1 LED)
LDP25-127-6B	OVRHLD25-127-66	OVR HW, LD, 25kA, 127V, L-N (1 LED), Mounting bracket
LDP25-127-7	OVRHLD25-127-7	OVR HW, LD, 25kA, 127V, L-G (1 LED)
LDP25-127-7B	OVRHLD25-127-76	OVR HW, LD, 25kA, 127V, L-G (1 LED), Mounting bracket
LDP25-127-8	OVRHLD25-127-8	OVR HW, LD, 25kA, 127V, N-G (0 LED)
LDP25-127-8B	OVRHLD25-127-86	OVR HW, LD, 25kA, 127V, N-G (0 LED), Mounting bracket
LDP25-127-9	OVRHLD25-127-9	OVR HW, LD, 25kA, 127V, L1-L2 (1 LED)
LDP25-127-9B	OVRHLD25-127-96	OVR HW, LD, 25kA, 127V, L1-L2 (1 LED), Mounting bracket

LDP25-230-1	OVRHLD25-230-1	OVR HW, LD, 25kA, 230V, L-N, L-G (1 LED)
LDP25-230-1B	OVRHLD25-230-16	OVR HW, LD, 25kA, 230V, L-N, L-G (1 LED), Mounting bracket
LDP25-230-2	OVRHLD25-230-2	OVR HW, LD, 25kA, 230V, L1-N, L2-N (2 LEDs)
LDP25-230-2B	OVRHLD25-230-26	OVR HW, LD, 25kA, 230V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP25-230-3	OVRHLD25-230-3	OVR HW, LD, 25kA, 230V, L1-G, L2-G (2 LEDs)
LDP25-230-3B	OVRHLD25-230-36	OVR HW, LD, 25kA, 230V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP25-230-4	OVRHLD25-230-4	OVR HW, LD, 25kA, 230V, L1-G, N-G (1 LED)
LDP25-230-4B	OVRHLD25-230-46	OVR HW, LD, 25kA, 230V, L1-G, N-G (1 LED), Mounting bracket
LDP25-230-5	OVRHLD25-230-5	OVR HW, LD, 25kA, 230V, L-N, L-G (2 LEDs)
LDP25-230-5B	OVRHLD25-230-56	OVR HW, LD, 25kA, 230V, L-N, L-G (2 LEDs), Mounting bracket
LDP25-230-6	OVRHLD25-230-6	OVR HW, LD, 25kA, 230V, L-N (1 LED)
LDP25-230-6B	OVRHLD25-230-66	OVR HW, LD, 25kA, 230V, L-N (1 LED), Mounting bracket
LDP25-230-7	OVRHLD25-230-7	OVR HW, LD, 25kA, 230V, L-G (1 LED)
LDP25-230-7B	OVRHLD25-230-76	OVR HW, LD, 25kA, 230V, L-G (1 LED), Mounting bracket
LDP25-230-8	OVRHLD25-230-8	OVR HW, LD, 25kA, 230V, N-G (0 LED)
LDP25-230-8B	OVRHLD25-230-86	OVR HW, LD, 25kA, 230V, N-G (0 LED), Mounting bracket
LDP25-230-9	OVRHLD25-230-9	OVR HW, LD, 25kA, 230V, L1-L2 (1 LED)
LDP25-230-9B	OVRHLD25-230-96	OVR HW, LD, 25kA, 230V, L1-L2 (1 LED), Mounting bracket

LDP25-277-1	OVRHLD25-277-1	OVR HW, LD, 25kA, 277V, L-N, L-G (1 LED)
LDP25-277-1B	OVRHLD25-277-16	OVR HW, LD, 25kA, 277V, L-N, L-G (1 LED), Mounting bracket
LDP25-277-2	OVRHLD25-277-2	OVR HW, LD, 25kA, 277V, L1-N, L2-N (2 LEDs)
LDP25-277-2B	OVRHLD25-277-26	OVR HW, LD, 25kA, 277V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP25-277-3	OVRHLD25-277-3	OVR HW, LD, 25kA, 277V, L1-G, L2-G (2 LEDs)
LDP25-277-3B	OVRHLD25-277-36	OVR HW, LD, 25kA, 277V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP25-277-4	OVRHLD25-277-4	OVR HW, LD, 25kA, 277V, L1-G, N-G (1 LED)
LDP25-277-4B	OVRHLD25-277-46	OVR HW, LD, 25kA, 277V, L1-G, N-G (1 LED), Mounting bracket
LDP25-277-5	OVRHLD25-277-5	OVR HW, LD, 25kA, 277V, L-N, L-G (2 LEDs)
LDP25-277-5B	OVRHLD25-277-56	OVR HW, LD, 25kA, 277V, L-N, L-G (2 LEDs), Mounting bracket
LDP25-277-6	OVRHLD25-277-6	OVR HW, LD, 25kA, 277V, L-N (1 LED)
LDP25-277-6B	OVRHLD25-277-66	OVR HW, LD, 25kA, 277V, L-N (1 LED), Mounting bracket
LDP25-277-7	OVRHLD25-277-7	OVR HW, LD, 25kA, 277V, L-G (1 LED)
LDP25-277-7B	OVRHLD25-277-76	OVR HW, LD, 25kA, 277V, L-G (1 LED), Mounting bracket
LDP25-277-8	OVRHLD25-277-8	OVR HW, LD, 25kA, 277V, N-G (0 LED)
LDP25-277-8B	OVRHLD25-277-86	OVR HW, LD, 25kA, 277V, N-G (0 LED), Mounting bracket
LDP25-277-9	OVRHLD25-277-9	OVR HW, LD, 25kA, 277V, L1-L2 (1 LED)
LDP25-277-9B	OVRHLD25-277-96	OVR HW, LD, 25kA, 277V, L1-L2 (1 LED), Mounting bracket

LDP30-120-1	OVRHLD30-120-1	OVR HW, LD, 30kA, 120V, L-N, L-G (1 LED)
LDP30-120-1B	OVRHLD30-120-16	OVR HW, LD, 30kA, 120V, L-N, L-G (1 LED), Mounting bracket
LDP30-120-2	OVRHLD30-120-2	OVR HW, LD, 30kA, 120V, L1-N, L2-N (2 LEDs)
LDP30-120-2B	OVRHLD30-120-26	OVR HW, LD, 30kA, 120V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP30-120-3	OVRHLD30-120-3	OVR HW, LD, 30kA, 120V, L1-G, L2-G (2 LEDs)
LDP30-120-3B	OVRHLD30-120-36	OVR HW, LD, 30kA, 120V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP30-120-4	OVRHLD30-120-4	OVR HW, LD, 30kA, 120V, L1-G, N-G (1 LED)
LDP30-120-4B	OVRHLD30-120-46	OVR HW, LD, 30kA, 120V, L1-G, N-G (1 LED), Mounting bracket
LDP30-120-5	OVRHLD30-120-5	OVR HW, LD, 30kA, 120V, L-N, L-G (2 LEDs)
LDP30-120-5B	OVRHLD30-120-56	OVR HW, LD, 30kA, 120V, L-N, L-G (2 LEDs), Mounting bracket
LDP30-120-6	OVRHLD30-120-6	OVR HW, LD, 30kA, 120V, L-N (1 LED)
LDP30-120-6B	OVRHLD30-120-66	OVR HW, LD, 30kA, 120V, L-N (1 LED), Mounting bracket
LDP30-120-7	OVRHLD30-120-7	OVR HW, LD, 30kA, 120V, L-G (1 LED)
LDP30-120-7B	OVRHLD30-120-76	OVR HW, LD, 30kA, 120V, L-G (1 LED), Mounting bracket
LDP30-120-8	OVRHLD30-120-8	OVR HW, LD, 30kA, 120V, N-G (0 LED)
LDP30-120-8B	OVRHLD30-120-86	OVR HW, LD, 30kA, 120V, N-G (0 LED), Mounting bracket
LDP30-120.9	OVRHLD30-120-9	OVR HW, LD, 30kA, 120V, L1-L2 (1 LED)
LDP30-120.9B	OVRHLD30-120-96	OVR HW, LD, 30kA, 120V, L1-L2 (1 LED), Mounting bracket


LDP30-127-1	OVRHLD30-127-1	OVR HW, LD, 30kA, 127V, L-N, L-G (1 LED)
LDP30-127-1B	OVRHLD30-127-16	OVR HW, LD, 30kA, 127V, L-N, L-G (1 LED), Mounting bracket
LDP30-127-2	OVRHLD30-127-2	OVR HW, LD, 30kA, 127V, L1-N, L2-N (2 LEDs)
LDP30-127-2B	OVRHLD30-127-26	OVR HW, LD, 30kA, 127V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP30-127-3	OVRHLD30-127-3	OVR HW, LD, 30kA, 127V, L1-G, L2-G (2 LEDs)
LDP30-127-3B	OVRHLD30-127-36	OVR HW, LD, 30kA, 127V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP30-127-4	OVRHLD30-127-4	OVR HW, LD, 30kA, 127V, L1-G, N-G (1 LED)
LDP30-127-4B	OVRHLD30-127-46	OVR HW, LD, 30kA, 127V, L1-G, N-G (1 LED), Mounting bracket
LDP30-127-5	OVRHLD30-127-5	OVR HW, LD, 30kA, 127V, L-N, L-G (2 LEDs)
LDP30-127-5B	OVRHLD30-127-56	OVR HW, LD, 30kA, 127V, L-N, L-G (2 LEDs), Mounting bracket
LDP30-127-6	OVRHLD30-127-6	OVR HW, LD, 30kA, 127V, L-N (1 LED)
LDP30-127-6B	OVRHLD30-127-66	OVR HW, LD, 30kA, 127V, L-N (1 LED), Mounting bracket
LDP30-127-7	OVRHLD30-127-7	OVR HW, LD, 30kA, 127V, L-G (1 LED)
LDP30-127-7B	OVRHLD30-127-76	OVR HW, LD, 30kA, 127V, L-G (1 LED), Mounting bracket
LDP30-127-8	OVRHLD30-127-8	OVR HW, LD, 30kA, 127V, N-G (0 LED)
LDP30-127-8B	OVRHLD30-127-86	OVR HW, LD, 30kA, 127V, N-G (0 LED), Mounting bracket
LDP30-127-9	OVRHLD30-127-9	OVR HW, LD, 30kA, 127V, L1-L2 (1 LED)
LDP30-127-9B	OVRHLD30-127-96	OVR HW, LD, 30kA, 127V, L1-L2 (1 LED), Mounting bracket

LDP30-230-1	OVRHLD30-230-1	OVR HW, LD, 30kA, 230V, L-N, L-G (1 LED)
LDP30-230-1B	OVRHLD30-230-16	OVR HW, LD, 30kA, 230V, L-N, L-G (1 LED), Mounting bracket
LDP30-230-2	OVRHLD30-230-2	OVR HW, LD, 30kA, 230V, L1-N, L2-N (2 LEDs)
LDP30-230-2B	OVRHLD30-230-26	OVR HW, LD, 30kA, 230V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP30-230-3	OVRHLD30-230-3	OVR HW, LD, 30kA, 230V, L1-G, L2-G (2 LEDs)
LDP30-230-3B	OVRHLD30-230-36	OVR HW, LD, 30kA, 230V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP30-230-4	OVRHLD30-230-4	OVR HW, LD, 30kA, 230V, L1-G, N-G (1 LED)
LDP30-B	OVRHLD30-230-46	OVR HW, LD, 30kA, 230V, L1-G, N-G (1 LED), Mounting bracket
LDP30-230-5	OVRHLD30-230-5	OVR HW, LD, 30kA, 230V, L-N, L-G (2 LEDs)
LDP30-230-5B	OVRHLD30-230-56	OVR HW, LD, 30kA, 230V, L-N, L-G (2 LEDs), Mounting bracket
LDP30-230-6	OVRHLD30-230-6	OVR HW, LD, 30kA, 230V, L-N (1 LED)
LDP30-230-6B	OVRHLD30-230-66	OVR HW, LD, 30kA, 230V, L-N (1 LED), Mounting bracket
LDP30-230-7	OVRHLD30-230-7	OVR HW, LD, 30kA, 230V, L-G (1 LED)
LDP30-230-7B	OVRHLD30-230-76	OVR HW, LD, 30kA, 230V, L-G (1 LED), Mounting bracket
LDP30-230-8	OVRHLD30-230-8	OVR HW, LD, 30kA, 230V, N-G (0 LED)
LDP30-230-8B	OVRHLD30-230-86	OVR HW, LD, 30kA, 230V, N-G (0 LED), Mounting bracket
LDP30-230-9	OVRHLD30-230-9	OVR HW, LD, 30kA, 230V, L1-L2 (1 LED)
LDP30-230-9B	OVRHLD30-230-96	OVR HW, LD, 30kA, 230V, L1-L2 (1 LED), Mounting bracket


LDP30-277-1	OVRHLD30-277-1	OVR HW, LD, 30kA, 277V, L-N, L-G (1 LED)
LDP30-277-1B	OVRHLD30-277-16	OVR HW, LD, 30kA, 277V, L-N, L-G (1 LED), Mounting bracket
LDP30-277-2	OVRHLD30-277-2	OVR HW, LD, 30kA, 277V, L1-N, L2-N (2 LEDs)
LDP30-277-2B	OVRHLD30-277-26	OVR HW, LD, 30kA, 277V, L1-N, L2-N (2 LEDs), Mounting bracket
LDP30-277-3	OVRHLD30-277-3	OVR HW, LD, 30kA, 277V, L1-G, L2-G (2 LEDs)
LDP30-277-3B	OVRHLD30-277-36	OVR HW, LD, 30kA, 277V, L1-G, L2-G (2 LEDs), Mounting bracket
LDP30-277-4	OVRHLD30-277-4	OVR HW, LD, 30kA, 277V, L1-G, N-G (1 LED)
LDP30-277-4B	OVRHLD30-277-46	OVR HW, LD, 30kA, 277V, L1-G, N-G (1 LED), Mounting bracket
LDP30-277-5	OVRHLD30-277-5	OVR HW, LD, 30kA, 277V, L-N, L-G (2 LEDs)
LDP30-277-5B	OVRHLD30-277-56	OVR HW, LD, 30kA, 277V, L-N, L-G (2 LEDs), Mounting bracket
LDP30-277-6	OVRHLD30-277-6	OVR HW, LD, 30kA, 277V, L-N (1 LED)
LDP30-277-6B	OVRHLD30-277-66	OVR HW, LD, 30kA, 277V, L-N (1 LED), Mounting bracket
LDP30-277-7	OVRHLD30-277-7	OVR HW, LD, 30kA, 277V, L-G (1 LED)
LDP30-277-7B	OVRHLD30-277-76	OVR HW, LD, 30kA, 277V, L-G (1 LED), Mounting bracket
LDP30-277-8	OVRHLD30-277-8	OVR HW, LD, 30kA, 277V, N-G (0 LED)
LDP30-277-8B	OVRHLD30-277-86	OVR HW, LD, 30kA, 277V, N-G (0 LED), Mounting bracket
LDP30-277-9	OVRHLD30-277-9	OVR HW, LD, 30kA, 277V, L1-L2 (1 LED)
LDP30-277-9B	OVRHLD30-277-96	OVR HW, LD, 30kA, 277V, L1-L2 (1 LED), Mounting bracket

	OVRHTE251201P	OVR HW, TE, 25kA, 120V, 1-phase, 2 wire + Ground
	OVRHTE251201P5	OVR HW, TE, 25kA, 120V, 1-phase, 2 wire + Ground, Dry contacts
	OVRHTE252401P	OVR HW, TE, 25kA, 240V, 1-phase, 2 wire + Ground
	OVRHTE252401P5	OVR HW, TE, 25kA, 240V, 1-phase, 2 wire + Ground, Dry contacts
XN25120/240-2G	OVRHTE251202S	OVR HW, TE, 25kA, 120/240V, 2-phase, 3 wire + Ground
XN25120/240-2GFC	OVRHTE251202S5	OVR HW, TE, 25kA, 120/240V, 2-phase, 3 wire + Ground, Dry contacts
XN25120/208-3GY	OVRHTE251203Y	OVR HW, TE, 25kA, 120/208 Wye, 3-phase, 4 wire + Ground
XN25120/208-3GYFC	OVRHTE251203Y5	OVR HW, TE, 25kA, 120/208 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN25220/380-3GY	OVRHTE252203Y	OVR HW, TE, 25kA, 220/380 Wye, 3-phase, 4 wire + Ground
XN25220/380-3GYFC	OVRHTE252203Y5	OVR HW, TE, 25kA, 220/380 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE252403Y	OVR HW, TE, 25kA, 240/415 Wye, 3-phase, 4 wire + Ground
	OVRHTE252403Y5	OVR HW, TE, 25kA, 240/415 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN25277/480-3GY	OVRHTE252773Y	OVR HW, TE, 25kA, 277/480 Wye, 3-phase, 4 wire + Ground
XN25277/480-3GYFC	OVRHTE252773Y5	OVR HW, TE, 25kA, 277/480 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE253473Y	OVR HW, TE, 25kA, 347/600 Wye, 3-phase, 4 wire + Ground
	OVRHTE253473Y5	OVR HW, TE, 25kA, 347/600 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN25240-3DG	OVRHTE252403D	OVR HW, TE, 25kA, 240V Delta, 3-phase, 3 wire + Ground
XN25240-3DGFC	OVRHTE252403D5	OVR HW, TE, 25kA, 240V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN25380-3DG	OVRHTE253803D	OVR HW, TE, 25kA, 380V Delta, 3-phase, 3 wire + Ground


XN25380-3DGFC	OVRHTE253803D5	OVR HW, TE, 25kA, 380V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN25480-3DG	OVRHTE254803D	OVR HW, TE, 25kA, 480V Delta, 3-phase, 3 wire + Ground
XN25480-3DGFC	OVRHTE254803D5	OVR HW, TE, 25kA, 480V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN25120/240-3GHD	OVRHTE251203H	OVR HW, TE, 25kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
XN25120/240-3GHDFC	OVRHTE251203H5	OVR HW, TE, 25kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Dry contacts




XN50120/240-2G	OVRHTE501201P	OVR HW, TE, 50kA, 120V, 1-phase, 2 wire + Ground
XN50120/240-2GFC	OVRHTE501201P5	OVR HW, TE, 50kA, 120V, 1-phase, 2 wire + Ground, Dry contacts
XN50120/208-3GY	OVRHTE502401P	OVR HW, TE, 50kA, 240V, 1-phase, 2 wire + Ground
XN50120/208-3GYFC	OVRHTE502401P5	OVR HW, TE, 50kA, 240V, 1-phase, 2 wire + Ground, Dry contacts
XN50220/380-3GY	OVRHTE501202S	OVR HW, TE, 50kA, 120/240V, 2-phase, 3 wire + Ground
XN50220/380-3GYFC	OVRHTE501202S5	OVR HW, TE, 50kA, 120/240V, 2-phase, 3 wire + Ground, Dry contacts



XN50277/480-3GY	OVRHTE501203Y	OVR HW, TE, 50kA, 120/208 Wye, 3-phase, 4 wire + Ground
XN50277/480-3GYFC	OVRHTE501203Y5	OVR HW, TE, 50kA, 120/208 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE502203Y	OVR HW, TE, 50kA, 220/380 Wye, 3-phase, 4 wire + Ground
	OVRHTE502203Y5	OVR HW, TE, 50kA, 220/380 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE502403Y	OVR HW, TE, 50kA, 240/415 Wye, 3-phase, 4 wire + Ground
	OVRHTE502403Y5	OVR HW, TE, 50kA, 240/415 Wye, 3-phase, 4 wire + Ground, Dry contacts



XN50277/480-3GY	OVRHTE502773Y	OVR HW, TE, 50kA, 277/480 Wye, 3-phase, 4 wire + Ground
XN50277/480-3GYFC	OVRHTE502773Y5	OVR HW, TE, 50kA, 277/480 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE503473Y	OVR HW, TE, 50kA, 347/600 Wye, 3-phase, 4 wire + Ground
	OVRHTE503473Y5	OVR HW, TE, 50kA, 347/600 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN50240-3DG	OVRHTE502403D	OVR HW, TE, 50kA, 240V Delta, 3-phase, 3 wire + Ground
XN50240-3DGFC	OVRHTE502403D5	OVR HW, TE, 50kA, 240V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN50380-3DG	OVRHTE503803D	OVR HW, TE, 50kA, 380V Delta, 3-phase, 3 wire + Ground
XN50380-3DGFC	OVRHTE503803D5	OVR HW, TE, 50kA, 380V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN50480-3DG	OVRHTE504803D	OVR HW, TE, 50kA, 480V Delta, 3-phase, 3 wire + Ground
XN50480-3DGFC	OVRHTE504803D5	OVR HW, TE, 50kA, 480V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN50120/240-3GHD	OVRHTE501203H	OVR HW, TE, 50kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
XN50120/240-3GHDFC	OVRHTE501203H5	OVR HW, TE, 50kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Dry contacts



XN80120/240-2G	OVRHTE801201P	OVR HW, TE, 80kA, 120V, 1-phase, 2 wire + Ground
XN80120/240-2GFC	OVRHTE801201P5	OVR HW, TE, 80kA, 120V, 1-phase, 2 wire + Ground, Dry contacts
XN80120/208-3GY	OVRHTE802401P	OVR HW, TE, 80kA, 240V, 1-phase, 2 wire + Ground
	OVRHTE802401P5	OVR HW, TE, 80kA, 240V, 1-phase, 2 wire + Ground, Dry contacts
	OVRHTE801202S	OVR HW, TE, 80kA, 120/240V, 2-phase, 3 wire + Ground
	OVRHTE801202S5	OVR HW, TE, 80kA, 120/240V, 2-phase, 3 wire + Ground, Dry contacts
	OVRHTE801203Y	OVR HW, TE, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground

XN80120/208-3GYFC	OVRHTE801203Y5	OVR HW, TE, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN80220/380-3GY	OVRHTE802203Y	OVR HW, TE, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground
XN80220/380-3GYFC	OVRHTE802203Y5	OVR HW, TE, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE802403Y	OVR HW, TE, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground
	OVRHTE802403Y5	OVR HW, TE, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN80277/480-3GY	OVRHTE802773Y	OVR HW, TE, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground
XN80277/480-3GYFC	OVRHTE802773Y5	OVR HW, TE, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE803473Y	OVR HW, TE, 80kA, 347/600 Wye, 3-phase, 4 wire + Ground
	OVRHTE803473Y5	OVR HW, TE, 80kA, 347/600 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN80240-3DG	OVRHTE802403D	OVR HW, TE, 80kA, 240V Delta, 3-phase, 3 wire + Ground
XN80240-3DGFC	OVRHTE802403D5	OVR HW, TE, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN80380-3DG	OVRHTE803803D	OVR HW, TE, 80kA, 380V Delta, 3-phase, 3 wire + Ground
XN80380-3DGFC	OVRHTE803803D5	OVR HW, TE, 80kA, 380V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN80480-3DG	OVRHTE804803D	OVR HW, TE, 80kA, 480V Delta, 3-phase, 3 wire + Ground
XN80480-3DGFC	OVRHTE804803D5	OVR HW, TE, 80kA, 480V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN80120/240-3GHD	OVRHTE801203H	OVR HW, TE, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
XN80120/240-3GHDFC	OVRHTE801203H5	OVR HW, TE, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Dry contacts

	OVRHTE1001201P	OVR HW, TE, 100kA, 120V, 1-phase, 2 wire + Ground
	OVRHTE1001201P5	OVR HW, TE, 100kA, 120V, 1-phase, 2 wire + Ground, Dry contacts
	OVRHTE1002401P	OVR HW, TE, 100kA, 240V, 1-phase, 2 wire + Ground
	OVRHTE1002401P5	OVR HW, TE, 100kA, 240V, 1-phase, 2 wire + Ground, Dry contacts
XN100120/240-2G	OVRHTE1001202S	OVR HW, TE, 100kA, 120/240V, 2-phase, 3 wire + Ground
XN100120/240-2GFC	OVRHTE1001202S5	OVR HW, TE, 100kA, 120/240V, 2-phase, 3 wire + Ground, Dry contacts
XN100120/208-3GY	OVRHTE1001203Y	OVR HW, TE, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground
XN100120/208-3GYFC	OVRHTE1001203Y5	OVR HW, TE, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN100220/380-3GY	OVRHTE1002203Y	OVR HW, TE, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground
XN100220/380-3GYFC	OVRHTE1002203Y5	OVR HW, TE, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE1002403Y	OVR HW, TE, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground
	OVRHTE1002403Y5	OVR HW, TE, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN100277/480-3GY	OVRHTE1002773Y	OVR HW, TE, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground
XN100277/480-3GYFC	OVRHTE1002773Y5	OVR HW, TE, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground, Dry contacts
	OVRHTE1003473Y	OVR HW, TE, 100kA, 347/600 Wye, 3-phase, 4 wire + Ground
	OVRHTE1003473Y5	OVR HW, TE, 100kA, 347/600 Wye, 3-phase, 4 wire + Ground, Dry contacts
XN100240-3DG	OVRHTE1002403D	OVR HW, TE, 100kA, 240V Delta, 3-phase, 3 wire + Ground
XN100240-3DGFC	OVRHTE1002403D5	OVR HW, TE, 100kA, 240V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN100380-3DG	OVRHTE1003803D	OVR HW, TE, 100kA, 380V Delta, 3-phase, 3 wire + Ground
XN100380-3DGFC	OVRHTE1003803D5	OVR HW, TE, 100kA, 380V Delta, 3-phase, 3 wire + Ground, Dry contacts

XN100480-3DG	OVRHTE1004803D	OVR HW, TE, 100kA, 480V Delta, 3-phase, 3 wire + Ground
XN100480-3DGFC	OVRHTE1004803D5	OVR HW, TE, 100kA, 480V Delta, 3-phase, 3 wire + Ground, Dry contacts
XN100120/240-3GHD	OVRHTE1001203H	OVR HW, TE, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
XN100120/240-3GHDFC	OVRHTE1001203H5	OVR HW, TE, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Dry contacts
OVRHTEMCK	OVRHTEMCK	OVR HW, TE, Metallic conduit installation kit
OVRHTEMPCK	OVRHTEMPCK	OVR HW, TE, Flexible plastic conduit installation kit
<hr/>		
1260-49	OVRHS3U401201P	OVR HW, S3, 40kA, 120V, 1-phase, 2 wire + Ground
1260-49-R	OVRHS3U401201P5	OVR HW, S3, 40kA, 120V, 1-phase, 2 wire + Ground, Dry contacts
1261-49	OVRHS3U402401P	OVR HW, S3, 40kA, 240V, 1-phase, 2 wire + Ground
1261-49-R	OVRHS3U402401P5	OVR HW, S3, 40kA, 240V, 1-phase, 2 wire + Ground ,Dry Contacts
	OVRHS3U402401PP	OVR HW, S3, 40kA, 240V, 1-phase, 2 wire + Ground ,Dry Contacts, Mounting bracket
	OVRHS3U401203H	OVR HW, S3, 40kA, 120/240V, 3-phase High Leg Delta, 4 wire + Ground
	OVRHS3U401203H5	OVR HW, S3, 40kA, 120/240V, 3-phase High Leg Delta, 4 wire + Ground ,Dry Contacts
	OVRHS3U402401PL	OVR HW, S3, 40kA, 240V, 1-phase, 2 wire + Ground, TT grounding system
1265-49	OVRHS3U401202S	OVR HW, S3, 40kA, 120/240V, 2-phase, 3 wire + Ground
1265-49-R	OVRHS3U401202S5	OVR HW, S3, 40kA, 120/240V, 2-phase, 3 wire + Ground ,Dry Contacts
	OVRHS3U402403D	OVR HW, S3, 40kA, 240V, 3-phase Delta, 4 wire + Ground
	OVRHS3U402403D5	OVR HW, S3, 40kA, 240V, 3-phase Delta, 4 wire + Ground, Dry Contacts
1456-49-D	OVRHS3U404803D	OVR HW, S3, 40kA, 480V, 3-phase Delta, 3 wire + Ground
	OVRHS3U404803D5	OVR HW, S3, 40kA, 480V, 3-phase Delta, 3 wire + Ground, Dry contacts
	OVRHS3U406003D	OVR HW, S3, 40kA, 600V, 3-phase Delta, 4 wire + Ground
	OVRHS3U406003D5	OVR HW, S3, 40kA, 600V, 3-phase Delta, 4 wire + Ground, Dry contacts
1455-49	OVRHS3U401203Y	OVR HW, S3, 40kA, 120/208V, 3-phase Wye, 4 wire + Ground
1455-49-R	OVRHS3U401203Y5	OVR HW, S3, 40kA, 120/208V, 3-phase Wye, 4 wire + Ground, Dry contacts
1456-49	OVRHS3U402773Y	OVR HW, S3, 40kA, 277/480V, 3-phase, 4 wire + Ground
1456-49-R	OVRHS3U402773Y5	OVR HW, S3, 40kA, 277/480V, 3-phase, 4 wire + Ground, Dry contacts
1457-49	OVRHS3U402303Y	OVR HW, S3, 40kA, 230-400V, 3-phase, 4 wire + Ground
1457-49-R	OVRHS3U402303Y5	OVR HW, S3, 40kA, 230-400V, 3-phase, 4 wire + Ground, Dry contacts
	OVRHS3U402303YP	OVR HW, S3, 40kA, 230-400V, 3-phase, 4 wire + Ground, Dry contacts, Mounting bracket
	OVRHS3U801202SR	OVR HW, S3, 80kA, 120/240V, 2-phase, 3 wire + Ground contains filter
<hr/>		
JSP-FMP	OVRHSPFMP	OVR HW, SP Flush Plate Mount
JSP0601P120	OVRHSP601201P	OVR HW, SP, 60kA, 120V, 1-phase, 2 wire + Ground
JSP0601P120F	OVRHSP601201P3	OVR HW, SP, 60kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP0601P120FM	OVRHSP601201PA	OVR HW, SP, 60kA, 120V, 1-phase, 2 wire + Ground, Filter + Monitor

JSP0601P120M	OVRHSP601201P1	OVR HW, SP, 60kA, 120V, 1-phase, 2 wire + Ground, Monitor
JSP0601P120S	OVRHSP601201P4	OVR HW, SP, 60kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP0601P120FS	OVRHSP601201PC	OVR HW, SP, 60kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP0601P240	OVRHSP602401P	OVR HW, SP, 60kA, 240V, 1-phase, 2 wire + Ground
JSP0601P240F	OVRHSP602401P3	OVR HW, SP, 60kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP0601P240FM	OVRHSP602401PA	OVR HW, SP, 60kA, 240V, 1-phase, 2 wire + Ground, Filter + Monitor
JSP0601P240M	OVRHSP602401P1	OVR HW, SP, 60kA, 240V, 1-phase, 2 wire + Ground, Monitor
JSP0601P240S	OVRHSP602401P4	OVR HW, SP, 60kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP0601P240FS	OVRHSP602401PC	OVR HW, SP, 60kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP0601S240	OVRHSP601202S	OVR HW, SP, 60kA, 120/240V, 2-phase, 3 wire + Ground
JSP0601S240F	OVRHSP601202S3	OVR HW, SP, 60kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP0601S240FM	OVRHSP601202SA	OVR HW, SP, 60kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Monitor
JSP0601S240M	OVRHSP601202S1	OVR HW, SP, 60kA, 120/240V, 2-phase, 3 wire + Ground, Monitor
JSP0601S240S	OVRHSP601202S4	OVR HW, SP, 60kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP0601S240FS	OVRHSP601202SC	OVR HW, SP, 60kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP0603D240	OVRHSP602403D	OVR HW, SP, 60kA, 240V Delta, 3-phase, 3 wire + Ground
JSP0603D240F	OVRHSP602403D3	OVR HW, SP, 60kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP0603D240FM	OVRHSP602403DA	OVR HW, SP, 60kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Monitor
JSP0603D240M	OVRHSP602403D1	OVR HW, SP, 60kA, 240V Delta, 3-phase, 3 wire + Ground, Monitor
JSP0603D240S	OVRHSP602403D4	OVR HW, SP, 60kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP0603D240FS	OVRHSP602403DC	OVR HW, SP, 60kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP0603H240	OVRHSP601203H	OVR HW, SP, 60kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP0603H240F	OVRHSP601203H3	OVR HW, SP, 60kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP0603H240FM	OVRHSP601203HA	OVR HW, SP, 60kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0603H240M	OVRHSP601203H1	OVR HW, SP, 60kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Monitor
JSP0603H240S	OVRHSP601203H4	OVR HW, SP, 60kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0603H240FS	OVRHSP601203HC	OVR HW, SP, 60kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0603Y208	OVRHSP601203Y	OVR HW, SP, 60kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP0603Y208F	OVRHSP601203Y3	OVR HW, SP, 60kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP0603Y208FM	OVRHSP601203YA	OVR HW, SP, 60kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0603Y208M	OVRHSP601203Y1	OVR HW, SP, 60kA, 120/208 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0603Y208S	OVRHSP601203Y4	OVR HW, SP, 60kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0603Y208FS	OVRHSP601203YC	OVR HW, SP, 60kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0603Y380	OVRHSP602203Y	OVR HW, SP, 60kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP0603Y380F	OVRHSP602203Y3	OVR HW, SP, 60kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP0603Y380FM	OVRHSP602203YA	OVR HW, SP, 60kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0603Y380M	OVRHSP602203Y1	OVR HW, SP, 60kA, 220/380 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0603Y380S	OVRHSP602203Y4	OVR HW, SP, 60kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure

JSP0603Y380FS	OVRHSP602203YC	OVR HW, SP, 60kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0603Y415	OVRHSP602403Y	OVR HW, SP, 60kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP0603Y415F	OVRHSP602403Y3	OVR HW, SP, 60kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP0603Y415FM	OVRHSP602403YA	OVR HW, SP, 60kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0603Y415M	OVRHSP602403Y1	OVR HW, SP, 60kA, 240/415 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0603Y415S	OVRHSP602403Y4	OVR HW, SP, 60kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0603Y415FS	OVRHSP602403YC	OVR HW, SP, 60kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0603Y480	OVRHSP602773Y	OVR HW, SP, 60kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP0603Y480F	OVRHSP602773Y3	OVR HW, SP, 60kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP0603Y480FM	OVRHSP602773YA	OVR HW, SP, 60kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0603Y480M	OVRHSP602773Y1	OVR HW, SP, 60kA, 277/480 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0603Y480S	OVRHSP602773Y4	OVR HW, SP, 60kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0603Y480FS	OVRHSP602773YC	OVR HW, SP, 60kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0801P120	OVRHSP801201P	OVR HW, SP, 80kA, 120V, 1-phase, 2 wire + Ground
JSP0801P120F	OVRHSP801201P3	OVR HW, SP, 80kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP0801P120FM	OVRHSP801201PA	OVR HW, SP, 80kA, 120V, 1-phase, 2 wire + Ground, Filter + Monitor
JSP0801P120M	OVRHSP801201P1	OVR HW, SP, 80kA, 120V, 1-phase, 2 wire + Ground, Monitor
JSP0801P120S	OVRHSP801201P4	OVR HW, SP, 80kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP0801P120FS	OVRHSP801201PC	OVR HW, SP, 80kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP0801P240	OVRHSP802401P	OVR HW, SP, 80kA, 240V, 1-phase, 2 wire + Ground
JSP0801P240F	OVRHSP802401P3	OVR HW, SP, 80kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP0801P240FM	OVRHSP802401PA	OVR HW, SP, 80kA, 240V, 1-phase, 2 wire + Ground, Filter + Monitor
JSP0801P240M	OVRHSP802401P1	OVR HW, SP, 80kA, 240V, 1-phase, 2 wire + Ground, Monitor
JSP0801P240S	OVRHSP802401P4	OVR HW, SP, 80kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP0801P240FS	OVRHSP802401PC	OVR HW, SP, 80kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP0801S240	OVRHSP801202S	OVR HW, SP, 80kA, 120/240V, 2-phase, 3 wire + Ground
JSP0801S240F	OVRHSP801202S3	OVR HW, SP, 80kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP0801S240FM	OVRHSP801202SA	OVR HW, SP, 80kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Monitor
JSP0801S240M	OVRHSP801202S1	OVR HW, SP, 80kA, 120/240V, 2-phase, 3 wire + Ground, Monitor
JSP0801S240S	OVRHSP801202S4	OVR HW, SP, 80kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP0801S240FS	OVRHSP801202SC	OVR HW, SP, 80kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP0803D240	OVRHSP802403D	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground
JSP0803D240F	OVRHSP802403D3	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP0803D240FM	OVRHSP802403DA	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Monitor
JSP0803D240M	OVRHSP802403D1	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Monitor
JSP0803D240S	OVRHSP802403D4	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP0803D240FS	OVRHSP802403DC	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure

JSP0803H240	OVRHSP801203H	OVR HW, SP, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP0803H240F	OVRHSP801203H3	OVR HW, SP, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP0803H240FM	OVRHSP801203HA	OVR HW, SP, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0803H240M	OVRHSP801203H1	OVR HW, SP, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Monitor
JSP0803H240S	OVRHSP801203H4	OVR HW, SP, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0803H240FS	OVRHSP801203HC	OVR HW, SP, 80kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0803Y208	OVRHSP801203Y	OVR HW, SP, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP0803Y208F	OVRHSP801203Y3	OVR HW, SP, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP0803Y208FM	OVRHSP801203YA	OVR HW, SP, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0803Y208M	OVRHSP801203Y1	OVR HW, SP, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0803Y208S	OVRHSP801203Y4	OVR HW, SP, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0803Y208FS	OVRHSP801203YC	OVR HW, SP, 80kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0803Y380	OVRHSP802203Y	OVR HW, SP, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP0803Y380F	OVRHSP802203Y3	OVR HW, SP, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP0803Y380FM	OVRHSP802203YA	OVR HW, SP, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0803Y380M	OVRHSP802203Y1	OVR HW, SP, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0803Y380S	OVRHSP802203Y4	OVR HW, SP, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0803Y380FS	OVRHSP802203YC	OVR HW, SP, 80kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0803Y415	OVRHSP802403Y	OVR HW, SP, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP0803Y415F	OVRHSP802403Y3	OVR HW, SP, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP0803Y415FM	OVRHSP802403YA	OVR HW, SP, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0803Y415M	OVRHSP802403Y1	OVR HW, SP, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0803Y415S	OVRHSP802403Y4	OVR HW, SP, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0803Y415FS	OVRHSP802403YC	OVR HW, SP, 80kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP0803Y480	OVRHSP802773Y	OVR HW, SP, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP0803Y480F	OVRHSP802773Y3	OVR HW, SP, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP0803Y480FM	OVRHSP802773YA	OVR HW, SP, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP0803Y480M	OVRHSP802773Y1	OVR HW, SP, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground, Monitor
JSP0803Y480S	OVRHSP802773Y4	OVR HW, SP, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP0803Y480FS	OVRHSP802773YC	OVR HW, SP, 80kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1001P120	OVRHSP1001201P	OVR HW, SP, 100kA, 120V, 1-phase, 2 wire + Ground
JSP1001P120F	OVRHSP1001201P3	OVR HW, SP, 100kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP1001P120FM	OVRHSP1001201PA	OVR HW, SP, 100kA, 120V, 1-phase, 2 wire + Ground, Filter + Monitor
JSP1001P120M	OVRHSP1001201P1	OVR HW, SP, 100kA, 120V, 1-phase, 2 wire + Ground, Monitor
JSP1001P120S	OVRHSP1001201P4	OVR HW, SP, 100kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP1001P120FS	OVRHSP1001201PC	OVR HW, SP, 100kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP1001P240	OVRHSP1002401P	OVR HW, SP, 100kA, 240V, 1-phase, 2 wire + Ground

JSP1001P240F	OVRHSP1002401P3	OVR HW, SP, 100kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP1001P240FM	OVRHSP1002401PA	OVR HW, SP, 100kA, 240V, 1-phase, 2 wire + Ground, Filter + Monitor
JSP1001P240M	OVRHSP1002401P1	OVR HW, SP, 100kA, 240V, 1-phase, 2 wire + Ground, Monitor
JSP1001P240S	OVRHSP1002401P4	OVR HW, SP, 100kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP1001P240FS	OVRHSP1002401PC	OVR HW, SP, 100kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP1001S240	OVRHSP1001202S	OVR HW, SP, 100kA, 120/240V, 2-phase, 3 wire + Ground
JSP1001S240F	OVRHSP1001202S3	OVR HW, SP, 100kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP1001S240FM	OVRHSP1001202SA	OVR HW, SP, 100kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Monitor
JSP1001S240M	OVRHSP1001202S1	OVR HW, SP, 100kA, 120/240V, 2-phase, 3 wire + Ground, Monitor
JSP1001S240S	OVRHSP1001202S4	OVR HW, SP, 100kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1001S240FS	OVRHSP1001202SC	OVR HW, SP, 100kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1003D240	OVRHSP1002403D	OVR HW, SP, 100kA, 240V Delta, 3-phase, 3 wire + Ground
JSP1003D240F	OVRHSP1002403D3	OVR HW, SP, 100kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP1003D240FM	OVRHSP1002403DA	OVR HW, SP, 100kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Monitor
JSP1003D240M	OVRHSP1002403D1	OVR HW, SP, 100kA, 240V Delta, 3-phase, 3 wire + Ground, Monitor
JSP1003D240S	OVRHSP1002403D4	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1003D240FS	OVRHSP1002403DC	OVR HW, SP, 80kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1003H240	OVRHSP1001203H	OVR HW, SP, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP1003H240F	OVRHSP1001203H3	OVR HW, SP, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP1003H240FM	OVRHSP1001203HA	OVR HW, SP, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Monitor
JSP1003H240M	OVRHSP1001203H1	OVR HW, SP, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Monitor
JSP1003H240S	OVRHSP1001203H4	OVR HW, SP, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1003H240FS	OVRHSP1001203HC	OVR HW, SP, 100kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1003Y208	OVRHSP1001203Y	OVR HW, SP, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP1003Y208F	OVRHSP1001203Y3	OVR HW, SP, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP1003Y208FM	OVRHSP1001203YA	OVR HW, SP, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP1003Y208M	OVRHSP1001203Y1	OVR HW, SP, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground, Monitor
JSP1003Y208S	OVRHSP1001203Y4	OVR HW, SP, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1003Y208FS	OVRHSP1001203YC	OVR HW, SP, 100kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1003Y380	OVRHSP1002203Y	OVR HW, SP, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP1003Y380F	OVRHSP1002203Y3	OVR HW, SP, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP1003Y380FM	OVRHSP1002203YA	OVR HW, SP, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP1003Y380M	OVRHSP1002203Y1	OVR HW, SP, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground, Monitor
JSP1003Y380S	OVRHSP1002203Y1	OVR HW, SP, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1003Y380FS	OVRHSP1002203Y1	OVR HW, SP, 100kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1003Y415	OVRHSP1002403Y	OVR HW, SP, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP1003Y415F	OVRHSP1002403Y3	OVR HW, SP, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP1003Y415FM	OVRHSP1002403YA	OVR HW, SP, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Monitor

JSP1003Y415M	OVRHSP1002403Y1	OVR HW, SP, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground, Monitor
JSP1003Y415S	OVRHSP1002403Y4	OVR HW, SP, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1003Y415FS	OVRHSP1002403YC	OVR HW, SP, 100kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1003Y480	OVRHSP1002773Y	OVR HW, SP, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP1003Y480F	OVRHSP1002773Y3	OVR HW, SP, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP1003Y480FM	OVRHSP1002773YA	OVR HW, SP, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Monitor
JSP1003Y480M	OVRHSP1002773Y1	OVR HW, SP, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground, Monitor
JSP1003Y480S	OVRHSP1002773Y4	OVR HW, SP, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1003Y480FS	OVRHSP1002773YC	OVR HW, SP, 100kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1201P120	OVRHSP1201201P	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground
JSP1201P120B	OVRHSP1201201P2	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground, Counter
JSP1201P120F	OVRHSP1201201P3	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP1201P120S	OVRHSP1201201P4	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP1201P120FB	OVRHSP1201201PB	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter
JSP1201P120FS	OVRHSP1201201PC	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP1201P120BS	OVRHSP1201201PD	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP1201P120FBS	OVRHSP1201201PT	OVR HW, SP, 120kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1201P240	OVRHSP1202401P	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground
JSP1201P240B	OVRHSP1202401P2	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground, Counter
JSP1201P240F	OVRHSP1202401P3	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP1201P240S	OVRHSP1202401P4	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP1201P240FB	OVRHSP1202401PB	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter
JSP1201P240FS	OVRHSP1202401PC	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP1201P240BS	OVRHSP1202401PD	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP1201P240FBS	OVRHSP1202401PT	OVR HW, SP, 120kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1201S240	OVRHSP1201202S	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground
JSP1201S240B	OVRHSP1201202S2	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground, Counter
JSP1201S240F	OVRHSP1201202S3	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP1201S240S	OVRHSP1201202S4	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1201S240FB	OVRHSP1201202SB	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter
JSP1201S240FS	OVRHSP1201202SC	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1201S240BS	OVRHSP1201202SD	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1201S240FBS	OVRHSP1201202ST	OVR HW, SP, 120kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203D240	OVRHSP1202403D	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground
JSP1203D240B	OVRHSP1202403D2	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Counter
JSP1203D240F	OVRHSP1202403D3	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP1203D240S	OVRHSP1202403D4	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure

JSP1203D240FB	OVRHSP1202403DB	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1203D240FS	OVRHSP1202403DC	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203D240BS	OVRHSP1202403DD	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203D240FBS	OVRHSP1202403DT	OVR HW, SP, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203H240	OVRHSP1201203H	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP1203H240B	OVRHSP1201203H2	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter
JSP1203H240F	OVRHSP1201203H3	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP1203H240S	OVRHSP1201203H4	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1203H240FB	OVRHSP1201203HB	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter
JSP1203H240FS	OVRHSP1201203HC	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203H240BS	OVRHSP1201203HD	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203H240FBS	OVRHSP1201203HT	OVR HW, SP, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203D380	OVRHSP1203803D	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground
JSP1203D380B	OVRHSP1203803D2	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground, Counter
JSP1203D380F	OVRHSP1203803D3	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground, Filter
JSP1203D380S	OVRHSP1203803D4	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1203D380FB	OVRHSP1203803DB	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1203D380FS	OVRHSP1203803DC	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203D380BS	OVRHSP1203803DD	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203D380FBS	OVRHSP1203803DT	OVR HW, SP, 120kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203D480	OVRHSP1204803D	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground
JSP1203D480B	OVRHSP1204803D2	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Counter
JSP1203D480F	OVRHSP1204803D3	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSP1203D480S	OVRHSP1204803D4	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1203D480FB	OVRHSP1204803DB	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1203D480FS	OVRHSP1204803DC	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203D480BS	OVRHSP1204803DD	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203D480FBS	OVRHSP1204803DT	OVR HW, SP, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203D600	OVRHSP1206003D	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground
JSP1203D600B	OVRHSP1206003D2	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground, Counter
JSP1203D600F	OVRHSP1206003D3	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground, Filter
JSP1203D600S	OVRHSP1206003D4	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1203D600FB	OVRHSP1206003DB	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1203D600FS	OVRHSP1206003DC	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203D600BS	OVRHSP1206003DD	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203D600FBS	OVRHSP1206003DT	OVR HW, SP, 120kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203Y208	OVRHSP1201203Y	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP1203Y208B	OVRHSP1201203Y2	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter

JSP1203Y208F	OVRHSP1201203Y3	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP1203Y208S	OVRHSP1201203Y4	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1203Y208FB	OVRHSP1201203YB	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1203Y208FS	OVRHSP1201203YC	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203Y208BS	OVRHSP1201203YD	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203Y208FBS	OVRHSP1201203YT	OVR HW, SP, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203Y380	OVRHSP1202203Y	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP1203Y380B	OVRHSP1202203Y2	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter
JSP1203Y380F	OVRHSP1202203Y3	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP1203Y380S	OVRHSP1202203Y4	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1203Y380FB	OVRHSP1202203YB	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1203Y380FS	OVRHSP1202203YC	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203Y380BS	OVRHSP1202203YD	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203Y380FBS	OVRHSP1202203YT	OVR HW, SP, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203Y415	OVRHSP1202403Y	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP1203Y415B	OVRHSP1202403Y2	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter
JSP1203Y415F	OVRHSP1202403Y3	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP1203Y415S	OVRHSP1202403Y4	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1203Y415FB	OVRHSP1202403YB	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1203Y415FS	OVRHSP1202403YC	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203Y415BS	OVRHSP1202403YD	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203Y415FBS	OVRHSP1202403YT	OVR HW, SP, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203Y480	OVRHSP1202773Y	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP1203Y480B	OVRHSP1202773Y2	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter
JSP1203Y480F	OVRHSP1202773Y3	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP1203Y480S	OVRHSP1202773Y4	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1203Y480FB	OVRHSP1202773YB	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1203Y480FS	OVRHSP1202773YC	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203Y480BS	OVRHSP1202773YD	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203Y480FBS	OVRHSP1202773YT	OVR HW, SP, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1203Y600	OVRHSP1203473Y	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground
JSP1203Y600B	OVRHSP1203473Y2	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter
JSP1203Y600F	OVRHSP1203473Y3	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter
JSP1203Y600S	OVRHSP1203473Y4	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1203Y600FB	OVRHSP1203473YB	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1203Y600FS	OVRHSP1203473YC	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1203Y600BS	OVRHSP1203473YD	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1203Y600FBS	OVRHSP1203473YT	OVR HW, SP, 120kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure

JSP1601P120	OVRHSP1601201P	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground
JSP1601P120B	OVRHSP1601201P2	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground, Counter
JSP1601P120F	OVRHSP1601201P3	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP1601P120S	OVRHSP1601201P4	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP1601P120FB	OVRHSP1601201PB	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter
JSP1601P120FS	OVRHSP1601201PC	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP1601P120BS	OVRHSP1601201PD	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP1601P120FBS	OVRHSP1601201PT	OVR HW, SP, 160kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1601P240	OVRHSP1602401P	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground
JSP1601P240B	OVRHSP1602401P2	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground, Counter
JSP1601P240F	OVRHSP1602401P3	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP1601P240S	OVRHSP1602401P4	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP1601P240FB	OVRHSP1602401PB	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter
JSP1601P240FS	OVRHSP1602401PC	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP1601P240BS	OVRHSP1602401PD	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP1601P240FBS	OVRHSP1602401PT	OVR HW, SP, 160kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1601S240	OVRHSP1601202S	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground
JSP1601S240B	OVRHSP1601202S2	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground, Counter
JSP1601S240F	OVRHSP1601202S3	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP1601S240S	OVRHSP1601202S4	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1601S240FB	OVRHSP1601202SB	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter
JSP1601S240FS	OVRHSP1601202SC	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1601S240BS	OVRHSP1601202SD	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1601S240FBS	OVRHSP1601202ST	OVR HW, SP, 160kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603D240	OVRHSP1602403D	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground
JSP1603D240B	OVRHSP1602403D2	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Counter
JSP1603D240F	OVRHSP1602403D3	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP1603D240S	OVRHSP1602403D4	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1603D240FB	OVRHSP1602403DB	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1603D240FS	OVRHSP1602403DC	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603D240BS	OVRHSP1602403DD	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603D240FBS	OVRHSP1602403DT	OVR HW, SP, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603H240	OVRHSP1601203H	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP1603H240B	OVRHSP1601203H2	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter
JSP1603H240F	OVRHSP1601203H3	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP1603H240S	OVRHSP1601203H4	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1603H240FB	OVRHSP1601203HB	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter

JSP1603H240FS	OVRHSP1601203HC	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603H240BS	OVRHSP1601203HD	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603H240FBS	OVRHSP1601203HT	OVR HW, SP, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603D380	OVRHSP1603803D	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground
JSP1603D380B	OVRHSP1603803D2	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground, Counter
JSP1603D380F	OVRHSP1603803D3	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground, Filter
JSP1603D380S	OVRHSP1603803D4	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1603D380FB	OVRHSP1603803DB	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1603D380FS	OVRHSP1603803DC	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603D380BS	OVRHSP1603803DD	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603D380FBS	OVRHSP1603803DT	OVR HW, SP, 160kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603D480	OVRHSP1604803D	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground
JSP1603D480B	OVRHSP1604803D2	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Counter
JSP1603D480F	OVRHSP1604803D3	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSP1603D480S	OVRHSP1604803D4	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1603D480FB	OVRHSP1604803DB	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1603D480FS	OVRHSP1604803DC	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603D480BS	OVRHSP1604803DD	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603D480FBS	OVRHSP1604803DT	OVR HW, SP, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603D600	OVRHSP1606003D	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground
JSP1603D600B	OVRHSP1606003D2	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground, Counter
JSP1603D600F	OVRHSP1606003D3	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground, Filter
JSP1603D600S	OVRHSP1606003D4	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP1603D600FB	OVRHSP1606003DB	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP1603D600FS	OVRHSP1606003DC	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603D600BS	OVRHSP1606003DD	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603D600FBS	OVRHSP1606003DT	OVR HW, SP, 160kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603Y208	OVRHSP1601203Y	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP1603Y208B	OVRHSP1601203Y2	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter
JSP1603Y208F	OVRHSP1601203Y3	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP1603Y208S	OVRHSP1601203Y4	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1603Y208FB	OVRHSP1601203YB	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1603Y208FS	OVRHSP1601203YC	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603Y208BS	OVRHSP1601203YD	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603Y208FBS	OVRHSP1601203YT	OVR HW, SP, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603Y380	OVRHSP1602203Y	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP1603Y380B	OVRHSP1602203Y2	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter
JSP1603Y380F	OVRHSP1602203Y3	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter

JSP1603Y380S	OVRHSP1602203Y4	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1603Y380FB	OVRHSP1602203YB	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1603Y380FS	OVRHSP1602203YC	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603Y380BS	OVRHSP1602203YD	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603Y380FBS	OVRHSP1602203YT	OVR HW, SP, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603Y415	OVRHSP1602403Y	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP1603Y415B	OVRHSP1602403Y2	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter
JSP1603Y415F	OVRHSP1602403Y3	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP1603Y415S	OVRHSP1602403Y4	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1603Y415FB	OVRHSP1602403YB	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1603Y415FS	OVRHSP1602403YC	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603Y415BS	OVRHSP1602403YD	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603Y415FBS	OVRHSP1602403YT	OVR HW, SP, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603Y480	OVRHSP1602773Y	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP1603Y480B	OVRHSP1602773Y2	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter
JSP1603Y480F	OVRHSP1602773Y3	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP1603Y480S	OVRHSP1602773Y4	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1603Y480FB	OVRHSP1602773YB	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1603Y480FS	OVRHSP1602773YC	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603Y480BS	OVRHSP1602773YD	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603Y480FBS	OVRHSP1602773YT	OVR HW, SP, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP1603Y600	OVRHSP1603473Y	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground
JSP1603Y600B	OVRHSP1603473Y2	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter
JSP1603Y600F	OVRHSP1603473Y3	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter
JSP1603Y600S	OVRHSP1603473Y4	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP1603Y600FB	OVRHSP1603473YB	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP1603Y600FS	OVRHSP1603473YC	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP1603Y600BS	OVRHSP1603473YD	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP1603Y600FBS	OVRHSP1603473YT	OVR HW, SP, 160kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2001P120	OVRHSP2001201P	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground
JSP2001P120B	OVRHSP2001201P2	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground, Counter
JSP2001P120F	OVRHSP2001201P3	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP2001P120S	OVRHSP2001201P4	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP2001P120FB	OVRHSP2001201PB	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter
JSP2001P120FS	OVRHSP2001201PC	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP2001P120BS	OVRHSP2001201PD	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP2001P120FBS	OVRHSP2001201PT	OVR HW, SP, 200kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure

JSP2001P240	OVRHSP2002401P	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground
JSP2001P240B	OVRHSP202401P2	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground, Counter
JSP2001P240F	OVRHSP2002401P3	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP2001P240S	OVRHSP2002401P4	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP2001P240FB	OVRHSP2002401PB	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter
JSP2001P240FS	OVRHSP2002401PC	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP2001P240BS	OVRHSP2002401PD	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP2001P240FBS	OVRHSP2002401PT	OVR HW, SP, 200kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2001S240	OVRHSP2001202S	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground
JSP2001S240B	OVRHSP2001202S2	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground, Counter
JSP2001S240F	OVRHSP2001202S3	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP2001S240S	OVRHSP2001202S4	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2001S240FB	OVRHSP2001202SB	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter
JSP2001S240FS	OVRHSP2001202SC	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2001S240BS	OVRHSP2001202SD	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2001S240FBS	OVRHSP2001202ST	OVR HW, SP, 200kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003D240	OVRHSP2002403D	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground
JSP2003D240B	OVRHSP2002403D2	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground, Counter
JSP2003D240F	OVRHSP2002403D3	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP2003D240S	OVRHSP2002403D4	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2003D240FB	OVRHSP2002403DB	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2003D240FS	OVRHSP2002403DC	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003D240BS	OVRHSP2002403DD	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003D240FBS	OVRHSP2002403DT	OVR HW, SP, 200kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003H240	OVRHSP2001203H	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP2003H240B	OVRHSP2001203H2	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter
JSP2003H240F	OVRHSP2001203H3	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP2003H240S	OVRHSP2001203H4	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2003H240FB	OVRHSP2001203HB	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter
JSP2003H240FS	OVRHSP2001203HC	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003H240BS	OVRHSP2001203HD	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003H240FBS	OVRHSP2001203HT	OVR HW, SP, 200kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003D380	OVRHSP2003803D	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground
JSP2003D380B	OVRHSP2003803D2	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground, Counter
JSP2003D380F	OVRHSP2003803D3	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground, Filter
JSP2003D380S	OVRHSP2003803D4	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2003D380FB	OVRHSP2003803DB	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2003D380FS	OVRHSP2003803DC	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure

JSP2003D380BS	OVRHSP2003803DD	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003D380FBS	OVRHSP2003803DT	OVR HW, SP, 200kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003D480	OVRHSP2004803D	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground
JSP2003D480B	OVRHSP2004803D2	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground, Counter
JSP2003D480F	OVRHSP2004803D3	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSP2003D480S	OVRHSP2004803D4	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2003D480FB	OVRHSP2004803DB	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2003D480FS	OVRHSP2004803DC	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003D480BS	OVRHSP2004803DD	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003D480FBS	OVRHSP2004803DT	OVR HW, SP, 200kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003D600	OVRHSP2006003D	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground
JSP2003D600B	OVRHSP2006003D2	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground, Counter
JSP2003D600F	OVRHSP2006003D3	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground, Filter
JSP2003D600S	OVRHSP2006003D4	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2003D600FB	OVRHSP2006003DB	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2003D600FS	OVRHSP2006003DC	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003D600BS	OVRHSP2006003DD	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003D600FBS	OVRHSP2006003DT	OVR HW, SP, 200kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003Y208	OVRHSP2001203Y	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP2003Y208B	OVRHSP2001203Y2	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter
JSP2003Y208F	OVRHSP2001203Y3	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP2003Y208S	OVRHSP2001203Y4	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2003Y208FB	OVRHSP2001203YB	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2003Y208FS	OVRHSP2001203YC	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003Y208BS	OVRHSP2001203YD	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003Y208FBS	OVRHSP2001203YT	OVR HW, SP, 200kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003Y380	OVRHSP2002203Y	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP2003Y380B	OVRHSP2002203Y2	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter
JSP2003Y380F	OVRHSP2002203Y3	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP2003Y380S	OVRHSP2002203Y4	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2003Y380FB	OVRHSP2002203YB	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2003Y380FS	OVRHSP2002203YC	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003Y380BS	OVRHSP2002203YD	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003Y380FBS	OVRHSP2002203YT	OVR HW, SP, 200kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003Y415	OVRHSP2002403Y	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP2003Y415B	OVRHSP2002403Y2	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter
JSP2003Y415F	OVRHSP2002403Y3	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP2003Y415S	OVRHSP2002403Y4	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure

JSP2003Y415FB	OVRHSP2002403YB	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2003Y415FS	OVRHSP2002403YC	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003Y415BS	OVRHSP2002403YD	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003Y415FBS	OVRHSP2002403YT	OVR HW, SP, 200kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003Y480	OVRHSP2002773Y	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP2003Y480B	OVRHSP2002773Y2	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter
JSP2003Y480F	OVRHSP2002773Y3	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP2003Y480S	OVRHSP2002773Y4	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground + Stainless Steel Enclosure
JSP2003Y480FB	OVRHSP2002773YB	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2003Y480FS	OVRHSP2002773YC	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003Y480BS	OVRHSP2002773YD	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003Y480FBS	OVRHSP2002773YT	OVR HW, SP, 200kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2003Y600	OVRHSP2003473Y	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground
JSP2003Y600B	OVRHSP2003473Y2	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter
JSP2003Y600F	OVRHSP2003473Y3	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter
JSP2003Y600S	OVRHSP2003473Y4	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2003Y600FB	OVRHSP2003473YB	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2003Y600FS	OVRHSP2003473YC	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2003Y600BS	OVRHSP2003473YD	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2003Y600FBS	OVRHSP2003473YT	OVR HW, SP, 200kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2401P120	OVRHSP2401201P	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground
JSP2401P120B	OVRHSP2401201P2	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground, Counter
JSP2401P120F	OVRHSP2401201P3	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP2401P120S	OVRHSP2401201P4	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP2401P120FB	OVRHSP2401201PB	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter
JSP2401P120FS	OVRHSP2401201PC	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP2401P120BS	OVRHSP2401201PD	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP2401P120FBS	OVRHSP2401201PT	OVR HW, SP, 240kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2401P240	OVRHSP2402401P	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground
JSP2401P240B	OVRHSP2402401P2	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground, Counter
JSP2401P240F	OVRHSP2402401P3	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP2401P240S	OVRHSP2402401P4	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP2401P240FB	OVRHSP2402401PB	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter
JSP2401P240FS	OVRHSP2402401PC	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP2401P240BS	OVRHSP2402401PD	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP2401P240FBS	OVRHSP2402401PT	OVR HW, SP, 240kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2401S240	OVRHSP2401202S	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground

JSP2401S240B	OVRHSP2401202S2	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground, Counter
JSP2401S240F	OVRHSP2401202S3	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP2401S240S	OVRHSP2401202S4	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2401S240FB	OVRHSP2401202SB	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter
JSP2401S240FS	OVRHSP2401202SC	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2401S240BS	OVRHSP2401202SD	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2401S240FBS	OVRHSP2401202ST	OVR HW, SP, 240kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403D240	OVRHSP2402403D	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground
JSP2403D240B	OVRHSP2402403D2	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground, Counter
JSP2403D240F	OVRHSP2402403D3	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP2403D240S	OVRHSP2402403D4	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2403D240FB	OVRHSP2402403DB	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2403D240FS	OVRHSP2402403DC	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403D240BS	OVRHSP2402403DD	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403D240FBS	OVRHSP2402403DT	OVR HW, SP, 240kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403H240	OVRHSP2401203H	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP2403H240B	OVRHSP2401203H2	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter
JSP2403H240F	OVRHSP2401203H3	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP2403H240S	OVRHSP2401203H4	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2403H240FB	OVRHSP2401203HB	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter
JSP2403H240FS	OVRHSP2401203HC	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403H240BS	OVRHSP2401203HH	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403H240FBS	OVRHSP2401203HT	OVR HW, SP, 240kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403D380	OVRHSP2403803D	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground
JSP2403D380B	OVRHSP2403803D2	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground, Counter
JSP2403D380F	OVRHSP2403803D3	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground, Filter
JSP2403D380S	OVRHSP2403803D4	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2403D380FB	OVRHSP2403803DB	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2403D380FS	OVRHSP2403803DC	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403D380BS	OVRHSP2403803DD	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403D380FBS	OVRHSP2403803DT	OVR HW, SP, 240kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403D480	OVRHSP2404803D	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground
JSP2403D480B	OVRHSP2404803D2	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground, Counter
JSP2403D480F	OVRHSP2404803D3	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSP2403D480S	OVRHSP2404803D4	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2403D480FB	OVRHSP2404803DB	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2403D480FS	OVRHSP2404803DC	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403D480BS	OVRHSP2404803DD	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure

JSP2403D480FBS	OVRHSP2404803DT	OVR HW, SP, 240kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403D600	OVRHSP2406003D	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground
JSP2403D600B	OVRHSP2406003D2	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground, Counter
JSP2403D600F	OVRHSP2406003D3	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground, Filter
JSP2403D600S	OVRHSP2406003D4	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP2403D600FB	OVRHSP2406003DB	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP2403D600FS	OVRHSP2406003DC	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403D600BS	OVRHSP2406003DD	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403D600FBS	OVRHSP2406003DT	OVR HW, SP, 240kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403Y208	OVRHSP2401203Y	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP2403Y208B	OVRHSP2401203Y2	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter
JSP2403Y208F	OVRHSP2401203Y3	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP2403Y208S	OVRHSP2401203Y4	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2403Y208FB	OVRHSP2401203YB	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2403Y208FS	OVRHSP2401203YC	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403Y208BS	OVRHSP2401203YD	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403Y208FBS	OVRHSP2401203YT	OVR HW, SP, 240kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403Y380	OVRHSP2402203Y	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP2403Y380B	OVRHSP2402203Y2	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter
JSP2403Y380F	OVRHSP2402203Y3	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP2403Y380S	OVRHSP2402203Y4	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2403Y380FB	OVRHSP2402203YB	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2403Y380FS	OVRHSP2402203YC	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403Y380BS	OVRHSP2402203YD	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403Y380FBS	OVRHSP2402203YT	OVR HW, SP, 240kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403Y415	OVRHSP2402403Y	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP2403Y415B	OVRHSP2402403Y2	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter
JSP2403Y415F	OVRHSP2402403Y3	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP2403Y415S	OVRHSP2402403Y4	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2403Y415FB	OVRHSP2402403YB	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2403Y415FS	OVRHSP2402403YC	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403Y415BS	OVRHSP2402403YD	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403Y415FBS	OVRHSP2402403YT	OVR HW, SP, 240kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403Y480	OVRHSP2402773Y	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP2403Y480B	OVRHSP2402773Y2	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter
JSP2403Y480F	OVRHSP2402773Y3	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP2403Y480S	OVRHSP2402773Y4	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2403Y480FB	OVRHSP2402773YB	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter

JSP2403Y480FS	OVRHSP2402773YC	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403Y480BS	OVRHSP2402773YD	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403Y480FBS	OVRHSP2402773YT	OVR HW, SP, 240kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP2403Y600	OVRHSP2403473Y	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground
JSP2403Y600B	OVRHSP2403473Y2	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter
JSP2403Y600F	OVRHSP2403473Y3	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter
JSP2403Y600S	OVRHSP2403473Y4	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP2403Y600FB	OVRHSP2403473YB	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP2403Y600FS	OVRHSP2403473YC	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP2403Y600BS	OVRHSP2403473YD	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP2403Y600FBS	OVRHSP2403473YT	OVR HW, SP, 240kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure

JSP3001P120	OVRHSP3001201P	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground
JSP3001P120B	OVRHSP3001201P2	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground, Counter
JSP3001P120F	OVRHSP3001201P3	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP3001P120S	OVRHSP3001201P4	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP3001P120FB	OVRHSP3001201PB	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter
JSP3001P120FS	OVRHSP3001201PC	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP3001P120BS	OVRHSP3001201PD	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP3001P120FBS	OVRHSP3001201PT	OVR HW, SP, 300kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3001P240	OVRHSP3002401P	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground
JSP3001P240B	OVRHSP3002401P2	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground, Counter
JSP3001P240F	OVRHSP3002401P3	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP3001P240S	OVRHSP3002401P4	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP3001P240FB	OVRHSP3002401PB	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter
JSP3001P240FS	OVRHSP3002401PC	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP3001P240BS	OVRHSP3002401PD	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP3001P240FBS	OVRHSP3002401PT	OVR HW, SP, 300kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3001S240	OVRHSP3001202S	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground
JSP3001S240B	OVRHSP3001202S2	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground, Counter
JSP3001S240F	OVRHSP3001202S3	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP3001S240S	OVRHSP3001202S4	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP3001S240FB	OVRHSP3001202SB	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter
JSP3001S240FS	OVRHSP3001202SC	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP3001S240BS	OVRHSP3001202SD	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP3001S240FBS	OVRHSP3001202ST	OVR HW, SP, 300kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003D240	OVRHSP3002403D	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground
JSP3003D240B	OVRHSP3002403D2	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground, Counter

JSP3003D240F	OVRHSP3002403D3	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP3003D240S	OVRHSP3002403D4	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP3003D240FB	OVRHSP3002403DB	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP3003D240FS	OVRHSP3002403DC	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003D240BS	OVRHSP3002403DD	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003D240FBS	OVRHSP3002403DT	OVR HW, SP, 300kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003H240	OVRHSP3001203H	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP3003H240B	OVRHSP3001203H2	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter
JSP3003H240F	OVRHSP3001203H3	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSP3003H240S	OVRHSP3001203H4	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP3003H240FB	OVRHSP3001203HB	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter
JSP3003H240FS	OVRHSP3001203HC	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003H240BS	OVRHSP3001203HD	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003H240FBS	OVRHSP3001203HT	OVR HW, SP, 300kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003D380	OVRHSP3003803D	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground
JSP3003D380B	OVRHSP3003803D2	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground, Counter
JSP3003D380F	OVRHSP3003803D3	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground, Filter
JSP3003D380S	OVRHSP3003803D4	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + stainless steel enclosure
JSP3003D380FB	OVRHSP3003803DB	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP3003D380FS	OVRHSP3003803DC	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003D380BS	OVRHSP3003803DD	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003D380FBS	OVRHSP3003803DT	OVR HW, SP, 300kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003D480	OVRHSP3004803D	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground
JSP3003D480B	OVRHSP3004803D2	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground, Counter
JSP3003D480F	OVRHSP3004803D3	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSP3003D480S	OVRHSP3004803D4	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP3003D480FB	OVRHSP3004803DB	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP3003D480FS	OVRHSP3004803DC	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003D480BS	OVRHSP3004803DD	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003D480FBS	OVRHSP3004803DT	OVR HW, SP, 300kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003D600	OVRHSP3006003D	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground
JSP3003D600B	OVRHSP3006003D2	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground, Counter
JSP3003D600F	OVRHSP3006003D3	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground, Filter
JSP3003D600S	OVRHSP3006003D4	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP3003D600FB	OVRHSP3006003DB	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP3003D600FS	OVRHSP3006003DC	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003D600BS	OVRHSP3006003DD	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003D600FBS	OVRHSP3006003DT	OVR HW, SP, 300kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure

JSP3003Y208	OVRHSP3001203Y	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP3003Y208B	OVRHSP3001203Y2	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter
JSP3003Y208F	OVRHSP3001203Y3	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP3003Y208S	OVRHSP3001203Y4	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP3003Y208FB	OVRHSP3001203YB	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP3003Y208FS	OVRHSP3001203YC	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003Y208BS	OVRHSP3001203YD	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003Y208FBS	OVRHSP3001203YT	OVR HW, SP, 300kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003Y380	OVRHSP3002203Y	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSP3003Y380B	OVRHSP3002203Y2	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter
JSP3003Y380F	OVRHSP3002203Y3	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP3003Y380S	OVRHSP3002203Y4	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP3003Y380FB	OVRHSP3002203YB	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP3003Y380FS	OVRHSP3002203YC	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003Y380BS	OVRHSP3002203YD	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003Y380FBS	OVRHSP3002203YT	OVR HW, SP, 300kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003Y415	OVRHSP3002403Y	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP3003Y415B	OVRHSP3002403Y2	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter
JSP3003Y415F	OVRHSP3002403Y3	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP3003Y415S	OVRHSP3002403Y4	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP3003Y415FB	OVRHSP3002403YB	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP3003Y415FS	OVRHSP3002403YC	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003Y415BS	OVRHSP3002403YD	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003Y415FBS	OVRHSP3002403YT	OVR HW, SP, 300kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003Y480	OVRHSP3002773Y	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP3003Y480B	OVRHSP3002773Y2	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter
JSP3003Y480F	OVRHSP3002773Y3	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP3003Y480S	OVRHSP3002773Y4	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP3003Y480FB	OVRHSP3002773YB	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP3003Y480FS	OVRHSP3002773YC	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP3003Y480BS	OVRHSP3002773YD	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003Y480FBS	OVRHSP3002773YT	OVR HW, SP, 300kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP3003Y600	OVRHSP3003473Y	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground
JSP3003Y600B	OVRHSP3003473Y2	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter
JSP3003Y600F	OVRHSP3003473Y3	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter
JSP3003Y600S	OVRHSP3003473Y4	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP3003Y600FB	OVRHSP3003473YB	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP3003Y600FS	OVRHSP3003473YC	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure

JSP3003Y600BS	OVRHSP3003473YD	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP3003Y600FBS	OVRHSP3003473YT	OVR HW, SP, 300kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4001P120	OVRHSP4001201P	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground
JSP4001P120B	OVRHSP4001201P2	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground, Counter
JSP4001P120F	OVRHSP4001201P3	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground, Filter
JSP4001P120S	OVRHSP4001201P4	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP4001P120FB	OVRHSP4001201PB	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter
JSP4001P120FS	OVRHSP4001201PC	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP4001P120BS	OVRHSP4001201PD	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP4001P120FBS	OVRHSP4001201PT	OVR HW, SP, 400kA, 120V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4001P240	OVRHSP4002401P	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground
JSP4001P240B	OVRHSP4002401P2	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground, Counter
JSP4001P240F	OVRHSP4002401P3	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground, Filter
JSP4001P240S	OVRHSP4002401P4	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSP4001P240FB	OVRHSP4002401PB	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter
JSP4001P240FS	OVRHSP4002401PC	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSP4001P240BS	OVRHSP4002401PD	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground, Counter + Stainless Steel Enclosure
JSP4001P240FBS	OVRHSP4002401PT	OVR HW, SP, 400kA, 240V, 1-phase, 2 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4001S240	OVRHSP4001202S	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground
JSP4001S240B	OVRHSP4001202S2	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground, Counter
JSP4001S240F	OVRHSP4001202S3	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSP4001S240S	OVRHSP4001202S4	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP4001S240FB	OVRHSP4001202SB	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter
JSP4001S240FS	OVRHSP4001202SC	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP4001S240BS	OVRHSP4001202SD	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP4001S240FBS	OVRHSP4001202ST	OVR HW, SP, 400kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003D240	OVRHSP4002403D	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground
JSP4003D240B	OVRHSP4002403D2	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground, Counter
JSP4003D240F	OVRHSP4002403D3	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSP4003D240S	OVRHSP4002403D4	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP4003D240FB	OVRHSP4002403DB	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP4003D240FS	OVRHSP4002403DC	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003D240BS	OVRHSP4002403DD	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003D240FBS	OVRHSP4002403DT	OVR HW, SP, 400kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003H240	OVRHSP4001203H	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSP4003H240B	OVRHSP4001203H2	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter
JSP4003H240F	OVRHSP4001203H3	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter

JSP4003H240S	OVRHSP4001203H4	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP4003H240FB	OVRHSP4001203HB	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter
JSP4003H240FS	OVRHSP4001203HC	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003H240BS	OVRHSP4001203HD	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003H240FBS	OVRHSP4001203HT	OVR HW, SP, 400kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003D380	OVRHSP4003803D	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground
JSP4003D380B	OVRHSP4003803D2	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground, Counter
JSP4003D380F	OVRHSP4003803D3	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground, Filter
JSP4003D380S	OVRHSP4003803D4	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP4003D380FB	OVRHSP4003803DB	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP4003D380FS	OVRHSP4003803DC	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003D380BS	OVRHSP4003803DD	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003D380FBS	OVRHSP4003803DT	OVR HW, SP, 400kA, 380V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003D480	OVRHSP4004803D	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground
JSP4003D480B	OVRHSP4004803D2	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground, Counter
JSP4003D480F	OVRHSP4004803D3	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSP4003D480S	OVRHSP4004803D4	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP4003D480FB	OVRHSP4004803DB	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP4003D480FS	OVRHSP4004803DC	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003D480BS	OVRHSP4004803DD	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003D480FBS	OVRHSP4004803DT	OVR HW, SP, 400kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003D600	OVRHSP4006003D	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground
JSP4003D600B	OVRHSP4006003D2	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground, Counter
JSP4003D600F	OVRHSP4006003D3	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground, Filter
JSP4003D600S	OVRHSP4006003D4	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSP4003D600FB	OVRHSP4006003DB	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter
JSP4003D600FS	OVRHSP4006003DC	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003D600BS	OVRHSP4006003DD	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003D600FBS	OVRHSP4006003DT	OVR HW, SP, 400kA, 600V Delta, 3-phase, 3 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003Y208	OVRHSP4001203Y	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSP4003Y208B	OVRHSP4001203Y2	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter
JSP4003Y208F	OVRHSP4001203Y3	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSP4003Y208S	OVRHSP4001203Y4	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP4003Y208FB	OVRHSP4001203YB	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP4003Y208FS	OVRHSP4001203YC	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003Y208BS	OVRHSP4001203YD	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003Y208FBS	OVRHSP4001203YT	OVR HW, SP, 400kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003Y380	OVRHSP4002203Y	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground

JSP4003Y380B	OVRHSP4002203Y2	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter
JSP4003Y380F	OVRHSP4002203Y3	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSP4003Y380S	OVRHSP4002203Y4	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP4003Y380FB	OVRHSP4002203YB	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP4003Y380FS	OVRHSP4002203YC	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003Y380BS	OVRHSP4002203YD	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003Y380FBS	OVRHSP4002203YT	OVR HW, SP, 400kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003Y415	OVRHSP4002403Y	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSP4003Y415B	OVRHSP4002403Y2	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter
JSP4003Y415F	OVRHSP4002403Y3	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSP4003Y415S	OVRHSP4002403Y4	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP4003Y415FB	OVRHSP4002403YB	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP4003Y415FS	OVRHSP4002403YC	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003Y415BS	OVRHSP4002403YD	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003Y415FBS	OVRHSP4002403YT	OVR HW, SP, 400kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003Y480	OVRHSP4002773Y	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSP4003Y480B	OVRHSP4002773Y2	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter
JSP4003Y480F	OVRHSP4002773Y3	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSP4003Y480S	OVRHSP4002773Y4	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP4003Y480FB	OVRHSP4002773YB	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP4003Y480FS	OVRHSP4002773YC	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003Y480BS	OVRHSP4002773YD	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003Y480FBS	OVRHSP4002773YT	OVR HW, SP, 400kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure
JSP4003Y600	OVRHSP4003473Y	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground
JSP4003Y600B	OVRHSP4003473Y2	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter
JSP4003Y600F	OVRHSP4003473Y3	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter
JSP4003Y600S	OVRHSP4003473Y4	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSP4003Y600FB	OVRHSP4003473YB	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter
JSP4003Y600FS	OVRHSP4003473YC	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSP4003Y600BS	OVRHSP4003473YD	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground, Counter + Stainless Steel Enclosure
JSP4003Y600FBS	OVRHSP4003473YT	OVR HW, SP, 400kA, 347/600 Wye, 3-phase, 4 wire + Ground, Filter + Counter + Stainless Steel Enclosure

JSP-FMP	OVRHSRFMP	OVR HW, SR Flush Plate Mount
JSPR1201P120	OVRHSR1201201P	OVR HW, SPR, 120kA, 120V, 1-phase, 2 wire + Ground
JSPR1201P120F	OVRHSR1201201P3	OVR HW, SPR, 120kA, 120V, 1-phase, 2 wire + Ground, Filter
JSPR1201P120FS	OVRHSR1201201PC	OVR HW, SPR, 120kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1201P120S	OVRHSR1201201P4	OVR HW, SPR, 120kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSPR1201P240	OVRHSR1202401P	OVR HW, SPR, 120kA, 240V, 1-phase, 2 wire + Ground

JSPR1201P240F	OVRHSR1202401P3	OVR HW, SPR, 120kA, 240V, 1-phase, 2 wire + Ground, Filter
JSPR1201P240FS	OVRHSR1202401PC	OVR HW, SPR, 120kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1201P240S	OVRHSR1202401P4	OVR HW, SPR, 120kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSPR1201S240	OVRHSR1201202S	OVR HW, SPR, 120kA, 120/240V, 2-phase, 3 wire + Ground
JSPR1201S240F	OVRHSR1201202S3	OVR HW, SPR, 120kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSPR1201S240FS	OVRHSR1201202SC	OVR HW, SPR, 120kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1201S240S	OVRHSR1201202S4	OVR HW, SPR, 120kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSPR1203D240	OVRHSR1202403D	OVR HW, SPR, 120kA, 240V Delta, 3-phase, 3 wire + Ground
JSPR1203D240F	OVRHSR1202403D3	OVR HW, SPR, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSPR1203D240FS	OVRHSR1202403DC	OVR HW, SPR, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203D240S	OVRHSR1202403D4	OVR HW, SPR, 120kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSPR1203D480	OVRHSR1204803D	OVR HW, SPR, 120kA, 480V Delta, 3-phase, 3 wire + Ground
JSPR1203D480F	OVRHSR1204803D3	OVR HW, SPR, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSPR1203D480FS	OVRHSR1204803DC	OVR HW, SPR, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203D480S	OVRHSR1204803D4	OVR HW, SPR, 120kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSPR1203H240	OVRHSR1201203H	OVR HW, SPR, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSPR1203H240F	OVRHSR1201203H3	OVR HW, SPR, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSPR1203H240FS	OVRHSR1201203HC	OVR HW, SPR, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203H240S	OVRHSR1201203H4	OVR HW, SPR, 120kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1203Y208	OVRHSR1201203Y	OVR HW, SPR, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSPR1203Y208F	OVRHSR1201203Y3	OVR HW, SPR, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1203Y208FS	OVRHSR1201203YC	OVR HW, SPR, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203Y208S	OVRHSR1201203Y4	OVR HW, SPR, 120kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1203Y380	OVRHSR1202203Y	OVR HW, SPR, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSPR1203Y380F	OVRHSR1202203Y3	OVR HW, SPR, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1203Y380FS	OVRHSR1202203YC	OVR HW, SPR, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203Y380S	OVRHSR1202203Y4	OVR HW, SPR, 120kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1203Y415	OVRHSR1202403Y	OVR HW, SPR, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSPR1203Y415F	OVRHSR1202403Y3	OVR HW, SPR, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1203Y415FS	OVRHSR1202403YC	OVR HW, SPR, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203Y415S	OVRHSR1202403Y4	OVR HW, SPR, 120kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1203Y480	OVRHSR1202773Y	OVR HW, SPR, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSPR1203Y480F	OVRHSR1202773Y3	OVR HW, SPR, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1203Y480FS	OVRHSR1202773YC	OVR HW, SPR, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203Y480S	OVRHSR1202773Y4	OVR HW, SPR, 120kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1203D380	OVRHSR1203803D	OVR HW, SPR, 120kA, 380V, 3-phase Delta, 4 wire + Ground
JSPR1203D380F	OVRHSR1203803D3	OVR HW, SPR, 120kA, 380V, 3-phase Delta, 4 wire + Ground, Filter
JSPR1203D380FS	OVRHSR1203803DC	OVR HW, SPR, 120kA, 380V, 3-phase Delta, 4 wire + Ground, Stainless Steel Enclosure

JSPR1203D380S	OVRHSR1203803D4	OVR HW, SPR, 120kA, 380V, 3-phase Delta, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203D600	OVRHSR1206003D	OVR HW, SPR, 120kA, 600V, 3-phase Delta, 4 wire + Ground
JSPR1203D600F	OVRHSR1206003D3	OVR HW, SPR, 120kA, 600V, 3-phase Delta, 4 wire + Ground, Filter
JSPR1203D600FS	OVRHSR1206003DC	OVR HW, SPR, 120kA, 600V, 3-phase Delta, 4 wire + Ground, Stainless Steel Enclosure
JSPR1203D600S	OVRHSR1206003D4	OVR HW, SPR, 120kA, 600V, 3-phase Delta, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1203Y600	OVRHSR1203473Y	OVR HW, SPR, 120kA, 347/600V, 3-phase Wye, 4 wire + Ground
JSPR1203Y600F	OVRHSR1203473Y3	OVR HW, SPR, 120kA, 347/600V, 3-phase Wye, 4 wire + Ground, Filter
JSPR1203Y600FS	OVRHSR1203473YC	OVR HW, SPR, 120kA, 347/600V, 3-phase Wye, 4 wire + Ground, Stainless Steel Enclosure
JSPR1203Y600S	OVRHSR1203473Y4	OVR HW, SPR, 120kA, 347/600V, 3-phase Wye, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1601P120	OVRHSR1601201P	OVR HW, SPR, 120kA, 120V, 1-phase, 2 wire + Ground
JSPR1601P120F	OVRHSR1601201P3	OVR HW, SPR, 160kA, 120V, 1-phase, 2 wire + Ground, Filter
JSPR1601P120FS	OVRHSR1601201PC	OVR HW, SPR, 160kA, 120V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1601P120S	OVRHSR1601201P4	OVR HW, SPR, 160kA, 120V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSPR1601P240	OVRHSR1602401P	OVR HW, SPR, 160kA, 240V, 1-phase, 2 wire + Ground
JSPR1601P240F	OVRHSR1602401P3	OVR HW, SPR, 160kA, 240V, 1-phase, 2 wire + Ground, Filter
JSPR1601P240FS	OVRHSR1602401PC	OVR HW, SPR, 160kA, 240V, 1-phase, 2 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1601P240S	OVRHSR1602401P4	OVR HW, SPR, 160kA, 240V, 1-phase, 2 wire + Ground, Stainless Steel Enclosure
JSPR1601S240	OVRHSR1601202S	OVR HW, SPR, 160kA, 120/240V, 2-phase, 3 wire + Ground
JSPR1601S240F	OVRHSR1601202S3	OVR HW, SPR, 160kA, 120/240V, 2-phase, 3 wire + Ground, Filter
JSPR1601S240FS	OVRHSR1601202SC	OVR HW, SPR, 160kA, 120/240V, 2-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1601S240S	OVRHSR1601202S4	OVR HW, SPR, 160kA, 120/240V, 2-phase, 3 wire + Ground, Stainless Steel Enclosure
JSPR1603D240	OVRHSR1602403D	OVR HW, SPR, 160kA, 240V Delta, 3-phase, 3 wire + Ground
JSPR1603D240F	OVRHSR1602403D3	OVR HW, SPR, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Filter
JSPR1603D240FS	OVRHSR1602403DC	OVR HW, SPR, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603D240S	OVRHSR1602403D4	OVR HW, SPR, 160kA, 240V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSPR1603D480	OVRHSR1604803D	OVR HW, SPR, 160kA, 480V Delta, 3-phase, 3 wire + Ground
JSPR1603D480F	OVRHSR1604803D3	OVR HW, SPR, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Filter
JSPR1603D480FS	OVRHSR1604803DC	OVR HW, SPR, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603D480S	OVRHSR1604803D4	OVR HW, SPR, 160kA, 480V Delta, 3-phase, 3 wire + Ground, Stainless Steel Enclosure
JSPR1603H240	OVRHSR1601203H	OVR HW, SPR, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground
JSPR1603H240F	OVRHSR1601203H3	OVR HW, SPR, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter
JSPR1603H240FS	OVRHSR1601203HC	OVR HW, SPR, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603H240S	OVRHSR1601203H4	OVR HW, SPR, 160kA, 120/240V Hi Leg Delta, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1603Y208	OVRHSR1601203Y	OVR HW, SPR, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground
JSPR1603Y208F	OVRHSR1601203Y3	OVR HW, SPR, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1603Y208FS	OVRHSR1601203YC	OVR HW, SPR, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603Y208S	OVRHSR1601203Y4	OVR HW, SPR, 160kA, 120/208 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure

JSPR1603Y380	OVRHSR1602203Y	OVR HW, SPR, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground
JSPR1603Y380F	OVRHSR1602203Y3	OVR HW, SPR, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1603Y380FS	OVRHSR1602203YC	OVR HW, SPR, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603Y380S	OVRHSR1602203Y4	OVR HW, SPR, 160kA, 220/380 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1603Y415	OVRHSR1602403Y	OVR HW, SPR, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground
JSPR1603Y415F	OVRHSR1602403Y3	OVR HW, SPR, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1603Y415FS	OVRHSR1602403YC	OVR HW, SPR, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603Y415S	OVRHSR1602403Y4	OVR HW, SPR, 160kA, 240/415 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1603Y480	OVRHSR1602773Y	OVR HW, SPR, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground
JSPR1603Y480F	OVRHSR1602773Y3	OVR HW, SPR, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter
JSPR1603Y480FS	OVRHSR1602773YC	OVR HW, SPR, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603Y480S	OVRHSR1602773Y4	OVR HW, SPR, 160kA, 277/480 Wye, 3-phase, 4 wire + Ground, Stainless Steel Enclosure
JSPR1603D380	OVRHSR1603803D	OVR HW, SPR, 160kA, 380V, 3-phase Delta, 4 wire + Ground
JSPR1603D380F	OVRHSR1603803D3	OVR HW, SPR, 160kA, 380V, 3-phase Delta, 4 wire + Ground, Filter
JSPR1603D380FS	OVRHSR1603803DC	OVR HW, SPR, 160kA, 380V, 3-phase Delta, 4 wire + Ground, Stainless Steel Enclosure
JSPR1603D380S	OVRHSR1603803D4	OVR HW, SPR, 160kA, 380V, 3-phase Delta, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603D600	OVRHSR1606003D	OVR HW, SPR, 160kA, 600V, 3-phase Delta, 4 wire + Ground
JSPR1603D600F	OVRHSR1606003D3	OVR HW, SPR, 160kA, 600V, 3-phase Delta, 4 wire + Ground, Filter
JSPR1603D600FS	OVRHSR1606003DC	OVR HW, SPR, 160kA, 600V, 3-phase Delta, 4 wire + Ground, Stainless Steel Enclosure
JSPR1603D600S	OVRHSR1606003D4	OVR HW, SPR, 160kA, 600V, 3-phase Delta, 4 wire + Ground, Filter + Stainless Steel Enclosure
JSPR1603Y600	OVRHSR1603473Y	OVR HW, SPR, 160kA, 347/600V, 3-phase Wye, 4 wire + Ground
JSPR1603Y600F	OVRHSR1603473Y3	OVR HW, SPR, 160kA, 347/600V, 3-phase Wye, 4 wire + Ground, Filter
JSPR1603Y600FS	OVRHSR1603473YC	OVR HW, SPR, 160kA, 347/600V, 3-phase Wye, 4 wire + Ground, Stainless Steel Enclosure
JSPR1603Y600S	OVRHSR1603473Y4	OVR HW, SPR, 160kA, 347/600V, 3-phase Wye, 4 wire + Ground, Filter + Stainless Steel Enclosure