



中国国家强制性产品认证证书

证书编号：2004010304138318

委托人名称、地址

ABB France

3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

生产者（制造商）名称、地址

ABB France

3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

生产企业名称、地址

ABB France

3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

产品名称和系列、规格、型号

切换电容器接触器

UA50-30...RA, UA63-30...RA, UA75-30...RA; 详见参数附件

产品标准和技术要求

GB/T14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求，
特发此证。

发证日期：2017年08月21日 有效期至：2022年08月21日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2004年12月28日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



主任：



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2004010304138318

NAME AND ADDRESS OF THE APPLICANT

ABB France
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

NAME AND ADDRESS OF THE MANUFACTURER

ABB France
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

NAME AND ADDRESS OF THE FACTORY

ABB France
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

PRODUCT NAME, MODEL AND SPECIFICATION

Contactors for capacitor switching
UA50-30...RA,UA63-30...RA,UA75-30...RA;See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.4-2010

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Aug.21,2017

Valid until: Aug.21,2022

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Dec.28,2004

The certificate information is available through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

附录:

第 1 页 共 2 页

证书编号: 2004010304138318

纸号: 1778893

UA50-30...RA,UA63-30...RA,UA75-30...RA

Ui:1000V;

UA50-30...RA:Ith:100A;

AC-6b:Ue/Ie:AC220-230-240/400-415/440/500-550/660-690V/66A;

UA63-30...RA:Ith:125A;

AC-6b:Ue/Ie:AC220-230-240/400-415/440/500-550/660-690V/76A;

UA75-30...RA:Ith:125A;

AC-6b:Ue/Ie:AC220-230-240/400-415/440/500-550/660-690V/88A;

Us:24V 50/60Hz,48V 50/60Hz,110V 50Hz/110-120V 60Hz,

220-230V 50Hz/230-240V 60Hz,380-400V 50Hz/400-415V 60Hz,

400-415V 50Hz/415-440V 60Hz;

3P;IP10

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心



中国国家强制性产品认证证书

附录:

第 2 页 共 2 页

证书编号: 2004010304138318

纸号: 1778893

型号的解释:

UA 50 30 00 RA
 I II III IV V VI

I - Main designation : UA

II - Range size
50, 63, 75

III - Main Pole Construction
30 - 3 Normally Opened and 0 Normally Closed main poles.

IV - Auxiliary Pole Construction
00 - No auxiliary pole provided.

V - RA means with insertion of damping resistors

VI - Coil code
See table 1

List of type

Designation
UA50-30-00RA + coil voltage
UA63-30-00RA + coil voltage
UA75-30-00RA + coil voltage

注: 此附录与证书同时使用时有效。



主任:



中国质量认证中心