

Stanilite®

Retrofit® LED kit Nexus® non-maintained



Range

Non-standard range

Product group

Retrofit LED kit




Features

- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, wireless
- RF frequency range 920 - 925 MHz



Catalogue no.	Description
Nexus products	
SGRETRFLEDKIT	Retrofit Nexus RF emergency kit (suits 2x36W batten SMRT)
Spare parts	
03-01311P	Battery LiFePO4 3.2V 4.5Ah



Dimensions			
Item	Length	Width	Height
Control pack	225mm	56mm	39mm
Battery	110mm	37mm	37mm
LED strip	550mm	23mm	
Weight			
Model	Weight		
Nexus RF	1.0kg		
Construction			
Part	Construction		
Control pack housing	White polycarbonate		

Light source		
	Model	Light source
	Nexus RF	3 x 6 LED strips 3.0W

Power consumption		
	Model	Power consumption
	Nexus RF	2.0W

Note: Preliminary results

Note:
 - Complies to IEC60598.2.22 and AS2293