

PRODUCT SPECIFICATION

# EG1LS1-S22

## Guideway 230v AC 22M IP40 Surface/Wall

Catalogue Number **EG1LS1-S22**  
 GID **7TCA091130R0404**  
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
 Power Supply System **Mains / Slave Operation**  
 Mounting Method/Form **Ceiling, Wall Surface**  
 Housing Material **Aluminium/Plastic**  
 Colour **Silver**  
 Dimensions (LxWxD) **235 x 66 x 172 mm**  
 Temperature Range **5 to 35°C**  
 Weight **1.5 Kg**

Emergency Duration (Hours) **Mains / Central Battery**  
 Battery **Mains / Central Battery**  
 Monitoring Equipment **None**  
 Lamp **1 x 2W LED**  
 Emergency Light Output (Lumens) **Not Applicable**  
 Average Lifespan light source (Hours) **100000 Hours**  
 Light Colour/Temperature/CRI **White / 5000 / 80**  
 Degree of Protection **IP40**

Type of Legend **Single or Double Sided**  
 Exit Sign Viewing/Recognition Distance (m) **22**  
 Nominal Voltage **220-240v AC/DC 0-60Hz**  
 Power Consumption **4.4 VA / 4 Watts**  
 Current **Nominal: 19mA (mA)**

### Accessories

**XEN2EG22** Down ISO7010 Legend Single Sided  
**XEN3EG22** Left ISO7010 Legend Single Sided  
**XEN6EG22** Right ISO7010 Legend Single Sided  
**XEN5EG22** Up ISO7010 Legend Single Sided  
**XBN1EG22** Arabic English Legend Single Sided  
**XEN0G22** Blank Legend Single Sided

**EG-T4EG** Cover Discs (2x semi-circular, 2x rectangular) for Slave

**EG-TKIT50** Suspension Kit Pendant 50mm  
**EG-TKIT100** Suspension Kit Pendant 100mm  
**EG-WKIT150** Wire Suspension Kit 150mm

**XEN602EG22** Down ISO7010 Legend Flag Mount  
**XEN603EG22** Left ISO7010 Legend Flag Mount  
**XEN606EG22** Right ISO7010 Legend Flag Mount  
**XEN605EG22** Up ISO7010 Legend Flag Mount



Exit Sign Flag Mount  
EG1LS1-S22 + XEN606EG22



Exit Sign Suspended  
EG1LS1-S22 + EG-TKIT50



Exit Sign Surface  
EG1LS1-S22

