

PRODUCT SPECIFICATION

EGR1LS1LTC-S32

Guideway 230v AC 32M IP40 EMEX Test Recess

Catalogue Number **EGR1LS1LTC-S32**
 GID **7TCA091140R0531**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Mains / Slave Operation**
 Mounting Method/Form **Ceiling, Wall Recessed**
 Housing Material **Aluminium/Plastic**
 Colour **Silver**
 Dimensions (LxWxD) **335 x 84 x 184 mm**
 Temperature Range **5 to 35°C**
 Weight **1.5 Kg**

Emergency Duration (Hours) **Mains / Central Battery**
 Battery **Mains / Central Battery**
 Monitoring Equipment **EMEX test**
 Lamp **1 x 4W LED**
 Emergency Light Output (Lumens) **Not Applicable**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 5000 / 80**
 Degree of Protection **IP40**

Type of Legend **Single or Double Sided**
 Exit Sign Viewing/Recognition Distance (m) **32**
 Nominal Voltage **220-240v AC 50/60Hz**
 Power Consumption **7.1 VA / 6.5 Watts**
 Current **Nominal: 31mA (mA)**

Accessories

XEN2EG32 Down ISO7010 Legend Single Sided
XEN3EG32 Left ISO7010 Legend Single Sided
XEN6EG32 Right ISO7010 Legend Single Sided
XEN5EG32 Up ISO7010 Legend Single Sided
XBN1EG32 Arabic English Legend Single Sided
XEN0G22 Blank Legend Single Sided

EG-T4EG Cover Discs (2x semi-circular, 2x rectangular) for Slave

EG-TKIT50 Suspension Kit Pendant 50mm
EG-TKIT100 Suspension Kit Pendant 100mm
EG-WKIT150 Wire Suspension Kit 150mm

XEN602EG32 Down ISO7010 Legend Flag Mount
XEN603EG32 Left ISO7010 Legend Flag Mount
XEN606EG32 Right ISO7010 Legend Flag Mount
XEN605EG32 Up ISO7010 Legend Flag Mount



Exit Sign Suspended
 EGR1LS1LTC-S32 + EG-WKIT150



Exit Sign Recessed
 EGR1LS1LTC-S32

