


Serenga 2

Project covering & stylish



Escape route - Surface mount wall

- Injection moulded - high grade polycarbonate body
- Specially designed lens with optimised light distribution for wall mounting applications
- Modular, First-Fix installation
- Ease of installation - unique moulded construction to retain IP rating without additional protection



—
Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTSR2-SWM3-G1	SFC M3 CT-NAVEO WALL - W3M WH	220-240 AC 50Hz	1 x LED 2W	203	3.5 / 3	3	5-40	1.0
SR2-SW230-G1	SFC230V WALL -W3M WH	220-240 AC/DC 0-60Hz			5.5 / 5	230V	0-40	0.7
SR2-SW230LT-G1	SFC 230V EMEX WALL - W3M WH	220-240 AC 50/60Hz			5.5 / 5	230V	0-40	0.7
SR2-SWM3-G1	SFC M3 AUTOTST WALL -W3M WH	220-240 AC 50Hz			3.5 / 3	3	5-40	1.0

Includes lens G
Black version available on request

Code	Lens	Type	Application
SR2-LENS1	A	Escape route	2-4m corridor use, ceiling mount
SR2-LENS2	B	Escape route, or object	4-8m corridor use, ceiling mount. Or spot light at 2-4m (ceiling mount)
SR2-LENS3	C	Escape route	8-12m corridor use, ceiling mount
SR2-LENS4	D	Open area	2-4m, open area space
SR2-LENS5	E	Open area	4-8m, open area space
SR2-LENS6	F	Open area	8-12m, open area space
SR2-LENS7*	G	Escape route	2-4m corridor use, wall mount

*Lens included in the box
See spacing tables on pages 132-133

