



EVA-R-CWI/ALU

Slave 2 watt, 230 Volt round aluminium recess led luminaire, series Evago. Light distribution: wide (W), for example canteens

Product Information

| | |
|-----------------|-----------------------|
| Type | EVA-R-CWI/ALU |
| Catalog number | 5510257064 |
| Category_ | Escape route lighting |
| GTIN | 08713812765358 |
| GID | 7TCA091190R0033 |
| Serie | Evago |
| Warranty (Year) | 5 |



Characteristics

| | |
|---|-------------------------------------|
| Power supply system | Central |
| Continuous operation | Yes |
| Mounting Method | Ceiling |
| Mounting form | Recess |
| Material housing | Aluminium / plastic |
| Colour housing | Aluminium |
| Material | Aluminium / polycarbonate |
| Colour | Aluminium |
| Length (mm) | 226 |
| Width (mm) | 100 |
| Height/depth (mm) | 38 |
| Maximum outer diameter (mm) | 100 |
| Built-in length (mm) | 226 |
| Built-in width (mm) | 68 |
| Built-in diameter (mm) | 68 |
| Built-in depth (mm) | 35 |
| Nominal voltage (V) | 230 |
| Voltage type | AC |
| Monitoring equipment | None |
| With lamp | Yes |
| Lamp Type | Led |
| Lamp holder | Other |
| Lamp power (W) | 2 |
| Number of lamps | 1 |
| Light output in emergency operation (lm) | 245 |
| Average lifespan light source (hours) | 100.000 |
| Colour of light | White |
| Colour temperature (K) | 5600 |
| CRI | 70 |
| Protection class | II |
| Degree of protection (IP) | 42 |
| With remote switch connection | No |
| Wiring system | Maintained / non-maintained circuit |
| Type of indicator | Not applicable |
| Circuit | Other |
| Power consumption maintained mode (W) | 5 |
| Apparent power consumption maintained mode (VA) | 5,5 |
| Nominal current (mA) | 24 |
| Inrush Current (A - 0.1ms) | 3 |

| | |
|------------------------|---------|
| Powerfactor | 0,9 |
| Temperature range (°C) | 0 ~ +40 |

Article Details

| | |
|-----------------|---------------------|
| Product class | Emergency luminaire |
| E-code | EC001957 |
| Discount group | 30407 |
| Harmonized code | 9405408440 |
| GLN | 8713812000008 |

Ordering information

| | |
|------------------------|--------|
| Orderable | Yes |
| Order-Unit | Pieces |
| Minimum order quantity | 1 |
| Order Increment | 1 |

Supply Information

| | |
|-----------------------------------|----------------|
| Weight (kg) | 0,313 |
| Packaging | Cardboard box |
| Packaging dimensions (LxWxH) (mm) | 225 x 170 x 62 |