

Horizon

Traditional & versatile



Back-lit LED exit sign

- Choice of IP40 surface mount (OH) or IP20 recessed (OZ)
- Shaped diffuser and contoured reflector
- First-Fix aluminium base with white polycarbonate luminaire body
- Clip-on legend panel
- Complies to IEC 60598.2.22



LED base unit

Order code	Description	Input voltage	Lamp type	Power consumption / duration		Environment temp. (°C)	Weight (kg)
				(VA/W)	(hrs)		
CTOH3L261	CT 2LED SIGN M3	220-240 AC 50Hz	2 x LED 1W	9.9 / 5.1	3	0-25	1.3
OH3L261	2LED SIGN M3	220-240 AC 50Hz		9.9 / 5.1	3	0-25	1.3
OH1L261HF	2XLED SIGN 230VHF	220-240 AC/DC 0-60Hz		6.8 / 3.1	230V	0-40	1.1
OH1L261LTC	2XLED SIGN 230VLTC	220-240 AC 50/60Hz		6.8 / 3.1	230V	0-40	1.1
CTOZ3L261	CT 2LED REC-SIGN M3	220-240 AC 50Hz		9.9 / 5.1	3	0-25	1.3
OZ3L261	2LED REC-SIGN M3	220-240 AC 50Hz		9.9 / 5.1	3	0-25	1.3
OZ1L261HF	2XLED REC-SIGN 230VHF	220-240 AC/DC 0-60Hz		6.8 / 3.1	230V	0-40	1.1
OZ1L261LTC	2XLED REC-SIGN 230VLTC	220-240 AC 50/60Hz		6.8 / 3.1	230V	0-40	1.1
OH3L261V2	2LEDS SIGN M3 220V60HZ	220-240 AC 50/60Hz		9.9 / 5.1	3	0-25	1.3
OZ3L261V2	2LED REC-SIGN M3 60HZ	220-240 AC 50/60Hz		9.9 / 5.1	3	0-25	1.3

Legends

Part No.	Pictogram
XEN2H	
XEN3H	
XEN6H	
XEN5H	
XLF802H	
XLF803H	
Arabic legend format	
XB01H	

ISO 7010 pictogram legends are shown. Euro format & Special legends are available to order see pages 139-141



Accessories

Order code	Description
OH/BCM	Ceiling bracket, vertical mount, for back-lit sign
OH/WG	Protective wire guard

