



## Luto/LED/400/24

Slave watt, 24 Volt surface mount led luminaire, series Luto

### Product Information

|                 |                            |
|-----------------|----------------------------|
| Type            | Luto/LED/400/24            |
| Catalog number  | 11110132                   |
| Category_       | Escape route signalisation |
| GTIN            | 08713812035024             |
| GID             | 7TCA091130R0000            |
| Serie           | Luto                       |
| Warranty (Year) | 5                          |



### Characteristics

|   |                                     |
|---|-------------------------------------|
| Power supply system                             | Central                             |
| Continuous operation                            | Yes                                 |
| Mounting Method                                 | Wall                                |
| Mounting form                                   | Surface                             |
| Material housing                                | Aluminium                           |
| Colour housing                                  | Aluminium                           |
| Material  | Aluminium                           |
| Colour  | Aluminium                           |
| Length (mm)                                     | 400                                 |
| Width (mm)                                      | 140                                 |
| Height/depth (mm)                               | 60                                  |
| Nominal voltage (V)                             | 24                                  |
| Voltage type                                    | AC/DC                               |
| Monitoring equipment                            | None                                |
| With lamp                                       | Yes                                 |
| Lamp Type                                       | Led                                 |
| Lamp holder                                     | Other                               |
| Average lifespan light source (hours)           | 100.000                             |
| Colour of light                                 | Red                                 |
| Protection class                                | I                                   |
| Degree of protection (IP)                       | 20                                  |
| With remote switch connection                   | No                                  |
| Wiring system                                   | Maintained / non-maintained circuit |
| Type of indicator                               | Only single-sided                   |
| Labelling type                                  | Insert sheet/plate                  |
| Circuit   | Other                               |
| Power consumption maintained mode (W)           | 10,71                               |
| Apparent power consumption maintained mode (VA) | 18,39                               |
| Powerfactor                                     | 0,58                                |
| Temperature range (°C)                          | 5 ~ +25                             |

### Article Details

|                 |                     |
|-----------------|---------------------|
| Product class   | Emergency luminaire |
| E-code          | EC001957            |
| Discount group  | 30405               |
| Harmonized code | 9405408440          |
| GLN             | 8713812000008       |

### Ordering information

|           |     |
|-----------|-----|
| Orderable | Yes |
|-----------|-----|

|                        |        |
|------------------------|--------|
| Order-Unit             | Pieces |
| Minimum order quantity | 1      |
| Order Increment        | 1      |

**Supply Information**

|                                   |                |
|-----------------------------------|----------------|
| Weight (kg)                       | 1,5            |
| Packaging                         | Cardboard box  |
| Packaging dimensions (LxWxH) (mm) | 492 x 147 x 62 |