


- NOTES:
- 1. MAXIMUM BAUD RATE IS 9600 (RS232)
  - 2. EXTERNAL POWER REQUIRED, RECEIVER MUST BE ON AT ALL TIMES.

REVISIONS					
REV	ACTION	DRAWN	CHECKED	APPROVED	DATE
AA	L6604	TIERNEY	TIERNEY	HOLLAND	99-02-06
AB	D12507	KASTNER	KASTNER	HOLLAND	02/01/16



ASSEMBLY/QUANTITY		ITEM NO.	PART NUMBER	DESCRIPTION	REF/ZONE DESIG MATERIAL	UNIT MEAS
PARTS LIST						
DO NOT SCALE DRAWING		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		PRODUCT LINE	LEVEL	
THIRD ANGLE PROJECTION		TOLERANCES ARE:		TOTALFLOW®	3	
		DECIMAL		DESIGN	DATE	
		.XX ±		HOLLAND	99-2-6	
		ANGULAR		DRAWN	TIERNEY	
		.XXX ±		CHECKED	TIERNEY	
		BREAK ALL SHARP CORNERS AND EDGES		APPROVED	HOLLAND	
		DIMENSIONS APPLY BEFORE FINISH			99-2-6	
				TITLE		
				WIRING & INTERCONNECT		
				METRICOM RADIO TO (6690, 6790)		
				WI		
				SCALE	SIZE	DOC TYPE
				NONE	B	WI
				DRAWING NO.		
				2018366		
				REV	SHEET	
				AB	1 OF 2	

# RADIO METRICOM

