






Lamp mounting height cross-reference table

Lamp type	Lamp number	Wattage	Maximum mounting height (feet)	
			for open lamp units	for enclosed lamp units
 MR16 halogen	580.0072	6V-5W Flood	8	8
	580.0074	6V-6W Flood	10	10
	580.0079	6V-10W Flood	25	20
	580.0099	12V-10W (38D)	12	12
	580.0080	12V-12W Flood	15	15
	580.0064	12V-20W Flood	20	20
	580.0068	12V-20W HO Flood	30	25
	580.0075	12V-20W AI Flood	20	20
	580.0083	12V-35W Di Flood	50	45
	580.0090	12V-35W HO Flood	55	50
	580.0076	12V-50W Di Flood	50	45
	580.0089	12V-50W HO Flood	70	65
	 MR16 LED	580.0093	12V-4W	25
580.0104	12V-5W	25	25	
580.0106	12V-6W	40	35	
Lamp type	Lamp number	Wattage	Maximum mounting height (feet)	
			for PAR18 heads	for PAR36 heads
 Wedge base T5, T8	570.0012	6V-5.4W	7	7
	570.0026	6V-7.2W	7	7
	570.0016	6V-9W	16	10
	570.0025	12V-9W	15	15
	570.0045	24V-9W	16	10
	570.0028	12V-12W	10	10
	570.0029	12V-18W	15	15
	570.0046	24V-18W	15	15
	Lamp type	Lamp number	Wattage	Maximum mounting height (feet)
for PAR18 heads				for PAR36 heads
 Bi-pin halogen T2-3/4, T2-1/4	580.0012	6V-6W	15	12
	580.0018	6V-8W	15	12
	580.0014	12V-8W	18	15
	580.0017	6V-10W	18	15
	580.0011	6V-12W	12	18
	580.0015	12V-12W	20	15
	580.0022	6V-20W	N/A	20
	580.0027	12V-20W	N/A	20

Lamp mounting height cross-reference table

Lamp type	Lamp number	Wattage	Maximum mounting height (feet) for PAR18 heads	Maximum mounting height (feet) for PAR36 heads
DC-bayonet RP-11, S8 	570.0010	6V-9W	N/A	12
	570.0011	12V-9W	N/A	12
	570.0020	6V-12W	N/A	10
	570.0037	6V-18W	N/A	15
	570.0030	12V-18W	N/A	20
	570.0038	6V-25W	N/A	20
	570.0031	12V-25W	N/A	25
Lamp type	Lamp number	Wattage	Maximum mounting height (feet) for PAR18 heads	Maximum mounting height (feet) for PAR36 heads
H1 / H3	580.0030	12V-55W	N/A	42
	580.0081	24V-70W	N/A	43
Lamp type	Lamp number	Wattage	Maximum mounting height (feet) for PAR18 heads	Maximum mounting height (feet) for PAR36 heads
Sealed beam incandescent PAR 36 	550.0018	6V-8W	N/A	20
	550.0026	12V-12W	N/A	18
	550.0027	12V-18W	N/A	20
	550.0017	6V-25W	N/A	25
	550.0023	12V-25W	N/A	18
	550.0035	6V-30W	N/A	25
	550.0034	12V-30W	N/A	25
Lamp type	Lamp number	Wattage	Maximum mounting height (feet) for PAR18 heads	Maximum mounting height (feet) for PAR36 heads
Sealed beam halogen PAR 36 	550.0022	6V-6W	N/A	17
	550.0024	12V-8W	N/A	20
	550.0037	6V-10W	N/A	25
	550.0019	6V-12W	N/A	20
	550.0025	12V-12W	N/A	25
	550.0021	6V-20W	N/A	35
	550.0047	12V-37W	N/A	60
	550.0012	12V-50W	N/A	35
Lamp type	Lamp number	Wattage	Fixture type	Maximum mounting height (feet)
LED lamp		Std-fwd throw	 LED emergency lighting unit	15
		Std-wide		15
		HT-fwd throw		20
		HT-wide		15
Lamp type	Lamp number	Wattage	Fixture type	Maximum mounting height (feet)
MR16	580.0093	4W LED	 Enclosed ribbed lens	8
	580.0080	12V-12W		8
	580.0064	12V-20W		8
	580.0068	12V-20W HO		8

Notes:

- Above maximum mounting heights are based on the performance of lamping only and are not to be used for photometric purposes, and are based on 0 ft spacing.
- Emergency lighting layouts must be based on the photometric information provided with each product.
- Regardless of the context of the installation, the final mounting height must be lower than stipulated above.