

SHRINK-KON®

# Heat-shrinkable tubing and insulation products



01 Dimensions  
Frame: 24 in. W x 54 in. H x 24 in. D  
Header: 24 in. W x 7 in. H



1. Innovative tubing solutions
2. Innovative insulation solutions

# Plan-O-Gram Display unit



A1	A2	A3	A4	A5	A6	A7	A8
A9	A10	A11	A12	A13	A14	A15	A16
A17	A18	A19	A20	A21	A22	A23	A24
A25	A26	A27	A28	A29	A30	A31	A32

Refer to Quick-Pop brochure  
Template, ELIP Merchandising  
for display accessories and shelves.



Side A

Cat. No.	Description	Qty/ Pkg	Order Qty
A1	HS16-12-4 Heavy-wall tubing*, 4 in, black, #14 - #10 AWG	5	20
A2	HS12-6-4 Heavy-wall tubing*, 4 in, black, #8 - #6 AWG	5	10
A3	HS12-6-4 Heavy-wall tubing*, 4 in, black, #8 - #6 AWG	5	10
A4	HS6-1-4 Heavy-wall tubing*, 4 in, black, #6 - #2 AWG	5	10
A5	HS4-30-4 Heavy-wall tubing*, 4 in, black, #1 - 3/0 AWG	5	10
A6	HS40-400-4 Heavy-wall tubing*, 4 in, black, 2/0 AWG - 350 kcmil	5	5
A7	HS40-400-4 Heavy-wall tubing*, 4 in, black, 2/0 AWG - 350 kcmil	5	5
A8	HS500-1000-4 Heavy-wall tubing*, 4 in, black, 500 - 1000 kcmil	2	2
A9	CPO125-0-A Thin-wall tubing*, black, #30 - #24 AWG	25	25
A10	CPO187-0-A Thin-wall tubing*, 4 in, black, #22 - #14 AWG	25	25
A11	CPO250-0-A Thin-wall tubing*, 4 in, black, #16 - #10 AWG	25	25
A12	CPO375-0-A Thin-wall tubing*, 4 in, black, #12 - #6 AWG	25	25
A13	CPO500-0-A Thin-wall tubing*, 4 in, black, #6 - #1 AWG	25	25
A14	CPO750-0-A Thin-wall tubing*, 4 in, black, #2 - 4/0 AWG	10	10
A15	CPO1000-0-A Thin-wall tubing*, 4 in, black, 2/0 AWG - 350 kcmil	10	10
A16	HS500-1000-4 Heavy-wall tubing*, 4 in, black, 500 - 1000 kcmil	2	2
A17	CPO-A-125-48 Thin-wall tubing* + adhesive, 4 in, black, #30 - #24 AWG	25	25
A18	CPO-A-187-48 Thin-wall tubing* + adhesive, 4 in, black, #22 - #14 AWG	25	25
A19	CPO-A-250-48 Thin-wall tubing* + adhesive, 4 in, black, #22 - #10 AWG	25	25
A20	CPO-A-375-48 Thin-wall tubing* + adhesive, 4 in, black, #16 - #6 AWG	25	25
A21	CPO-A-375-48 Thin-wall tubing* + adhesive, 4 in, black, #16 - #6 AWG	25	25
A22	CPO-A-500-48 Thin-wall tubing* + adhesive, 4 in, black, #22 - #2 AWG	25	25
A23	CPO-A-750-48 Thin-wall tubing* + adhesive, 4 in, black, #4 - 3/0 AWG	25	25
A24	CPO-A-750-48 Thin-wall tubing* + adhesive, 4 in, black, #4 - 3/0 AWG	25	25
A25	CPO-A-250-C-48 Thin-wall tubing* + adhesive, 4 in, transparent, #22 - #10 AWG	25	25
A26	CPO125-C-A Thin-wall tubing*, 4 in, transparent, #30 - #24 AWG	25	25
A27	CPO250-C-A Thin-wall tubing*, 4 in, transparent, #16 - #10 AWG	25	25
A28	CPO250-C-A Thin-wall tubing*, 4 in, transparent, #16 - #10 AWG	25	25
A29	CPO375-C-A Thin-wall tubing*, 4 in, transparent, #12 - #6 AWG	25	25
A30	CPO375-C-A Thin-wall tubing*, 4 in, transparent, #12 - #6 AWG	25	25
A31	CPO500-C-A Thin-wall tubing*, 4 in, transparent, #6 - #1 AWG	25	25
A32	CPO500-C-A Thin-wall tubing*, 4 in, transparent, #6 - #1 AWG	25	25

\* Heat-shrinkable tubing



B1	B2	B3	B4
B5	B6	B7	B8
B9	B10	B11	
B12	B13	B14	B15 B16 B17
B18	B19	B20	B21 B22

Side B

Cat. No.	Description	Qty/ Pkg	Order Qty
B1	WM-0-45 E-Z-CODE Wire marker books. Legend: 0 - 45	10	10
B2	WM-46-90 E-Z-CODE Wire marker books. Legend: 46 - 90	10	10
B3	WM-0 THRU 9 E-Z-CODE Wire marker books. Legend: 0 - 9	10	10
B4	WM-A-Z E-Z-CODE Wire marker books. Legend: A - Z	10	10
B5	CPO250-C-6 Thin-wall tubing*, 6 in, transparent, #16 - #10 AWG	20	100
B6	CPO375-C-6 Thin-wall tubing*, 6 in, transparent, #12 - #6 AWG	20	100
B7	CPO500-C-6 Thin-wall tubing*, 6 in, transparent, #6 - #1 AWG	10	50
B8	CPO750-C-6 Thin-wall tubing*, 6 in, transparent, #2 - 4/0 AWG	10	50
B9	AC5X3 Adhesive Insulating Cover 5 x 3 Inch pad	10	50
B10	AC5X7 Adhesive Insulating Cover 5 x 7 Inch pad	10	50
B11	HS-KIT Thin-wall tubing*, 6 in, black, #14 AWG - 350 kcmil	1	5
	ou CHS-KIT Thin-wall tubing*, 6 in, 7 colours, #14 AWG - 350 kcmil	1	5
B12	MSC500 Motor stub splice insulators 350 - 500 kcmil	5	5
B13	MSC250 Motor stub splice insulators 350 - 500 kcmil	2	6
B14	MSC20 Motor stub splice insulators 350 - 500 kcmil	4	12
B15	MSC2 Motor stub splice insulators 350 - 500 kcmil	10	20
B16	MSC8 Motor stub splice insulators 350 - 500 kcmil	10	30
B17	MSC14 Motor stub splice insulators 350 - 500 kcmil	15	30
B18	HSC8-4 Heat-shrinkable end caps #8 - #6 AWG	10	40
B19	HSC2-20 Heat-shrinkable end caps #6 - #2 AWG	10	40
B20	HSC30-250 Heat-shrinkable end caps #1 - 3/0 AWG	5	30
B21	HSC300-600 Heat-shrinkable end caps 2/0 AWG - 350 kcmil	5	20
B22	HSC700-1000 Heat-shrinkable end caps 250 - 500 kcmil	5	10

\* Heat-shrinkable tubing