

Pictogramoverzicht

NEN-EN-ISO 7010

Pictogramoverzicht

L x H (mm)	Opaal Lexan 2 mm		Folie 0,5 mm	Inlegfolie 0,3 mm		231x126	202x136	Inlegfolie 0,35 mm	Zelfklevende folie 0,1 mm		
	222x113	322x113	326x180	292x140	296x162			302x127	275x117	202x157	
	EVAGO 22	EVAGO 32	HOR	SER-FC(X) SER-FO(X)	SER-FI(X)	PRE	IND	AQL 08	AQL/DZ DIB325 FM(N)	IND	
	PP 220/51	PP 320/51	P 51	P 51-SER-C	P 51-SER-I	P51-PRE	PF 202/51	PSA 51	TS 275/51	TS 202/51	
	PP 220/52	PP 320/52	P 52	P 52-SER-C	P 52-SER-I	P52-PRE	PF 202/52	PSA 52	TS 275/52	TS 202/52	
	PP 220/53	PP 320/53	P 53	P 53-SER-C	P 53-SER-I	P53-PRE	PF 202/53	PSA 53	TS 275/53	TS 202/53	
	PP 220/58	PP 320/58	P 58	P 58-SER-C	P 58-SER-I	P58-PRE	PF 202/58	PSA 58	TS 275/58	TS 202/58	
	PP 220/OPAAL	PP 320/OPAAL	P OPAAL						PSA OPAAL		
	PP 220/10	PP 320/10	P 10	P 10-SER-C	P 10-SER-I	P10-PRE					
	PP 220/11	PP 320/11	P 11	P 11-SER-C	P 11-SER-I	P11-PRE					
			P 12								
			P 13	P 13-SER-C	P 13-SER-I	P13-PRE		PSA 13			

Pictogramoverzicht

L x H (mm)	Opaal PET-G 3 mm			Helder perspex (XT) 8 mm	
	320x137	675x295	315x175	315x175	315x175
	TA-TL 400 WER	(D)TA 725	ITA	HOR(I)	HOR(I)
	PP 400/51	PP 725/51	PPT 315/51/BL	PP 315/51/BL	PPL 315/51/BL
	PP 400/52	PP 725/52	PPT 315/52/BL	PP 315/52/BL	PPL 315/52/BL
	PP 400/53	PP 725/53	PPT 315/53/BL	PP 315/53/BL	PPL 315/53/BL
	PP 400/58	PP 725/58	PPT 315/58/BL	PP 315/58/BL	PPL 315/58/BL
				PP 315/10/BL	PPL 315/10/BL
				PP 315/11/BL	PPL 315/11/BL
				PP 315/12/BL	PPL 315/12/BL
				PP 315/13/BL	PPL 315/13/BL

Pictogramplaten met /BL zijn enkelzijdig bedrukt (achterzijde groen). Indien dubbelzijdige bedrukking gewenst is dan /BL vervangen door /DZ.