

PRODUCT LEAFLET

Cold shrink earthing kit

CSE 12-42 kV



For CSE-A, CSE-B, CSS-B and TP-A, an earthing kit must be used which shall be ordered separately. In 3-core cable earthing kit, cold shrink crutch seal, protective hoses, constant force springs and Cu-braids are included. In 1-core cable earthing kit, cold shrink protective hoses, constant force springs and Cu-braids are included.

Type	Product Type	Conductor cross section (mm ²)			
		8.7/15(17.5) kV	12/20(24)kV	18/30(36)kV	26/35(40.5)kV
3-core with armoring earthing kit	3151-3871CNTHB	25-50	25-35	-	-
	3151-3872CNTHB	70-120	50-95	35	-
	3151-3873CNTHB	150-240	120-185	50-95	-
	3151-3874CNTHB	300-400	240-300	120-185	50-95
	3151-3875CNTHB	500-630	400-500	240-400	120-185
	3151-3876CNTHB	-	630	500-630	240-400
	3151-3877CNTHB	-	-	-	500-630
1-core without armoring earthing kit	3151-3871CNTHB1	25-50	25-35	-	-
	3151-3872CNTHB1	70-120	50-95	35	-
	3151-3873CNTHB1	150-240	120-185	50-95	-
	3151-3874CNTHB1	300-400	240-300	120-185	-
	3151-3875CNTHB1	500-630	400-500	240-400	50-185
	3151-3876CNTHB1	-	630	500-630	240-400
	3151-3877CNTHB1	-	-	-	500-630
1-core with armoring earthing kit	3151-3871CNTHB2	25-50	25-35	-	-
	3151-3872CNTHB2	70-120	50-95	35-50	-
	3151-3873CNTHB2	150-240	120-185	70-150	-
	3151-3874CNTHB2	300-400	240-300	185-240	50-150
	3151-3875CNTHB2	500-630	400-630	300-400	185-300
	3151-3876CNTHB2	-	-	500-630	400-630
1-core copper wire screen unarmored earthing kit	3151-3871CNTHB-CW	25-50	25-35	-	-
	3151-3872CNTHB-CW	70-120	50-95	25	-
	3151-3873CNTHB-CW	150-240	120-185	35-95	25
	3151-3874CNTHB-CW	300-400	240-400	120-240	35-95
	3151-3875CNTHB-CW	500-630	500-630	300-400	120-240
	3151-3876CNTHB-CW	-	-	500-630	300-630
Lead sheath submarine cable earthing kit	3151-3875CNTHB-WP	-	-	-	59-95
	3151-3876CNTHB-WP	-	-	-	120-185
	3151-3877CNTHB-WP	-	-	-	240-630