



DECO LED20/HF

Slave 20 watt 230 Volt surface mount led luminaire, series Decolux

Product Information

Type	DECO LED20/HF
Catalog number	11100355
Category_	Escape route lighting
GTIN	08713812772226
GID	7TCA304050R0022
Serie	Decolux
Warranty (Year)	3



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling;Wall
Mounting form	Surface
Material housing	Plastic
Colour housing	White
Material cover	Plastic, opal
Material	Plastic
Colour	White
Length (mm)	350
Width (mm)	350
Height/depth (mm)	101
Maximum outer diameter (mm)	350
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	20
Number of lamps	1
Light output in emergency operation (lm)	1830
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	4000
CRI	80
Protection class	I
Degree of protection (IP)	65
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Impact strength (IK)	10
Power consumption maintained mode (W)	19,5
Apparent power consumption maintained mode (VA)	20,8
Nominal current (mA)	86
Inrush Current (A - 0.1ms)	0,8
Powerfactor	0,93
Temperature range (°C)	0 ~ +40

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30401
Harmonized code	9405608000
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,8
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	355 x 355 x 110