



AQL 03/HF/LED

Slave 3 watt, 230 Volt surface mount led luminaire, series Aqualux

Product Information

Type	AQL 03/HF/LED
Catalog number	7000055
Category_	Escape route lighting
GTIN	08713812758336
GID	7TCA091130R0316
Serie	Aqualux
Warranty (Year)	5



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling;Wall
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	White / aluminium
Material cover	Plastic, transparent
Material	Aluminium / polycarbonate
Colour	White / aluminium
Length (mm)	381
Width (mm)	170
Height/depth (mm)	75
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	3
Number of lamps	1
Light output in emergency operation (lm)	153
Average lifespan light source (hours)	50.000
Colour of light	White
Colour temperature (K)	6500
Protection class	II
Degree of protection (IP)	65
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Impact strength (IK)	10
Power consumption maintained mode (W)	4,8
Apparent power consumption maintained mode (VA)	8,3
Nominal current (mA)	35,9
Inrush Current (A - 0.1ms)	3,6
Powerfactor	0,58
Temperature range (°C)	0 ~ +35

Article Details

Product class	Emergency luminaire
---------------	---------------------

E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,448
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111