



中国国家强制性产品认证证书

证书编号: 2003010304060095

委托人名称、地址

ABB France
2 rue d'Arsonval 69680 Chassieu France

生产者(制造商)名称、地址

ABB France
2 rue d'Arsonval 69680 Chassieu France

生产企业名称、地址

ABB Bulgaria EOOD - Rakovski branch
BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of
Rakovski, Rakovski Industrial Zone, 14 Industrial Road 1, nr, 14-18

产品名称和系列、规格、型号

切换电容器接触器

UA26, UA30; Ui: 1000V; UA26: Ith: 45A; AC-6b: Ue/le: AC220/230/240/400/415/440/500/550/660/690V/31A;
UA30: Ith: 65A; AC-6b: Ue/le: AC220/230/240/400/415/440/500/550/660/690V/41A; Us: 24V 50/60Hz,
48V 50/60Hz, 110V 50Hz/110-120V 60Hz, 220-230V 50Hz/230-240V 60Hz, 380-400V 50Hz/400-415V 60Hz,
400-415V 50Hz/415-440V 60Hz; 极数: 3P; 配用辅助触头: (本体): 1NOIth: 16A; AC-15: Ue/le:
24-127V/6A, 220-240V/4A, 380-440V/3A, 500-690V/2A; DC-13: Ue/le: 24V/6A, 48V/2.8A, 72V/2A,
110-125V/1.1A, 220-250V/0.55A; 型号解释详见附件

产品标准和技术要求

GB/T 14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求,
特发此证。

发证日期: 2020年08月07日有效期至: 2022年05月23日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2003年07月15日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

经中国合格评定国家认可委员会认可 CNAS C001-P



主任:

陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2003010304060095

NAME AND ADDRESS OF THE APPLICANT

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE MANUFACTURER

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE FACTORY

ABB Bulgaria EOOD – Rakovski branch
BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski Industrial Zone, 14 Industrial Road 1, nr,14-18

PRODUCT NAME, MODEL AND SPECIFICATION

Contactors for capacitor switching

UA26, UA30; Ui: 1000V; UA26: Ith: 45A; AC-6b: Ue/le: AC220/230/240/400/415/440/500/550/660/690V/31A; UA30: Ith: 65A; AC-6b: Ue/le: AC220/230/240/400/415/440/500/550/660/690V/41A; Us: 24V 50/60 Hz, 48V 50/60Hz, 110V 50Hz/110-120V 60Hz, 220-230V 50Hz/230-240V 60Hz, 380-400V 50Hz/400-415 V 60Hz, 400-415V 50Hz/415-440V 60Hz; Poles: 3P; Attached Auxiliary Contacts:1NOIth: 16A; AC-15: Ue/le: 24-127V/6A, 220-240V/4A, 380-440V/3A, 500-690V/2A; DC-13: Ue/le: 24V/6A, 48V/2.8A, 72V/2 A, 110-125V/1.1A, 220-250V/0.55A

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.4-2010

This is to certify that the above mentioned product(s) complies with therequirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Aug.07,2020Valid until:May.23,2022

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Jul.15,2003

The certificate information is available through CNCA's website: www.cnca.gov.cn
Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

附录:

第 1 页 共 1 页

证书编号: 2003010304060095

纸号: 2658770

型号的解释:

UA	26	30	10	
I	II	III	IV	V

I - Main designation : UA

II - Range size

26, 30

III - Main Pole Construction

30 - 3 Normally Opened and 0 Normally Closed main poles.

IV - Auxiliary Pole Construction

01 - One normally closed auxiliary pole provided.

10 - One Normally opened auxiliary pole provided.

V - Coil code

Coil code	Control voltage	
	50Hz	60Hz
81	24	24
83	48	48
84	110	110-120
80	220-230	230-240
85	380-400	400-415
86	400-415	415-440

注: 此附录与证书同时使用时有效



主任:

陆杨



中国质量认证中心