

Hazardous location remote fixture



CERTIFICATION

CLASS I

Division 2 Group A, B, C, D

CLASS II

Division 1 & 2 Group E, F, G

CLASS III

Contact your ABB sales representative to verify classification



APPROVALS



Key features and benefits

Quality illumination requires fewer fixtures

Certified Class I Zone 2, Groups IIA, IIB and IIC

Certified Class I Division 2, Groups A, B, C and D as per CSA C22.2

No.137-M1981

Temperature Codes: T4, T4A and T5 as per Canadian Electrical Code, Part I and CSA C22.2 No.137-M1981)

Extreme operational temperature range: -40°C (-40°F)

Choice of single- or double-lamp models

High-efficacy LED lamps of 4W, 5W and 6W

Input voltage: 6V, 12V, 24V or 120V

Fully gasketed die-cast aluminum back plate

Clear polycarbonate cover, UV and impact resistant

Easy installation on a 4-inch octagonal box (included)

Comes standard with tamper-proof screws and bit

Certified to CSA 22.2 No.141-15

DIMENSIONS Dimensions are approximate and subject to change.

