


Dimension drawings

Automatic transfer switches

UL: 30U, 60U, 100U, 125U, 160U, 200U

IEC: 200E, 250E



OX_30-250

No. of poles	2	3	4
A	45/1.77	45/1.77	45/1.77
A1	277/10.91	277/10.91	277/10.91
A2	120/4.72	165/6.50	210/8.27
B	285/11.22	330/12.99	375/14.76

Note: B dimension, recommended to leave 2cm/1" free space on the left side (for removing the mechanism)