

PRODUCT SPECIFICATION

# CTSR2-SWM3-G1

## Serenga 2 Self-Contained IP54 Naveo Wall Surface

Catalogue Number **CTSR2-SWM3-G1**  
GID **7TCA091180R0246**

Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Self-Contained (individual battery)**  
Mounting Method/Form **Ceiling Surface**  
Housing Material **Aluminium/Plastic**  
Colour **White**  
Dimensions (LxWxD) **150 x 150 x 35 mm**  
Temperature Range **5 to 40°C**  
Weight **0.961 Kg**

Nominal Voltage **220-240v AC 50Hz**  
Emergency Duration (Hours) **3 Hours**  
Battery **NiMH**  
Monitoring Equipment **Naveo test**  
Lamp **1 x 2W LED**  
Light output in Emergency Operation **203 Lumens**  
Average Lifespan light source (hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 5600 / 70**  
Degree of Protection **IP 54 IK tbc**

Wiring System **Maintained / non-maintained circuit**  
Type of Legend **Not Applicable**  
Exit Sign Viewing/Recognition Distance (m) **Not Applicable**  
Power Consumption **3.5 VA / 3 Watts**  
Nominal Current **15 (mA)**  
Inrush Current **tbc A to 0.1 ms**

### Accessories

- SR2-LENS1** Lens A Escape route 2-4M Ceiling mount
- SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount
- SR2-LENS3** Lens C Escape route 8-12M Ceiling mount
- SR2-LENS4** Lens D Open Area 2-4M Ceiling mount
- SR2-LENS5** Lens E Open Area 4-8M Ceiling mount
- SR2-LENS6** Lens E Open Area 8-12M Ceiling mount
- SR2-LENS7** Lens G Escape route 2-4M Wall mount

