



产品认证证书

证书编号: CQC2006010304208085

申请人名称及地址

ABB AB, Control Products
SE-721 61 Vasteras Sweden

制造商名称及地址

ABB AB, Control Products
SE-721 61 Vasteras Sweden

生产企业名称及地址

ABB 新会低压开关有限公司 (V005372)
广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号

软起动器

PSR3-600-70, PSR6-600-70, PSR9-600-70, PSR12-600-70, PSR16-600-70, PSRC3-600-70, PSRC6-600-70, PSRC9-600-70,
PSRC12-600-70, PSRC16-600-70, PSR3-600-11, PSR6-600-11, PSR9-600-11, PSR12-600-11, PSR16-600-11,
PSRC3-600-11, PSRC6-600-11, PSRC9-600-11, PSRC12-600-11, PSRC16-600-11,
PSRC3-600-70-1, PSRC6-600-70-1, PSRC9-600-70-1, PSRC12-600-70-1, PSRC16-600-70-1: 详细参数及型号解释见附件

产品标准和技术要求

GB/T 14048.6-2016

认证模式

型式试验+获证后监督

上述产品符合 CQC11-462142-2019 认证规则的要求, 特发此证。

发证日期: 2020年08月14日 有效期至: 2024年03月25日
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: _____

陆杨



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0346448



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2006010304208085

NAME AND ADDRESS OF THE APPLICANT

ABB AB,Control Products

SE-721 61 Vasteras Sweden

NAME AND ADDRESS OF THE MANUFACTURER

ABB AB,Control Products

SE-721 61 Vasteras Sweden

NAME AND ADDRESS OF THE FACTORY

ABB Xinhui Low Voltage Switchgear Co.,Ltd. (V005372)

Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China

PRODUCT NAME, MODEL AND SPECIFICATION

soft starter

PSR3-600-70, PSR6-600-70, PSR9-600-70, PSR12-600-70, PSR16-600-70, PSRC3-600-70, PSRC6-600-70, PSRC9-600-70, PSRC12-600-70, PSRC16-600-70, PSR3-600-11, PSR6-600-11, PSR9-600-11, PSR12-600-11, PSR16-600-11, PSRC3-600-11, PSRC6-600-11, PSRC9-600-11, PSRC12-600-11, PSRC16-600-11, PSRC3-600-70-1, PSRC6-600-70-1, PSRC9-600-70-1, PSRC12-600-70-1, PSRC16-600-70-1: See the attachment for detailed parameters and explanation

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.6-2016

TYPE OF CERTIFICATION SCHEMES

Type testing+Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462142-2019 .

Valid from: Aug.14,2020

Valid until: Mar.25,2024

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President: _____

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nanshuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

C 0346448



产品认证证书

附录

第 1 页 共 2 页

证书编号: CQC2006010304208085

纸号: 346448

详细参数:

PSR3-600-70, PSR6-600-70, PSR9-600-70, PSR12-600-70, PSR16-600-70, PSRC3-600-70, PSRC6-600-70, PSRC9-600-70, PSRC12-600-70, PSRC16-600-70, PSR3-600-11, PSR6-600-11, PSR9-600-11, PSR12-600-11, PSR16-600-11, PSRC3-600-11, PSRC6-600-11, PSRC9-600-11, PSRC12-600-11, PSRC16-600-11, PSRC3-600-70-1, PSRC6-600-70-1, PSRC9-600-70-1, PSRC12-600-70-1, PSRC16-600-70-1

额定绝缘电压 (Ui): 600V;

约定发热电流 (Ith):

PSR3-600-70, PSR3-600-11, PSRC3-600-11, PSRC3-600-70, PSRC3-600-70-1: 3.9A,
PSR6-600-70, PSR6-600-11, PSRC6-600-11, PSRC6-600-70, PSRC6-600-70-1: 6.8A,
PSR9-600-70, PSR9-600-11, PSRC9-600-11, PSRC9-600-70, PSRC9-600-70-1 : 9A,
PSR12-600-70, PSR12-600-11, PSRC12-600-11, PSRC12-600-70, PSRC12-600-70-1: 12A,
PSR16-600-70, PSR16-600-11, PSRC16-600-11, PSRC16-600-70, PSRC16-600-70-1: 16A;

额定工作电压 (Ue): AC208~600V;

额定工作电流 (Ie): 3.9A, 6.8A, 9A, 12A, 16A;

额定功率 (Pe):

PSR3-600-70, PSR3-600-11, PSRC3-600-11, PSRC3-600-70, PSRC3-600-70-1:
230VAC/0.75kW, 400VAC/1.5kW, 500VAC/2.2kW;
PSR6-600-70, PSR6-600-11, PSRC6-600-11, PSRC6-600-70, PSRC6-600-70-1:
230VAC/1.5kW, 400VAC/3kW, 500VAC/4kW;
PSR9-600-70, PSR9-600-11, PSRC9-600-11, PSRC9-600-70, PSRC9-600-70-1 :
230VAC/2.2kW, 400VAC/4kW, 500VAC/4kW;
PSR12-600-70, PSR12-600-11, PSRC12-600-11, PSRC12-600-70, PSRC12-600-70-1:
230VAC/3kW, 400VAC/5.5kW, 500VAC/5.5kW;

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 2 页 共 2 页

证书编号: CQC2006010304208085

纸 号: 346448

PSR16-600-70, PSR16-600-11, PSRC16-600-11, PSRC16-600-70, PSRC16-600-70-1:

230VAC/4kW, 400VAC/7.5kW, 500VAC/7.5kW;

使用类别: AC-53a;极数: 3P; 外壳防护等级: IP20

型号的解释:

(Explanation of model/ type)

PSR 3-600-70-1

1 2 3 4 5

1 = Product family name (Soft starter), it can be PSR or PSRC;

(产品系列(软起动器), 可以是 PSR 或 PSRC)

2 = Rated motor current (in line), it can be 3, 6, 9, 12, 16;

(额定电机电流(外接法), 可以是 3,6,9,12,16)

3 = Rated main voltage, it can be 600;

(额定主回路电压, 是 600)

4 = Supply voltage, Us, it can be 70, 11;

(控制回路电源电压 Us, 可以是 70 或 11)

70=100-240 V AC, 11=24V AC/DC;

5 = Design code, it can be 1 or blank;

(设计代码, 可以是 1 或 空白)

1 = Customer specific software not related to safety (optional, only PSRC)..

(特定客户软件版本, 与安全无关(PSRC 系列可选))

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>