

PRODUCT SPECIFICATION

# OH3L261V2

## Horizon Self-Contained 25M IP40 Self-Test Wall Surface

Catalogue Number **OH3L261V2**  
GID **7TCA091160R0300**  
Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Self-Contained (individual battery)**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **Aluminium/Plastic**  
Colour **White/Silver**  
Dimensions (LxWxD) **364 x 167 x 82 mm**  
Temperature Range **0 to 25°C**  
Weight **1.3 Kg**

Emergency Duration (Hours) **3 Hours**  
Battery **NiCd**  
Monitoring Equipment **Automatic self test**  
Lamp **2 x 2W LED**  
Emergency Light Output (Lumens) **Not Applicable**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 6350 / 73**  
Degree of Protection **IP40**

Type of Legend **Single Sided (Order separate)**  
Exit Sign Viewing/Recognition Distance (m) **25**  
Nominal Voltage **220-240v AC 50/60Hz**  
Power Consumption **9.9 VA / 5.1 Watts**  
Current **Nominal: 42.5mA (mA) Inrush: 18A**

### Accessories

**XEN2H** Single Sided Down ISO7010 Legend  
**XEN3H** Single Sided Left ISO7010 Legend  
**XEN6H** Single Sided Right ISO7010 Legend  
**XEN5H** Single Sided Up ISO7010 Legend  
**XB01H** Single Sided Arabic English Legend  
**XLF-SN802** Fire Extinguisher Legend  
**XLF-SN803** Hose Reel Legend

**OH/BCM** Ceiling Bracket for Vertical Mount  
**OH/WG** Protective Wire Guard



Exit Sign  
OH3L261V2 + XEN2H

