

PRODUCT SPECIFICATION

LTCXXW1LS1

Daylite 230v AC Opal IP65 EMEX Test Surface

Catalogue Number **LTCXXW1LS1**
GID **7TCA091140R0544**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Mains / Slave Operation**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Plastic**
Colour **White**
Dimensions (LxWxD) **342 x 98 x 72 mm**
Temperature Range **0 to 40°C**
Weight **0.67 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
Battery **Mains / Central Battery**
Monitoring Equipment **EMEX test**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **214**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**
Exit Sign Viewing/Recognition Distance (m) **23**
Nominal Voltage **220-240v AC 50/60Hz**
Power Consumption **4.6 VA / 4.4 Watts**
Current **Nominal: 13.59mA (mA) Inrush: 1.1A**

Accessories

RSEN2X Down ISO7010 Legend
RSEN3X Left ISO7010 Legend
RSEN6X Right ISO7010 Legend
RSEN5X Up ISO7010 Legend
RSB1X Arabic English Legend

XTR Semi-recessing bezel White



Exit Sign
LTCXXW1LS1 + RSEN5X



Bulkhead
LTCXXW1LS1

