



中国国家强制性产品认证证书

证书编号：2010010304445623

委托人名称、地址

ABB France
2 rue d'Arsonval 69680 Chassieu France

生产者（制造商）名称、地址

ABB France
2 rue d'Arsonval 69680 Chassieu France

生产企业名称、地址

ABB France
2 rue d'Arsonval 69680 Chassieu France

产品名称和系列、规格、型号

接触器
AF*26, AF*30, AF*38; 具体型号见附件

产品标准和技术要求

GB/T 14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求，特发此证。

发证日期：2020 年 08 月 07 日有效期至：2024 年 12 月 10 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2010 年 11 月 25 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询
经中国合格评定国家认可委员会认可 CNAS C001-P



主任：陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2010010304445623

NAME AND ADDRESS OF THE APPLICANT

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE MANUFACTURER

ABB France
2 rue d'Arsonval 69680 Chassieu France

NAME AND ADDRESS OF THE FACTORY

ABB France
2 rue d'Arsonval 69680 Chassieu France

PRODUCT NAME, MODEL AND SPECIFICATION

Contactor
AF*26, AF*30, AF*38; see the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.4-2010

This is to certify that the above mentioned product(s) complies with therequirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Aug.07,2020**Valid until:**Dec.10,2024

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Nov.25,2010

The certificate information is available through CNCA's website: www.cnca.gov.cn
Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

附 录

第 1 页 共 4 页

证书编号: 2010010304445623

纸 号: 2658780

AF*26, AF*30, AF*38

Ui: 690V;

Uimp: 6kV;

Ith: 55A (contactors 4-Pole),

50A (contactors 3-Pole with screw terminals and Ring Tongue terminals 螺钉端子和环形端子),

35A (contactors 3-Pole with spring terminals 弹簧端子);

AF*26_3P screw 螺钉 / Push-In 插入 Ring Tongue 环形:

AC-1: Ue/Ie: 690V/45A;

AC-3: Ue/Ie:

220-230-240V/26A, 380-400V/26A, 415V/26A, 440V/26A, 500V/23A, 690V/17A;

AC-8a: Ue/Ie: 400V/30A;

AF26_4P screw 螺钉 / Ring Tongue 环形:

AC-1: Ue/Ie: 690V/45A;

AF*26_3P spring 弹簧:

AC-1: Ue/Ie: 690V/35A;

AC-3: Ue/Ie:

220-230-240V/26A, 380-400V/26A, 415V/26A, 440V/26A, 500V/23A, 690V/17A;

AC-8a: Ue/Ie: 400V/30A;

AF*30_3P screw 螺钉 / Push-In 插入 Ring Tongue 环形:

AC-1: Ue/Ie: 690V/50A;

AC-3: Ue/Ie:

220-230-240V/33A, 380-400V/32A, 415V/32A, 440V/32A, 500V/28A, 690V/21A;

AC-8a: Ue/Ie: 400V/40A;

AF*38_3P screw 螺钉 / Push-In 插入 Ring Tongue 环形:

AC-1: Ue/Ie: 690V/50A;

AC-3: Ue/Ie:

注: 此附录与证书同时使用时有效。



主 任: 陆 楠



中国质量认证中心



中国国家强制性产品认证证书

附 录

第 2 页 共 4 页

证书编号: 2010010304445623

纸 号: 2658780

220-230-240V/40A, 380-400V/38A, 415V/38A, 440V/38A, 500V/33A, 690V/24A;

AC-8a: Ue/Ie:400V/50A;

AF38_4P screw 螺钉/ Ring Tongue 环形:

AC-1: Ue/Ie: 690V/55A;

Us: Normal Power 正常功耗: 24-60V 50/60Hz, 24-60V 50/60Hz 20-60V DC,

48-130V 50/60Hz-DC, 100-250V 50/60Hz-DC, 250-500V 50/60Hz-DC;

Low Power 低功耗: 12-20VDC, 24-60V 50/60Hz 20-60V DC, 48-130V 50/60Hz-DC,

100-250V 50/60Hz-DC, 24VDC;

极数:3P, 4P;

外壳防护等级: IP20;

配用辅助触头: (外置)

CA4-***, CAT4-***, VE4;

Ith: 16A;

AC-15:Ue/Ie: 500-690V/2A, 380-440V/3A, 220-240V/4A, 24-127V/6A;

DC-13:Ue/Ie: 600V/0.1A, 500V/0.13A, 400V/0.15A, 220-250V/0.27A, 110-125V/0.55A,

72V/1A, 48V/4A, 24V/6A;

CAL4-**, CA4-**, CC4-**;

Ith: 16A;

AC-15:Ue/Ie:AC690V/2A, AC500V/2A, AC440V/3A, AC400V/3A, AC240V/4A, AC127V/6A;

DC-13:Ue/Ie:DC600V/0.1A, DC500V/0.13A, DC400V/0.15A, DC250V/0.27A, DC125V/0.55A,

DC72V/1A, DC48V/4A, DC24V/6A;

1NO, 1NC, 2NO2NC

注: 此附录与证书同时使用时有效。



主 任: 陆 楠



中国质量认证中心



中国国家强制性产品认证证书

附 录

第 3 页 共 4 页

证书编号: 2010010304445623

纸 号: 2658780

型号解释:

AF S 26 Z B - 30 - 00 RT - 21 U

I II III IV V VI VII VIII IX X

I - Main designation - AF 产品系列

II - Application

Blank - Standard applications 空白: 基本型号

S contactor for safety application S: 安全接触器

III - Range size 大小

26, 30, 38

IV - Coil Type 线圈类型

Blank - Normal Power Coil (NP) 空白-正常功耗线圈(NP)

Z - Low Power Coil (LP) Z-低功耗线圈(LP)

V - Application type 应用类型

Blank - Industrial 空白-工业用

B - Railway / rolling stock B-铁路机车应用

VI - Main Pole Construction

22 - 2 normally opened and 2 normally closed main poles. 2 常开 2 常闭

30 - 3 normally opened and 0 normally closed main poles. 3 常开

40 - 4 normally opened and 0 normally closed main poles. 4 常开

VII - Auxiliary Pole Construction

00 - 0 normally closed auxiliary pole provided. 无辅助触头

11 - 1 normally opened and 1 normally closed auxiliary poles, side mounting 1 常开 1 常闭, 侧面安装

22 - 2 normally opened and 2 normally closed auxiliary poles, mounted as 2nd stack (AFS only available

with this configuration) 2 常开 2 常闭, 仅用于安全接触器

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心



中国国家强制性产品认证证书

附 录

第 4 页 共 4 页

证书编号: 2010010304445623

纸 号: 2658780

VIII - Connection type 接线方式

Blank = Screw type connection 空白=螺钉端子接线

S = Spring type connection 弹簧端子接线

K = Push in terminals 插入式端子接线

RT = Ring Tongue connection 环形端子接线

IX - Coil code 线圈代号

See table 1 见表 1

X - Blank =All the markets 空白=所有市场

U = For North America markets U=北美市场

Table 1:

Control Voltage 控制电压	Coil code 线圈代号
NP 24-60V 50/60Hz	41
NP 24-60V 50/60Hz 20-60V DC	11
NP 48-130V 50/60Hz-DC	12
NP 100-250V 50/60Hz-DC	13
NP 250-500V 50/60Hz-DC	14
LP 12-20VDC	20
LP 24-60V 50/60Hz 20-60V DC	21
LP 48-130V 50/60Hz-DC	22
LP 100-250V 50/60Hz-DC	23
LP 24V DC	30

注: 此附录与证书同时使用时有效。



主 任: 陆 楠



中国质量认证中心