TYPICAL WIRING DIAGRAM

c UL us LISTED

POWER OUTLET 66FL



USE COPPER WIRE ONLY

RAINPROOF POWER OUTLET
CAT. NO. U013P MOD 3
30 AMPS MAX
120 VOLTS AC
TYPE 3R ENCLOSURE

- GROUND-FAULT CIRCUIT-INTERRUPTER (GFCI) PROTECTION IS NOT PROVIDED AS PART OF THIS POWER OUTLET. IF GFCI PROTECTION IS REQUIRED, THE POWER OUTLET SHALL BE INSTALLED ON A GFCI PROTECTED CIRCUIT.

- USE ONLY 60 DEG. C (140 DEG. F) OR 75 DEG. C (167 DEG. F) CONDUCTORS ON ALL FIELD INSTALLED LINE, LOAD AND NEUTRAL TERMINATIONS. - CONNECT LINE WIRES TO PROPER TERMINALS ON RECEPTACLE.

- SUITABLE FOR USE AS RECREATIONAL VEHICLE SITE SUPPLY. IF USED AS RECREATIONAL VEHICLE SITE SUPPLY EQUIPMENT, DO NOT BOND NEUTRAL.

LUG TIGHTENING TORQUE (IN-LB)

SCREW TYPE	WIRE SIZE	TORQUE
SLOT	14 - 10 8 6 - 4 3 - 2/0	32 - 35 36 - 40 41 - 45 45 - 50

WIRE RANGE

CONNECTOR	COPPER	
	SOLID	STRD
LINE - R32UWR	10-4	10-4
LOAD - PLUG	--	--
NEUTRAL - R32UWR	10-4	10-4
EQUIPMENT GRND. - GL2	12-8	12-2
R32UWR RECEPTACLE	TORQUE: 25 IN-LB.	

WHEN CABINET HAS PROVISIONS FOR A CONDUIT HUB, SELECT FROM THE CHART BELOW

CONDUIT SIZE	CLOSURE CAP	3/4	1	1 1/4	1 1/2
CAT. NO.	B01	B07	B10	B12	B15

DANGER

HAZARD OF ELECTRICAL SHOCK OR BURN. TURN OFF POWER BEFORE WORKING INSIDE THIS EQUIPMENT.

RISQUE D´ÉLECTROCUTION OU DE BRÛLURE ÉTEINDRE TOUTES LES SOURCES D´ALIMENTATION DE L´ÉQUIPMENT AVEC D´Y TRAVALIER.

MIDWEST ELECTRIC PRODUCTS, INC
305 GREGSON DRIVE
CARY, NC 27511
WWW.MIDWESTELECTRIC.COM
SAL318@

MNP600005P REV. B

Midwest®