

CRF

Fixed external male thread fitting



Straight fitting with fixed external male thread. For insertion into threaded entries or knockouts using a locknut to secure.

Certifications / Standards:



Fire performance / EMC:



Features & benefits:

- Easy to install and secure grip
- Only two pieces to reduce total cost and components

Applications:

- Light industrial
- General purpose
- Commercial and industrial construction



Material:

- Nickel plated brass

Temperature range:

°C	-65	-45	-25	-5	0	5	60	90	105	120	250	350
°F	-85	-49	-13	23	32	41	140	194	221	248	482	662

Static
Dynamic

Ingress protection:

Conduit	IP54
CRGE	✓

UV Resistance:

- Very high

Conforms to:

- CE marked to Low Voltage Directive 2014/35/EU

Chemical resistance guide:

- See publication TDS000081

Compatible with:

- CRGE galvanised steel PVC covered conduit

CRF fitting – Part numbers and dimensions

Part No.	Conduit size		Nominal dimensions (mm)			
	Metric thread	Nominal Conduit Size	A	B	Min Bore	W1
CRF00M16	M16 x 1.5	12	11.0	18.0	8.5	17.0
CRF01M16	M16 x 1.5	16	12.0	15.0	11.5	20.0
CRF02M20	M20 x 1.5	20	11.0	17.0	15.1	24.0
CRF03M25	M25 x 1.5	25	12.5	20.5	18.8	30.0
CRF04M32	M32 x 1.5	32	12.5	26.5	26.2	38.0
CRF05M40	M40 x 1.5	40	21.0	18.5	34.0	46.0
CRF06M50	M50 x 1.5	50	21.0	27.0	45.0	45.0
CRF07M63	M63 x 1.5	63	27.0	34.0	54.0	70.0
CRF08M75	M75 x 1.5	75	30.0	39.5	36.5	84.0

