



中国国家强制性产品认证证书

证书编号: 2024010307658788

认证委托人名称及地址

ABB S. p. A.

Via Vittor Pisani 16-20124 Milano (MI)-Italy

生产者名称及地址

ABB S. p. A.

Viale dell'Industria 18-20010 Vittuone (MI)-Italy

生产企业名称及地址

ABB S. p. A.

Via Ardeatina 2491-00040 Santa Palomba (RM) - Italy

产品名称和系列、型号、规格

剩余电流动作断路器

DS201: Uimp: 4kV;Ui: 500V;Ue: 230V;In: 2A,4A,6A,8A,10A,13A,16A,20A,25A,32A,40A;瞬时脱扣类型: B, C 型;IΔ n: 10 mA, 30 mA, 100mA,300mA;额定剩余动作类型: A, AC, AP-R, 电磁式;IΔ m: 4500 A (32A,40A),6000A(2A,4A,6A,8A,10A,13A,16A,20A,25A);Ics:6000A;Icn: 6000A;极数: 1P+N;适用于隔离;适用频率: 50/60Hz; 型号解释见附页

产品标准和技术要求

GB/T 16917.1-2014;GB/T 16917.21-2008

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024)的要求, 特发此证。

发证日期: 2024 年 07 月 16 日 有效期至: 2029 年 07 月 15 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验,
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010307658788

证书附页: 第 1 页 共 1 页

型号解释:

DS 201	C	16	0.03	A
1	2	3	4	5

1——Series DS201 系列

2——Instantaneous tripping current 瞬时脱扣特性:

B – B Characteristic 特性

C – C Characteristic 特性

3——Rated current 额定电流:

2A; 4A; 6 A; 8A; 10A; 13A; 16 A; 20A; 25A; 32A; 40A

4——Rated residual current 额定剩余动作电流 $I_{\Delta n}$

0,01 A; 0,03 A; 0.1A; 0,3 A;

5——Operating characteristic 剩余电流动作特性:

AC- AC 型; A- A 型; AP-R - AP-R 型

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010307658788

NAME AND ADDRESS OF THE APPLICANT

ABB S.p.A.
Via Vittor Pisani 16-20124 Milano (MI)-Italy

NAME AND ADDRESS OF THE MANUFACTURER

ABB S.p.A.
Viale dell'Industria 18-20010 Vittuone (MI)-Italy

NAME AND LOCATION OF THE FACTORY

ABB S.p.A.
Via Ardeatina 2491-00040 Santa Palomba (RM) - Italy

PRODUCT NAME,MODEL AND SPECIFICATION

Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBO's)

DS201 : Uimp: 4kV;Ui: 500V;Ue: 230V;In: 2A,4A,6A,8A,10A,13A,16A,20A,25A,32A,40A;Type B,C;IΔ n : 10 mA, 30 mA, 100mA,300mA;Type A , AC , AP-R , Electromagnetic ;IΔ m : 4500 A
(32A,40A),6000A(2A,4A,6A,8A,10A,13A,16A,20A,25A);Ics:6000A;Icn: 6000A;Poles: 1P+N;Suitable for isolation ;
Applicable frequency : 50/60Hz

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 16917.1-2014;GB/T 16917.21-2008

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.16,2024

Valid until: Jul.15,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010307658788

Appendix: Page 1 of 1

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

<u>DS 201</u>	<u>C</u>	<u>16</u>	<u>0.03</u>	<u>A</u>
1	2	3	4	5

1—Series DS201 系列

2—Instantaneous tripping current 瞬时脱扣特性:

B – B Characteristic 特性

C – C Characteristic 特性

3—Rated current 额定电流:

2A; 4A; 6 A; 8A; 10A; 13A; 16 A; 20A; 25A; 32A; 40A

4—Rated residual current 额定剩余动作电流 $I_{\Delta n}$

0,01 A; 0,03 A; 0.1A; 0,3 A;

5—Operating characteristic 剩余电流动作特性:

AC- AC 型; A- A 型; AP-R - AP-R 型

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.