




$S = \begin{cases} \text{Ø13} - \text{Special IM 3001/*11} \\ \text{M10} - \text{Special IM 3601/*11} \end{cases}$
M2AA 080

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador


VC233: Flange ring FF 165 / Aro brida FF 165 // VC234: Flange ring FT 165 / Aro brida FT 165

Motor Dimension Print

Motor Type :
M2AA 080

Document N° :
3GZE 500 082-951.005

Description : Motor flange mounted special (2-pieces) IM3001/*11 or IM3601/*11
Motor con brida (2 piezas) IM3001/*11 o IM3601/*11



Unit : Discret Automation & Motion - Fábrica Motores
Date : 2012-11-29

Issued by : ERM/ A. Caubera
Approved by : ERM/ G. Blanes

Replaces :
Replaced by :

Asea Brown Boveri, S.A.

Customer Reference :

ABB